

# DATA SHEET

## ANTI-SULFURATED CHIP RESISTORS AUTOMOTIVE GRADE

AA series

$\pm 5\%$ ,  $\pm 1\%$ ,  $\pm 0.5\%$

sizes 0201/0402/0603/0805/1206/

1210/1218/2010/2512

RoHS compliant & Halogen free



**SCOPE**

This specification describes AA0201 to AA2512 chip resistors with lead-free terminations made by thick film process.

**APPLICATIONS**

- Car electronics
- Engine control unit
- Body control system
- Safety devices

**FEATURES**

- Superior resistance against sulfur containing atmosphere
- AEC-Q200 qualified
- Moisture sensitivity level: MSL I
- AA series soldering is compliant with J-STD-020D
- Halogen free epoxy
- RoHS compliant
- Reduce environmentally hazardous waste
- High component and equipment reliability
- The resistors are 100% performed by automatic optical inspection

**ORDERING INFORMATION - GLOBAL PART NUMBER**

Part number is identified by the series name, size, tolerance, packaging type, temperature coefficient, taping reel and resistance value.

**GLOBAL PART NUMBER**

**AA** XXXX X X X XX XXXX L  
 (1) (2) (3) (4) (5) (6) (7)

**(1) SIZE**

0201 / 0402 / 0603 / 0805 / 1206 / 1210 / 1218 / 2010 / 2512

**(2) TOLERANCE**

D = ±0.5%  
 F = ±1%  
 J = ±5% (for Jumper ordering, use code of J)

**(3) PACKAGING TYPE**

R = Paper/PE taping reel                      K = Embossed taping reel

**(4) TEMPERATURE COEFFICIENT OF RESISTANCE**

– = Base on spec

**(5) TAPING REEL**

07 = 7 inch dia. Reel                                      13 = 13 inch dia. Reel

**(6) RESISTANCE VALUE**

1Ω to 10 MΩ  
 There are 2~4 digits indicated the resistance value. Letter R/K/M is decimal point, no need to mention the last zero after R/K/M, e.g. 1K2, not 1K20.

**(7) DEFAULT CODE**

Letter L is the system default code for ordering only. (Note)

Resistance rule of global part number

| Resistance coding rule | Example                                  |
|------------------------|--|
| XRXX<br>(1 to 9.76 Ω)  | 1R = 1 Ω<br>1R5 = 1.5 Ω<br>9R76 = 9.76 Ω |
| XXRX<br>(10 to 97.6 Ω) | 10R = 10 Ω<br>97R6 = 97.6 Ω              |
| XXXR<br>(100 to 976 Ω) | 100R = 100 Ω<br>976R = 976 Ω             |
| XKXX<br>(1 to 9.76 KΩ) | 1K = 1,000 Ω<br>9K76 = 9760 Ω            |
| XMXX<br>(1 to 9.76 MΩ) | 1M = 1,000,000 Ω<br>9M76 = 9,760,000 Ω   |
| XXMX<br>(10 MΩ)        | 10M = 10,000,000 Ω                       |

**ORDERING EXAMPLE**

The ordering code for an AA0402 chip resistor, value 100 KΩ with ±1% tolerance, supplied in 7-inch tape reel is: AA0402FR-07100KL

**NOTE**

1. All our R-Chip products are RoHS compliant and Halogen free. "LFP" of the internal 2D reel label states "Lead-Free Process".
2. On customized label, "LFP" or specific symbol can be printed.

**MARKING**


AA0201 / AA0402



AA0603 / AA0805 / AA1206 / AA1210 / AA2010 / AA2512




AA0603



AA0805 / AA1206 / AA1210 / AA2010 / AA2512



AA1218



**NOTE**

For further marking information, please refer to data sheet "Chip resistors marking". Marking of AA series is the same as RC series.

**CONSTRUCTION**

The resistors are constructed on top of an automotive grade ceramic body. Internal metal electrodes are added at each end and connected by a resistive glaze. The resistive glaze is covered by a lead-free glass. The composition of the glaze is adjusted to give the approximately required resistance value and laser trimming of this resistive glaze achieves the value within tolerance. The whole element is covered by a protective overcoat. Size 0603 and bigger is marked with the resistance value on top. Finally, the two external terminations (Ni / matte tin) are added, as shown in Fig.8.


**OUTLINES**



**DIMENSIONS**

Table I For outlines, please refer to Fig. 9

| TYPE   | L (mm)     | W (mm)     | H (mm)     | l <sub>1</sub> (mm) | l <sub>2</sub> (mm) |
|--------|------------|------------|------------|---------------------|---------------------|
| AA0201 | 0.60 ±0.03 | 0.30 ±0.03 | 0.23 ±0.03 | 0.12 ±0.05          | 0.15 ±0.05          |
| AA0402 | 1.00 ±0.05 | 0.50 ±0.05 | 0.35 ±0.05 | 0.20 ±0.10          | 0.25 ±0.10          |
| AA0603 | 1.60 ±0.10 | 0.80 ±0.10 | 0.45 ±0.10 | 0.25 ±0.15          | 0.25 ±0.15          |
| AA0805 | 2.00 ±0.10 | 1.25 ±0.10 | 0.50 ±0.10 | 0.35 ±0.20          | 0.35 ±0.20          |
| AA1206 | 3.10 ±0.10 | 1.60 ±0.10 | 0.55 ±0.10 | 0.45 ±0.20          | 0.50 ±0.20          |
| AA1210 | 3.10 ±0.10 | 2.60 ±0.15 | 0.57 ±0.10 | 0.45 ±0.20          | 0.50 ±0.20          |
| AA1218 | 3.10 ±0.10 | 4.60 ±0.10 | 0.57 ±0.10 | 0.45 ±0.20          | 0.50 ±0.20          |
| AA2010 | 5.00 ±0.10 | 2.50 ±0.15 | 0.57 ±0.10 | 0.55 ±0.20          | 0.55 ±0.20          |
| AA2512 | 6.35 ±0.10 | 3.20 ±0.15 | 0.57 ±0.10 | 0.60 ±0.20          | 0.60 ±0.20          |



**ELECTRICAL CHARACTERISTICS**

Table 2

| TYPE   | RESISTANCE RANGE  | CHARACTERISTICS             |                      |                       |                                 |  | Jumper Criteria                         |
|--------|---|-----------------------------|----------------------|-----------------------|---------------------------------|--|---|
|        |   | Operating Temperature Range | Max. Working Voltage | Max. Overload Voltage | Dielectric Withstanding Voltage | Temperature Coefficient of Resistance  |   |
| AA0201 |   |                             | 25V                  | 50V                   | 50V                             | $1\Omega \leq R \leq 10\Omega$ ,<br>$-100/+400$ ppm/°C<br>$10\Omega < R \leq 10\text{M}\Omega$ ,<br>$\pm 300$ ppm/°C | Rated Current 0.5A<br>Max. Current 1.0A |
| AA0402 |   |                             | 50 V                 | 100 V                 | 100 V                           |  | Rated Current 1A<br>Max. Current 2A     |
| AA0603 | 5% (E24)<br>$1\Omega \leq R \leq 22\text{M}\Omega$                          |                             | 75V                  | 150 V                 | 150 V                           |  | Rated Current 1A<br>Max. Current 2A     |
| AA0805 | (0201: Max. 10MΩ.<br>1218: Max. 1MΩ)<br>0.5%, 1% (E24/E96)                  | -55 °C to +155 °C           | 150 V                | 300 V                 | 300 V                           |  | Rated Current 2A<br>Max. Current 5A     |
| AA1206 | $1\Omega \leq R \leq 10\text{M}\Omega$<br>(1218: Max. 1MΩ)<br>Jumper < 50mΩ |                             | 200 V                | 400 V                 | 500 V                           | $1\Omega \leq R \leq 10\Omega$ ,<br>$\pm 200$ ppm/°C   | Rated Current 2A<br>Max. Current 10A    |
| AA1210 |   |                             | 200 V                | 500 V                 | 500 V                           | $10\Omega < R \leq 10\text{M}\Omega$ ,<br>$\pm 150$ ppm/°C   | Rated Current 2A<br>Max. Current 10A    |
| AA1218 |   |                             | 200 V                | 500 V                 | 500 V                           | $10\text{M}\Omega < R \leq 22\text{M}\Omega$ ,<br>$\pm 200$ ppm/°C   | Rated Current 6A<br>Max. Current 10A    |
| AA2010 |   |                             | 200 V                | 500 V                 | 500 V                           |  | Rated Current 2A<br>Max. Current 10A    |
| AA2512 |   |                             | 200 V                | 500 V                 | 500 V                           |  | Rated Current 2A<br>Max. Current 10A    |

**FOOTPRINT AND SOLDERING PROFILES**

Recommended footprint and soldering profiles. Please refer to data sheet “Chip resistors mounting”.

**PACKING STYLE AND PACKAGING QUANTITY**

Table 3 Packing style and packaging quantity

| PACKING STYLE            | REEL DIMENSION | AA0201 | AA0402 | AA0603 | AA0805 | AA1206 | AA1210 | AA1218 | AA2010 | AA2512 |
|--------------------------|----------------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| Paper/PE taping reel (R) | 7" (178 mm)    | 10,000 | 10,000 | 5,000  | 5,000  | 5,000  | 5,000  | ---    | ---    | ---    |
|                          | 13" (330 mm)   | 50,000 | 50,000 | 20,000 | 20,000 | 20,000 | 20,000 | ---    | ---    | ---    |
| Embossed taping reel (K) | 7" (178 mm)    | ---    | ---    | ---    | ---    | ---    | ---    | 4,000  | 4,000  | 4,000  |

**NOTE**

I. For paper/PE/embossed tape and reel specifications/dimensions, please refer to data sheet “Chip resistors packing”.

**FUNCTIONAL DESCRIPTION**

**OPERATING TEMPERATURE RANGE**

Range: -55°C to +155°C

**POWER RATING**

Each type rated power at 70°C:

- AA0201=1/20W (0.05W)
- AA0402=1/16 W (0.0625W)
- AA0603=1/10 W (0.1W)
- AA0805=1/8 W (0.125W)
- AA1206=1/4 W (0.25W)
- AA1210=1/2 W (0.5W)
- AA1218=1 W
- AA2010=3/4 W (0.75W)
- AA2512=1 W

**RATED VOLTAGE**

The DC or AA (rms) continuous working voltage corresponding to the rated power is determined by the following formula:

$$V = \sqrt{P \times R}$$

Or Maximum working voltage whichever is less

Where

V = Continuous rated DC or AA (rms) working voltage (V)

P = Rated power (W)

R = Resistance value ( $\Omega$ )



**TESTS AND REQUIREMENTS**

Table 4 Test condition, procedure and requirements

| TEST                         | TEST METHOD                                | PROCEDURE   | REQUIREMENTS   |
|------------------------------|--|---|--|
| High Temperature Exposure    | AEC-Q200 Test 3<br>MIL-STD-202 Method 108  | 1,000 hours at $T_A = 155\text{ }^\circ\text{C}$ , unpowered  | $\pm(1.0\%+0.05\Omega)$<br><50 m $\Omega$ for Jumper   |
| Moisture Resistance          | AEC-Q200 Test 6<br>MIL-STD-202 Method 106  | Each temperature / humidity cycle is defined at 8 hours (method 106F), 3 cycles / 24 hours for 10d. with $25\text{ }^\circ\text{C} / 65\text{ }^\circ\text{C}$ 95% R.H, without steps 7a & 7b, unpowered<br><br>Parts mounted on test-boards, without condensation on parts | $\pm(0.5\%+0.05\Omega)$ for D/F tol.<br>$\pm(2.0\%+0.05\Omega)$ for J tol.<br><100 m $\Omega$ for Jumper                     |
| Biased Humidity              | AEC-Q200 Test 7<br>MIL-STD-202 Method 103  | 1,000 hours; $85\text{ }^\circ\text{C} / 85\%$ RH<br>10% of operating power<br><br>Measurement at $24\pm 4$ hours after test conclusion.  | $\pm(3.0\%+0.05\Omega)$<br><100 m $\Omega$ for Jumper  |
| Operational Life             | AEC-Q200 Test 8<br>MIL-STD-202 Method 108  | 1,000 hours at $125\text{ }^\circ\text{C}$ , derated voltage applied for 1.5 hours on, 0.5 hour off, still-air required   | $\pm(1.0\%+0.05\Omega)$<br><100 m $\Omega$ for Jumper  |
| Resistance to Soldering Heat | AEC-Q200 Test 15<br>MIL-STD-202 Method 210 | Condition B, no pre-heat of samples<br>Lead-free solder, $260\pm 5\text{ }^\circ\text{C}$ , $10\pm 1$ seconds immersion time<br><br>Procedure 2 for SMD: devices fluxed and cleaned with isopropanol  | $\pm(0.5\%+0.05\Omega)$ for D/F tol.<br>$\pm(1.0\%+0.05\Omega)$ for J tol.<br><50 m $\Omega$ for Jumper<br>No visible damage |
| Thermal Shock                | AEC-Q200 Test 16<br>MIL-STD-202 Method 107 | $-55/+125\text{ }^\circ\text{C}$<br><br>Number of cycles is 300. Devices mounted<br><br>Maximum transfer time is 20 seconds.<br>Dwell time is 15 minutes. Air – Air   | $\pm(1.0\%+0.05\Omega)$<br><50 m $\Omega$ for Jumper   |
| ESD                          | AEC-Q200 Test 17<br>AEC-Q200-002           | 1 pos. + 1 neg. discharges<br>0201: 500V<br>0402/0603: 1KV<br>0805 and above: 2KV   | $\pm(3.0\%+0.05\Omega)$<br><50 m $\Omega$ for Jumper   |

| TEST   | TEST METHOD                               | PROCEDURE   | REQUIREMENTS                                    |
|--|---|---|---|
| Solderability<br>- Wetting                     | AEC-Q200 Test 18                          | Electrical Test not required Magnification 50X<br>SMD conditions:<br>(a) Method B, aging 4 hours at 155 °C dry heat, dipping at 235±3 °C for 5±0.5 seconds.<br>(b) Method B, steam aging 8 hours, dipping at 215±3 °C for 5±0.5 seconds.<br>(c) Method D, steam aging 8 hours, dipping at 260±3 °C for 7±0.5 seconds.   | Well tinned (≥95% covered)<br>No visible damage |
|  | J-STD-002                                 |   |   |
| Board Flex                                     | AEC-Q200 Test 21<br>AEC-Q200-005          | Chips mounted on a 90mm glass epoxy resin PCB (FR4)<br>Bending for 0201/0402: 5 mm<br>0603/0805: 3 mm<br>1206 and above: 2 mm<br>Holding time: minimum 60 seconds   | ±(1.0%+0.05Ω)<br><50 mΩ for Jumper              |
| Temperature Coefficient of Resistance (T.C.R.) | IEC 60115-1 4.8<br>MIL-STD-202 Method 304 | At +25/-55 °C and +25/+125 °C<br><br><b>Formula:</b><br>$T.C.R = \frac{R_2 - R_1}{R_1(t_2 - t_1)} \times 10^6 \text{ (ppm/°C)}$<br>Where<br>t <sub>1</sub> =+25 °C or specified room temperature<br>t <sub>2</sub> =-55 °C or +125 °C test temperature<br>R <sub>1</sub> =resistance at reference temperature in ohms<br>R <sub>2</sub> =resistance at test temperature in ohms | Refer to table 2                                |
| Short Time Overload                            | IEC60115-1 4.13                           | 2.5 times of rated voltage or maximum overload voltage whichever is less for 5 sec at room temperature  | ±(1.0%+0.05Ω)<br><50 mΩ for Jumper              |
| FOS  | ASTM-B-809-95                             | - Sulfur (saturated vapor) 1000 hours, 90±2 °C unpowered  | ±(1.0%+0.05Ω)                                   |
|  | ASTM-B-809-95*<br>*Modified               | - Sulfur 750 hours, 105 °C. unpowered   | ±(4.0%+0.05Ω)                                   |



**REVISION HISTORY**

| REVISION  | DATE          | CHANGE NOTIFICATION | DESCRIPTION                              |
|-----------|---------------|---------------------|--|
| Version 3 | Dec. 08, 2015 | -                   | - Update Dielectric Withstanding Voltage |
| Version 2 | Apr. 09, 2015 | -                   | - Modified FOS test procedure            |
| Version 1 | Jan. 27, 2015 | -                   | - Dimensions update                      |
| Version 0 | Feb. 27, 2014 | -                   | - First issue of this specification      |

**LEGAL DISCLAIMER**

Yageo, its distributors and agents (collectively, "Yageo"), hereby disclaims any and all liabilities for any errors, inaccuracies or incompleteness contained in any product related information, including but not limited to product specifications, datasheets, pictures and/or graphics. Yageo may make changes, modifications and/or improvements to product related information at any time and without notice.

Yageo makes no representation, warranty, and/or guarantee about the fitness of its products for any particular purpose or the continuing production of any of its products. To the maximum extent permitted by law, Yageo disclaims (i) any and all liability arising out of the application or use of any Yageo product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for a particular purpose, non-infringement and merchantability.

Yageo statements regarding the suitability of products for certain types of applications are based on Yageo's knowledge of typical operating conditions for such types of applications in a generic nature. Such statements are neither binding statements of Yageo nor intended to constitute any warranty concerning the suitability for a specific customer application or use. They are intended for use only by customers with requisite knowledge and experience for determining whether Yageo products are the correct products for their application or use. In addition, unpredictable and isolated cases of product failure may still occur, therefore, customer application or use of Yageo products which requires higher degree of reliability or safety, shall employ additional protective safeguard measures to ensure that product failure would not result in personal injury or property damage.

Yageo products are not designed for application or use in medical, life-saving, or life-sustaining devices or for any other application or use in which the failure of Yageo products could result in personal injury or death. Customers using or selling Yageo products not expressly indicated for above-mentioned purposes shall do so at their own risk and agree to fully indemnify Yageo and hold Yageo harmless.

Information provided here is intended to indicate product specifications only. Yageo reserves all the rights for revising this content without further notification, as long as products are unchanged. Any product change will be announced by PCN.