



PLA171 Single-Pole, Normally Open OptoMOS[®] Relay

Parameter	Rating	Units
Load Voltage	800	V _P
Load Current	100	mA _{rms} / mA _{DC}
On-Resistance (max)	50	Ω
Input Control Current	2	mA

Features

- 7mm Separation of Output Pins
- 800V_P Blocking Voltage
- 5000V_{rms} Input/Output Isolation
- Low Drive Power Requirements
- Arc-Free With No Snubbing Circuits
- No EMI/RFI Generation
- Small Surface Mount Package
- Flammability Rating UL 94 V-0

Applications

- Instrumentation
- Multiplexers
- Data Acquisition
- Electronic Switching
- I/O Subsystems
- Meters (Watt-Hour, Water, Gas)
- Medical Equipment—Patient/Equipment Isolation
- Automotive High-Voltage Circuitry
- Aerospace
- Industrial Controls

Description

Specially designed to provide 7mm of separation between the two output pins, IXYS Integrated Circuits' PLA171 is a single-pole, normally open (1-Form-A) Solid State Relay that uses optically coupled MOSFET technology to provide an enhanced input to output isolation of 5000V_{rms}.

Its optically coupled outputs, which use the patented OptoMOS architecture, are controlled by a highly efficient infrared LED.

The PLA171 is designed to replace, and offers superior reliability over, electromechanical relays. This device provides bounce-free switching in a compact surface-mount package.


Approvals

- UL Certified Component: File E76270
- EN/IEC 60950-1 Certified Component: Certificate available on our website


Ordering Information

Part #	Description
PLA171P	6-Pin (8-Pin Body) Flatpack (50/Tube)
PLA171PTR	6-Pin (8-Pin Body) Flatpack, Tape & Reel (1000/Reel)

Pin Configuration



Switching Characteristics of Normally Open Devices





Absolute Maximum Ratings are stress ratings. Stresses in excess of these ratings can cause permanent damage to the device. Functional operation of the device at conditions beyond those indicated in the operational sections of this data sheet is

Typical values are characteristic of the device at +25°C, and are the result of engineering evaluations. They are provided for information purposes only, and are not part of the manufacturing

not implied.

testing requirements.

Absolute Maximum Ratings @ 25°C

Parameter	Ratings	Units
Blocking Voltage	800	V _P
Reverse Input Voltage	5	V
Input Control Current	50	mA
Peak (10ms)	1	А
Input Power Dissipation ¹	150	mW
Total Power Dissipation ²	800	mW
ESD, Human Body Model	8	kV
Isolation Voltage, Input to Output (60 Seconds)	5000	V _{rms}
Operational Temperature	-40 to +85	°C
Storage Temperature	-40 to +125	°C
Derate linearly 1.22 mW//90		

¹ Derate linearly 1.33 mW / °C

² Derate linearly 6.67 mW / °C

Electrical Characteristics @ 25°C


Parameter Conditions Symbol Min Units Тур Max **Output Characteristics** Load Current Continuous 1 100 I_c=2mA I, mA_{rms} / mA_{DC} -Peak I_F=2mA , t=10ms I_{LPK} . _ ±350 mA_P On-Resistance² $I_{r}=2mA, I_{I}=100mA$ 40 50 - R_{ON} Ω $I_{r}=5mA$, $I_{I}=1mA$ 70 85 -Off-State Leakage Current $I_{\rm F}$ =0mA, $V_{\rm I}$ =800 $V_{\rm P}$ -1 I_{leak} μΑ Switching Speeds Turn-On 0.42 5 t_{on} $I_{F}=5mA, V_{I}=10V$ ms Turn-Off t_{off} 0.15 5 -Output Capacitance $I_{r}=0$ mA, $V_{1}=50$ V, f=1MHz C_{OUT} 11 pF -Input Characteristics Input Control Current to Activate ³ I,=100mA 0.39 2 mΑ $|_{F}$ -Input Control Current to Deactivate 0.1 mΑ I_{F} Input Voltage Drop 1.2 I_c=5mA V_{F} 0.9 1.5 V Reverse Input Current V_R=5V I_{R} . . 10 μA **Common Characteristics** pF Input to Output Capacitance V_{IO}=0V, f=1MHz CIO -3 -


Load derates linearly from 100mA @ 25°C to 55mA @85°C.
Measurement taken within 1 second of on-time.


³ For applications requiring high temperature operation (greater than 60°C) a minimum LED drive current of 5mA is recommended.





PERFORMANCE DATA*












On-Resistance (Ω)



Blocking Voltage (V_P)


0


956 964 972 980 988 996 1004


*Unless otherwise noted, data presented in these graphs is typical of device operation at 25°C. For guaranteed parameters not indicated in the written specifications, please contact our application department.





PERFORMANCE DATA*















Temperature (°C)





0.20





0


Voltage (V)


2

4

6

Maximum Load Current vs. Temperature (I_F=5mA)





100

50

0

-50


-100

-6

-4

-2

-oad Current (mA)



*Unless otherwise noted, data presented in these graphs is typical of device operation at 25°C. For guaranteed parameters not indicated in the written specifications, please contact our application department.

20

-40 -20 0 20 40 60 80 100



Manufacturing Information

Moisture Sensitivity

All plastic encapsulated semiconductor packages are susceptible to moisture ingression. IXYS Integrated Circuits classifies its plastic encapsulated devices for moisture sensitivity according to the latest version of the joint industry standard, IPC/JEDEC J-STD-020, in force at the time of product evaluation. We test all of our products to the maximum conditions set forth in the standard, and guarantee proper operation of our devices when handled according to the limitations and information in that standard as well as to any limitations set forth in the information or standards referenced below.

Failure to adhere to the warnings or limitations as established by the listed specifications could result in reduced product performance, reduction of operable life, and/or reduction of overall reliability.

This product carries a Moisture Sensitivity Level (MSL) classification as shown below, and should be handled according to the requirements of the latest version of the joint industry standard **IPC/JEDEC J-STD-033**.

Device	Moisture Sensitivity Level (MSL) Classification	
PLA171P	MSL 1	

ESD Sensitivity



This product is ESD Sensitive, and should be handled according to the industry standard JESD-625.

Soldering Profile

Provided in the table below is the Classification Temperature (T_C) of this product and the maximum dwell time the body temperature of this device may be $(T_C - 5)^{\circ}C$ or greater. The classification temperature sets the Maximum Body Temperature allowed for this device during lead-free reflow processes. For through-hole devices, and any other processes, the guidelines of **J-STD-020** must be observed.

Device	Classification Temperature (T _c)	Dwell Time (t _p)	Max Reflow Cycles
PLA171P	260°C	30 seconds	3


Board Wash

IXYS Integrated Circuits recommends the use of no-clean flux formulations. Board washing to reduce or remove flux residue following the solder reflow process is acceptable provided proper precautions are taken to prevent damage to the device. These precautions include, but are not limited to: using a low pressure wash and providing a follow up bake cycle sufficient to remove any moisture trapped within the device due to the washing process. Due to the variability of the wash parameters used to clean the board, determination of the bake temperature and duration necessary to remove the moisture trapped within the package is the responsibility of the user (assembler). Cleaning or drying methods that employ ultrasonic energy may damage the device and should not be used. Additionally, the device must not be exposed to flux or solvents that are Chlorine- or Fluorine-based.






Mechanical Dimensions



PLA171PTR Tape & Reel



For additional information please visit our website at: www.ixysic.com

IXYS Integrated Circuits makes no representations or warranties with respect to the accuracy or completeness of the contents of this publication and reserves the right to make changes to specifications and product descriptions at any time without notice. Neither circuit patent licenses nor indemnity are expressed or implied. Except as set forth in IXYS Integrated Circuits' Standard Terms and Conditions of Sale, IXYS Integrated Circuits assumes no liability whatsoever, and disclaims any express or implied warranty, relating to its products including, but not limited to, the implied warranty of merchantability, fitness for a particular purpose, or infringement of any intellectual property right.

The products described in this document are not designed, intended, authorized or warranted for use as components in systems intended for surgical implant into the body, or in other applications intended to support or sustain life, or where malfunction of IXYS Integrated Circuits' product may result in direct physical harm, injury, or death to a person or severe property or environmental damage. IXYS Integrated Circuits reserves the right to discontinue or make changes to its products at any time without notice.