







NO.	H	
01	1.5	
02	1.6	
03	1.7	√
04	2.0	
05	2.5	
06	4.3	





P. C. B. Layout



Circuit Diagram


Remarks:

1. Rated current, Voltage: DC 12V 50mA
2. Contact resistance: $\leq 50m\Omega$
3. Insulation resistance: $\geq 100M\Omega$
4. The intensity of operations: $250 \pm 50gf$
5. Life requirements: 100000 times
6. Withstand voltage: AC250V 1 minute
7. All materials comply with RoHS2.0 standards



Remarks:

- 1, The number of tapes per volume is 4000 PCS;
- 2, Braiding process, can not be caused by carrying half crushed;
- 3, Pay attention to the direction of the tape, with a clockwise direction out of the carrier tape, with a hole in the top or right

NO.	PART NAME	MATERIAL	QTY	FINISHING	General	Tolerance	DRAWN	YANGBIAO	Product Name	Tact switch
6	Housing	PPA	1	Black	$X \leq 1$	± 0.05	AFFIRM	YANGGUOQUAN	Model Number	TS52BA17B25B001
5	Terminal	Phosphor copper	4	Ag Plating	$1 \leq X \leq 5$	± 0.10	AUDITING		DATE	2017-07-08
4	Shrapnel	SUS	1	Ag Plating	$5 \leq X \leq 10$	± 0.15				
3	Paster	Polyimide	1	Yellow	$X > 10$	± 0.25				
2	Cover	SUS	1	Primary	ANGLE	$\pm 3^\circ$	SHEET	1:1 UNIT mm		
1	Button	Brass	1	Yellow						
							 ZHEJIANG HONGSUI PRECISION ELECTRONIC CO., LTD			

