


Datasheet

Features

- 1) Twice the rated voltage of conventional products..
- 2) Perfect for use in high voltage circuit. (Camera Flash circuit, etc)
- 3) ROHM resistors have obtained ISO9001 / IATF16949 certification.
- 4) Corresponds to AEC-Q200.



Products list

Part No.	Siz (mm)	ze (inch)	Rated power (70°c) (W)	Limiting plement voltage (V)	Temperature coefficient (ppm/°C)	Resistance tolerance (%)	Resistanc	0	Operating temperature range (°C)	Automotive grade available
					±200	F(±1%)		, (E24/96 series)		
KTR03	1608	0603	0.10	350	±100	F(±1%)	10≦R≦10M	(E24/96 series)	-55 ~ +155	Yes
					<u>+200</u>	J(±5%)	1≦R≦10M	(E24 series)		
KTR10	2012	0805	0.125	400	±100	F(±1%)	1≦R≦10M	(E24/96 series)	-55 ~ +155	Yes
KIKIU	2012	0005	0.125	400	±200	J(±5%)	1≦R≦30M	(E24 series)	-55 ~ +155	165
KTR18	3216	1206	0.25	500	±100	F(±1%)	1≦R≦10M	(E24/96 series)	-55 ~ +155	Yes
KI KIO	5210	1200	0.25	500	±200	J(±5%)	1≦R≦10M	(E24 series)	-55 ~ +155	165
KTR25	3225	1210	0.33	600	±100	F(±1%)	1≦R≦10M	(E24/96 series)	-55 ~ +155	Yes
IN R23	5225	1210	0.33	000	<u>+200</u>	J(±5%)	1≦R≦10M	(E24 series)	-55~ +155	165

* E24 : Standard products, E96 : Custom products.

* Design and specifications are subject to change without notice.Carefully check the specification sheet supplied with the product before using or ordering it.

Part number description

Part No.	
KTR	


(High voltage resistance chip resistors)

Size (mm [inch])
03 (1608 [0603])
10 (2012 [0805])
18 (3216 [1206])
25 (3225 [1210])


0




Packagir	Packaging specifications code						
Part No.	Code	Packaging specifications	Quantity / Reel				
KTR03	EZP	Paper tape (4mm Ptch)	5,000				
KTR10	EZP	Paper tape (4mm Ptch)	5,000				
KTR18	EZP	Paper tape (4mm Ptch)	5,000				
KTR25	JZP	Embossed tape (4mm Ptch)	4,000				



•Chip resistor dimensions and markings








<Marking method>

There are three or four digits used for the calculation number w according to IEC code and "R" is used for the decimal point.

(Unit:mm)

Part No.	(mm)	(inch)	L	W	t	а	b	Marking existence
KTR03	1608	0603	1.60 ±0.10	0.80 ±0.10	0.45±0.10	0.30 ±0.20	0.30±0.20	No*
KTR10	2012	0805	2.00 ±0.10	1.25±0.10	0.55 ±0.10	0.30 ±0.20	0.40±0.20	Yes
KTR18	3216	1206	3.20 ±0.15	1.60±0.15	0.55 ±0.10	0.30 ±0.25	0.50 ±0.25	Yes
KTR25	3225	1210	3.20 ±0.15	2.50 ±0.15	0.55 ±0.10	0.30 ±0.25	0.50±0.25	Yes
	•						*Onlywi	th square mark

•Land pattern example




				(Unit:mm)
Dimensions Part No.	А	В	С	D
KTR03	1.0	2.0	0.8	0.5
KTR10	1.2	2.6	1.15	0.7
KTR18	2.2	4.0	1.5	0.9
KTR25	2.2	4.0	2.3	0.9



•Derating curve

When the ambient temperature exceeds 70°C, power dissipation must be adjusted according to the derating curve below.

KTR03/10/18/25



Characteristics

Test items	Guaranteed Value	Test conditions
Resistance	See P.1	20°C
Variation of resistance with temperature	See P.1	Measurement: +25/-55, +25/+125°C
Overload	±(2.0%+0.1Ω)	Test voltage is the smaller one of ① or ② ①Rated voltage(current)×2.5, 2s ②Maximum overload voltage ※
Solderability	Anew uniform coating of minimum of 95% of the surface being immersed and no soldering damage.	Rosin-ethanol solution(25% mass) Soldering condition:245±5°C Duration of immersion:2.0±0.5s
Resistance to soldering heat	$\pm(1.0\% + 0.05\Omega)$ No remarkable abnormality on the appearance.	Soldering condition:260±5°C Duration of immersion:10±1s
Rapid change of temperature	±(1.0%+0.05Ω)	Test temp:-55°C~+125°C 5cycles
Damp heat, steady state	±(3.0%+0.1Ω)	40°C, 93%(Relative humidity) Test time: 1,000h
Endurance at 70°C	±(3.0%+0.1Ω)	Rated voltage(current),70°C 1.5h:ON-0.5h:OFF Test time: 1,000h
Endurance	±(3.0%+0.1Ω)	155°C Test time : 1,000h
Resistance to solvent	±(1.0%+0.05Ω)	23±5°C Immersion cleaning, 5±0.5min Solvent: 2-propanol
Bend strength of the end face plating	$\pm(1.0\% \pm 0.05\Omega)$ Without mechanical damage such as breaks.	-

Maximum overload voltage (Test voltage)


KTR03	KTR10	KTR18	KTR25
500V	800V	1000V	1200V



JIS C 5201-1

Compliance Standard(s): IEC60115-8

•Tape dimensions



_	_				(Unit:mm)
Part No.	W	F	E	A0	B0
KTR03	8.0 <u>±</u> 0.3	3.5±0.05	1.75 <i>±</i> 0.1	1.1±0.1	1.9±0.1
KTR10	8.0±0.3	3.5±0.05	1.75±0.1	1.65 ^{+0.2} -0.1	2.4 ^{+0.2} -0.1
KTR18	8.0 <u>±</u> 0.3	3.5±0.05	1.75 <i>±</i> 0.1	1.95 ^{+0.1} -0.05	3.5 ^{+0.15} -0.05
			•	•	


Part No.	D0	P0	P1	P2	T2
KTR03	Ф1.5 ^{+0.1}	4.0±0.1	4.0±0.1	2.0±0.05	MAX1.1
KTR10	Ф1.5 ^{+0.1}	4.0±0.1	4.0±0.1	2.0±0.05	MAX1.1
KTR18	Ф1.5 ^{+0.1}	4.0±0.1	4.0±0.1	2.0±0.05	MAX1.1


■Embossed tape P2 PC ß P1 AO

_	_				(Uhit:mm)
Part No.	W	F	E	A0	B0
	8.0±0.3	3.5±0.05	1.75±0.1	3.0±0.1	3.5±0.1
KTR25	D0	P0	P1	P2	K
	Ф1.5 ^{+0.1} 0	4.0±0.1	4.0±0.1	2.0±0.05	MAX1.1

Reel dimensions

Using two kinds of reels for taping.





				(Unit : mm)
Part No.	A	В	С	D
KTR03	Ф180 ⁰ -1.5	Ф60 ⁺¹ 0	9 <mark>+1.0</mark> 90	Ф13±0.2
KTR10				
KTR18				
KTR25				



Notice

Precaution on using ROHM Products

 If you intend to use our Products in devices requiring extremely high reliability (such as medical equipment (Note 1), aircraft/spacecraft, nuclear power controllers, etc.) and whose malfunction or failure may cause loss of human life, bodily injury or serious damage to property ("Specific Applications"), please consult with the ROHM sales representative in advance. Unless otherwise agreed in writing by ROHM in advance, ROHM shall not be in any way responsible or liable for any damages, expenses or losses incurred by you or third parties arising from the use of any ROHM's Products for Specific Applications.

JAPAN	USA	EU	CHINA
CLASSII	CLASSⅢ	CLASS II b	CLASSⅢ
CLASSⅣ	CLASSI	CLASSII	

2. ROHM designs and manufactures its Products subject to strict quality control system. However, semiconductor products can fail or malfunction at a certain rate. Please be sure to implement, at your own responsibilities, adequate safety measures including but not limited to fail-safe design against the physical injury, damage to any property, which a failure or malfunction of our Products may cause. The following are examples of safety measures:

[a] Installation of protection circuits or other protective devices to improve system safety

[b] Installation of redundant circuits to reduce the impact of single or multiple circuit failure

- 3. Our Products are not designed under any special or extraordinary environments or conditions, as exemplified below. Accordingly, ROHM shall not be in any way responsible or liable for any damages, expenses or losses arising from the use of any ROHM's Products under any special or extraordinary environments or conditions. If you intend to use our Products under any special or extraordinary environments or conditions (as exemplified below), your independent verification and confirmation of product performance, reliability, etc, prior to use, must be necessary:
 - [a] Use of our Products in any types of liquid, including water, oils, chemicals, and organic solvents
 - [b] Use of our Products outdoors or in places where the Products are exposed to direct sunlight or dust
 - [c] Use of our Products in places where the Products are exposed to sea wind or corrosive gases, including Cl₂, H₂S, NH₃, SO₂, and NO₂
 - [d] Use of our Products in places where the Products are exposed to static electricity or electromagnetic waves
 - [e] Use of our Products in proximity to heat-producing components, plastic cords, or other flammable items
 - [f] Sealing or coating our Products with resin or other coating materials
 - [g] Use of our Products without cleaning residue of flux (Exclude cases where no-clean type fluxes is used. However, recommend sufficiently about the residue.); or Washing our Products by using water or water-soluble cleaning agents for cleaning residue after soldering
 - [h] Use of the Products in places subject to dew condensation
- 4. The Products are not subject to radiation-proof design.
- 5. Please verify and confirm characteristics of the final or mounted products in using the Products.
- 6. In particular, if a transient load (a large amount of load applied in a short period of time, such as pulse, is applied, confirmation of performance characteristics after on-board mounting is strongly recommended. Avoid applying power exceeding normal rated power; exceeding the power rating under steady-state loading condition may negatively affect product performance and reliability.
- 7. De-rate Power Dissipation depending on ambient temperature. When used in sealed area, confirm that it is the use in the range that does not exceed the maximum junction temperature.
- 8. Confirm that operation temperature is within the specified range described in the product specification.
- 9. ROHM shall not be in any way responsible or liable for failure induced under deviant condition from what is defined in this document.

Precaution for Mounting / Circuit board design

- 1. When a highly active halogenous (chlorine, bromine, etc.) flux is used, the residue of flux may negatively affect product performance and reliability.
- 2. In principle, the reflow soldering method must be used on a surface-mount products, the flow soldering method must be used on a through hole mount products. If the flow soldering method is preferred on a surface-mount products, please consult with the ROHM representative in advance.

For details, please refer to ROHM Mounting specification

Precautions Regarding Application Examples and External Circuits

- 1. If change is made to the constant of an external circuit, please allow a sufficient margin considering variations of the characteristics of the Products and external components, including transient characteristics, as well as static characteristics.
- 2. You agree that application notes, reference designs, and associated data and information contained in this document are presented only as guidance for Products use. Therefore, in case you use such information, you are solely responsible for it and you must exercise your own independent verification and judgment in the use of such information contained in this document. ROHM shall not be in any way responsible or liable for any damages, expenses or losses incurred by you or third parties arising from the use of such information.

Precaution for Electrostatic

This Product is electrostatic sensitive product, which may be damaged due to electrostatic discharge. Please take proper caution in your manufacturing process and storage so that voltage exceeding the Products maximum rating will not be applied to Products. Please take special care under dry condition (e.g. Grounding of human body / equipment / solder iron, isolation from charged objects, setting of lonizer, friction prevention and temperature / humidity control).

Precaution for Storage / Transportation

- 1. Product performance and soldered connections may deteriorate if the Products are stored in the places where:
 - [a] the Products are exposed to sea winds or corrosive gases, including Cl₂, H₂S, NH₃, SO₂, and NO₂
 - [b] the temperature or humidity exceeds those recommended by ROHM
 - [c] the Products are exposed to direct sunshine or condensation
 - [d] the Products are exposed to high Electrostatic
- 2. Even under ROHM recommended storage condition, solderability of products out of recommended storage time period may be degraded. It is strongly recommended to confirm solderability before using Products of which storage time is exceeding the recommended storage time period.
- 3. Store / transport cartons in the correct direction, which is indicated on a carton with a symbol. Otherwise bent leads may occur due to excessive stress applied when dropping of a carton.
- 4. Use Products within the specified time after opening a humidity barrier bag. Baking is required before using Products of which storage time is exceeding the recommended storage time period.

Precaution for Product Label

A two-dimensional barcode printed on ROHM Products label is for ROHM's internal use only.

Precaution for Disposition

When disposing Products please dispose them properly using an authorized industry waste company.

Precaution for Foreign Exchange and Foreign Trade act

Since concerned goods might be fallen under listed items of export control prescribed by Foreign exchange and Foreign trade act, please consult with ROHM in case of export.

Precaution Regarding Intellectual Property Rights

- 1. All information and data including but not limited to application example contained in this document is for reference only. ROHM does not warrant that foregoing information or data will not infringe any intellectual property rights or any other rights of any third party regarding such information or data.
- 2. ROHM shall not have any obligations where the claims, actions or demands arising from the combination of the Products with other articles such as components, circuits, systems or external equipment (including software).
- 3. No license, expressly or implied, is granted hereby under any intellectual property rights or other rights of ROHM or any third parties with respect to the Products or the information contained in this document. Provided, however, that ROHM will not assert its intellectual property rights or other rights against you or your customers to the extent necessary to manufacture or sell products containing the Products, subject to the terms and conditions herein.

Other Precaution

- 1. This document may not be reprinted or reproduced, in whole or in part, without prior written consent of ROHM.
- 2. The Products may not be disassembled, converted, modified, reproduced or otherwise changed without prior written consent of ROHM.
- 3. In no event shall you use in any way whatsoever the Products and the related technical information contained in the Products or this document for any military purposes, including but not limited to, the development of mass-destruction weapons.
- 4. The proper names of companies or products described in this document are trademarks or registered trademarks of ROHM, its affiliated companies or third parties.

General Precaution

- 1. Before you use our Products, you are requested to care fully read this document and fully understand its contents. ROHM shall not be in an y way responsible or liable for failure, malfunction or accident arising from the use of a ny ROHM's Products against warning, caution or note contained in this document.
- 2. All information contained in this docume nt is current as of the issuing date and subject to change without any prior notice. Before purchasing or using ROHM's Products, please confirm the latest information with a ROHM sale s representative.
- 3. The information contained in this document is provided on an "as is" basis and ROHM does not warrant that all information contained in this document is accurate an d/or error-free. ROHM shall not be in an y way responsible or liable for any damages, expenses or losses incurred by you or third parties resulting from inaccuracy or errors of or concerning such information.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

ROHM Semiconductor:

KTR10EZPF2204 KTR10EZPF1603 KTR10EZPJ105 KTR10EZPJ151 KTR10EZPJ225 KTR18EZPF7502					
KTR10EZPF5102 KTR10EZPF3001 KTR10EZPF2000 KTR10EZPF68R0 KTR10EZPF8200 KTR18EZPF4702					
KTR18EZPF1203 KTR10EZPF10R0 KTR10EZPF2403 KTR18EZPF5100 KTR10EZPF1304 KTR10EZPF4993					
KTR03EZPF6204 KTR03EZPF6804 KTR03EZPF5604 KTR03EZPF8200 KTR10EZPF1602 KTR10EZPF1R00					
KTR10EZPF33R0 KTR10EZPF3600 KTR03EZPF2004 KTR03EZPF3003 KTR10EZPF1502 KTR10EZPF2703					
KTR03EZPF4702 KTR03EZPF4R30 KTR03EZPF6R80 KTR03EZPF8204 KTR10EZPF1800 KTR03EZPF2400					
KTR03EZPF5R60 KTR10EZPF1500 KTR18EZPF51R0 KTR18EZPF5102 KTR10EZPF15R0 KTR18EZPF4993					
KTR03EZPF4R70 KTR18EZPF8201 KTR18EZPF4992 KTR18EZPF1803 KTR18EZPF2402 KTR03EZPF1803					
KTR18EZPF10R0 KTR18EZPF3002 KTR03EZPF1R80 KTR03EZPF2204 KTR10EZPF75R0 KTR18EZPF3001					
KTR03EZPF2704 KTR03EZPF7504 KTR10EZPF2202 KTR10EZPF4303 KTR03EZPF3301 KTR18EZPF36R0					
KTR10EZPF4991 KTR18EZPF1303 KTR03EZPF8R20 KTR18EZPF2000 KTR03EZPF6R20 KTR18EZPF1000					
KTR18EZPF2203 KTR18EZPF4700 KTR10EZPF1000 KTR03EZPF1000 KTR03EZPF2703 KTR03EZPF2R40					
KTR10EZPF1803 KTR03EZPF3900 KTR03EZPF1R10 KTR03EZPF2203 KTR10EZPF3904 KTR10EZPJ185					
KTR03EZPF4701 KTR03EZPF5R10 KTR03EZPF1004 KTR03EZPF1204 KTR25JZPJ684 KTR25JZPJ105					
KTR25JZPJ104 KTR03EZPF2404 KTR03EZPF1002 KTR03EZPF1R00 KTR03EZPJ103 KTR03EZPJ475					
KTR03EZPF1003 KTR03EZPJ102 KTR03EZPF1103 KTR03EZPF3903 KTR03EZPJ332 KTR03EZPJ334					
KTR03EZPJ471 KTR03EZPF10R0 KTR18EZPJ335 KTR18EZPJ155					