









ROHS



NOTE:
 1. Operating Force: 180gf±50gf
 2. Travel : 2.4±0.3mm



PCB Layout(Pattern Side)



Circuit Diagram

NO.	Operating Type	Part No.	Base Colour	Cover Colour	Knob Colour
1	Push To Lock	K8-8081D-L1	Black	White	Blue
2	Push No Lock	K8-8081D-N1	White	Black	Black
3	Push No Sound No Lock	K8-8081D-NN	White	Black	White

⑧	Terminal	—	6	Brass strip	Plating silver	—
⑦	Contact	—	2	Phosphor bronze	Plating silver	—
⑥	Securing glue	—	2	PA66	Black	—
⑤	Spring	—	1	SUS	Natural	—
④	Base	—	1	PBT	Black	—
③	Crochet Needle	—	1	SUS	Natural	—
②	Cover	—	1	POM	White	—
①	KNOB	—	1	POM	Blue	—

ITEM	PART NAME	TER'NO.	QTY.	MATERIAL	FINISHING	REMARK
------	-----------	---------	------	----------	-----------	--------

APPROVALS		DATE		HRO 華碩 ELECTRONICS CO.,LTD		
DRAWN	J.X.Zhang	2013/10/14		TITLE:	PUSHBUTTON SWITCHS	
CHECKED				PART NO.		
APPROVALS						
TOLERANCES ARE		30~以上	±0.30	ANGLE	UNIT: mm	SCALE: 1:1
		10~30	±0.20			
		5~10	±0.15			
		~ 5	±0.10			
			±2'	DRAWING NO.	SHEET 1 OF 1	

ECN NO.	REV.	DATE.	DESCRIPTION.	CHANGE.	CHECK.	APPRO.
	A		NEW			