



REV.	ECN NO OR DESCRIPTION	REVISED	DATE




**SPECIFICATIONS:**

**1. ELECTRICAL CHARACTERISTICS**



- 1-1. CONTACT RESISTANCE: 80 milliohms MAX.
- 1-2. INSULATION RESISTANCE: 1,000 Megohms MIN.
- 1-3. DIELECTRIC WITHSTANDING VOLTAGE: 500V AC FOR 1 MINUTE.

**2. MECHANICAL CHARACTERISTICS**

- 2-1. RETENTION FORCE: MIN.100gf/PIN
- 2-2. DURABILITY: 3,000 CYCLES
- 3. RoHS 2002/95/EC COMPLIANT.



Pin No.	Pin assignment	Pin No.	Pin assignment
1	DAT2	6	VSS
2	CD/DAT3	7	DAT0
3	CMD	8	DAT1
4	VDD	Cd	
5	CLK	G	



C	SHELL	1	STAINLESS STEEL 0.15t	Ni PLATING
B	CONTACT	8	COPPER ALLOY 0.15t	Gold Flash On Contact Area Tin plated on Solder tail All over Nickel Plated .
A	HOUSING	1	HIGH-TEMPERATURE PLASTIC UL94-V0	BLACK
NO	DESCRIPTION	QTY	MATERIAL	PLATING & COLOR

UNLESS OTHERWISE SPECIFIED TOLERANCES

DECIMALS:	ANGLES:
X :±0.5	X :±2°
X.X :±0.20	X.X :±1°
X.XX :±0.10	



**东莞市汉博电子科技有限公司**  
DONGGUAN HANBO TECHNOLOGY CO., LTD

TITLE					T-FLASH CONN HING TYP 1.8H				
DWN	xiong	PART NO. TF-014-H18							
CHKD	lee	SCALE:1:1	UNIT: mm						
APVD	wang	SIZE: A4	SHEET:10F 1	REV: A4					
CUSTOMER COPY									