

PCB Layout

2- ϕ 0.75 Holes


Circuit diagram



NO.1	
PART NO	H
A	2.0
B	2.5

NO.4-NO.5	
PART NO	NOTE
01~99	SERIAL NUMBER

NO.2	
PART NO	VIGOR
1	90 \pm 30
3	180 \pm 30
4	250 \pm 30





PART NO.

K2-1807UA

NO.3	
PART NO	MATERIAL/QTY
S	SUS/1PC
D	SUS/2PCS

PART NO.

K2-1807UN



⑥	Dust cover	1	KAPTON FILM	Yellow		
⑤	Terminal	2	Phosphor Bronze	Plating silver		
④	Contact	2	F.Ag/SUS			
③	Base	1	Nylon	Black		
②	Cover	1	SUS	Natural		
①	Keystroke	1	Nylon	Black		
ITEM	PART NAME	TER'NO.	QTY.	MATERIAL	FINISHING	REMARK

APPROVALS

DATE

DRAWN xu qi feng

DATE 2014/10/21

CHECKED

TITLE: TACT SWITCHS

APPROVALS

PART NO. K2-1807UD-000W-00

ECN NO.	REV.	DATE.	DESCRIPTION.	CHANGE.	CHECK.	APPRO.
	A		NEW			
TOLERANCES ARE 30~125 \pm ±0.30 ANGLE UNIT: mm SCALE: 1:1 PROJ:						
10~30 ±0.20						
5~10 ±0.15						
~5 ±0.10						
±2' DRAWING NO. SHEET 1 OF 1						



HONGJIAN ELECTRONICS CO., LTD