





ROHS



Terminal No.◎



Circuit Diagram

NOTE:
Contact Resistance: 200 mΩ Max.
Operating Force: 50±10gf
Lifetime: 100,000 Cycles

◎5	Base	—	1	PPA	Black	—
◎4	Terminal	—	2	Phosphor Bronze	Ag Plated	—
◎3	Trestle	—	1	SPCC	Cr Plated	—
◎2	Cover	—	1	POM	Black	—
◎1	Knob	—	1	POM	Black	—
ITEM	PART NAME	TER'NO.	QTY.	MATERIAL	FINISHING	REMARK

APPROVALS			DATE		 ELECTRONICS CO.,LTD		
DRAWN	LIUCAN	2020.12.08		TITLE:			DETECTOR SWITCHS
APPROVALS				PART NO.	K5-1120AA-01		
TOLERANCES ARE			30~以上	±0.30	ANGLE	UNIT: mm SCALE: 1:1 PROJ:	
			10~30	±0.20	DRAWING NO.		
			5~10	±0.15			
			~ 5	±0.10			
ECN NO.	REV.	DATE.	NEW DESCRIPTION.	CHANGE.	CHECK.	APPRO.	SHEET 1 OF 1

ECN NO.	REV.	DATE.	NEW DESCRIPTION.	CHANGE.	CHECK.	APPRO.
---------	------	-------	------------------	---------	--------	--------