



PCB Layout (Pattern Side)



NO.1	
PART NO.	H
A	3.8
B	4.3
C	4.8
D	5
E	5.5
F	6
G	6.5
H	7
I	7.5
J	8
K	8.5
L	9
M	10

NO.2	
PART NO.	vigor
1	90±30
2	130±30
3	180±30
4	250±30
5	350±50

NO.3	
PART NO	MATERIAL/qty
S	SUS/1PC
C	C5210/1PC
D	SUS/2PCS
F	C5210/2PCS

NO.4	
PART NO	L L1
A	7.0 8.0

NO.5-NO.6	
PART NO	NOTE
01~99	SERIAL NUMBER

⑤	Terminal	4	Brass(0.30t)	Plating silver	
④	Contact	1	F.Ag/SUS	Block	
③	Base	1	PA46	Block	
②	Cover	1	SUS		
①	Keystoke	1	PA46	Block	

ITEM	PART NAME	TER'NO.	QTY.	MATERIAL	FINISHING	REMARK
------	-----------	---------	------	----------	-----------	--------

APPROVALS	DATE	ELECTRONICS CO.,LTD				
-----------	------	---------------------	--	--	--	--

DRAWN	J.X.Zhong	2013/6/24	TACT SWITCHS			
CHECKED			TACT SWITCHS			
APPROVALS			TACT SWITCHS			

TOLERANCES ARE	30~11.1	10~30	±0.30	ANGLE	UNIT: mm	SCALE: 1:1	PROJ.
----------------	---------	-------	-------	-------	----------	------------	-------

ECN NO.	REV	DATE	CHANGE.	CHECK.	APPRO.	DRAWING NO.	SHEET 1 OF 1
---------	-----	------	---------	--------	--------	-------------	--------------

ECN NO.	REV	DATE	CHANGE.	CHECK.	APPRO.
	B				
	A				

DESCRIPTION.	NEW
--------------	-----