

## XL-3528SURC

# 技术数据表 Technical Data Sheet

# 3528 红色 贴片式发光二极管

# 特点 (Characteristics):


- \* 外观尺寸 (L/W/H) :3.5\*2.8\*1.9mm Qutline Dimensions (L/w/h): 3.5 x 2.8 x 1.9mm
- \* 发光颜色及胶体: 红色/白色胶体 Luminous color and colloid:Red / white colloid
- \* 环保工艺符合ROHS要求 Environmental protection products Complied With ROHS Directive
- \* EIA规范标准包装 EIA standard packaging
- \* 适用于SMT贴片自动化生产 Suitable for SMT automatic production
- \* 适用于回流焊制程 Suitable for reflow soldering process
- \* 宽角度发光 Wide angle luminescence
- \* 低功率消耗 Low power consumption
- \* 多种颜色可选 Multiple colors available

# 应用领域(Product application):

- \* 医用设备: 内窥镜、血氧仪 Medical equipment: endoscope、oximeter
- \* 汽车电子: 背光按键灯、指示灯 Automotive electronics: backlight key light 、 indicator light
- \* 工业产品: 电子仪表盘、工业设备 Industrial products: electronic instrument panel、industrial equipment
- \* 智能家居: 白色家电、数码管LED Smart home: white appliances, nixie tube LED
- \* 通讯产品: 手机按键灯、路由器、电视盒 Communication products: mobile phone button lamp, router













# 目录

# Catalogue

<b>电性参数</b>	
lectrical Characteristics3	i
<b>基型特性曲线</b>	
ypical Characteristic Curves5	,
「靠性实验	
eliability Test Items And Conditions	5
<b>卜形尺寸</b>	
Outline Dimensions	7
型 <b>装</b>	
ackaging	3
<b>建接指导</b>	
Guideline for Soldering	9
使用注意事项	
recautions	11



电性参数

**Electrical Characteristics** 

# **◇极限参数** (温度=25℃):


Absolute maximum ratings (Temperature=25°C):

参 数	符号	最大额定值	单位
Parameters	Symbol	Maximum rating	Unit
消耗功率			
Consumed power	Pd	60	mW
最大脉冲电流			
(1/10占空比, 0.1ms脉宽)			
Peak Forward current	$ m I_{FP}$	50	mA
(1/10 duty cycle, 0.1ms pulse width)	-11		
正向直流工作电流			
Forward DC working current	$I_{\mathrm{F}}$	40	mA
反向电压		_	
Reverse voltage	$V_R$	7	V
工作环境温度			
Working ambient temperature	Topr	-30°C	~+ 80°C
存储环境温度			
Storage ambient temperature	Tstg	-35°C~+80°C	
		回流焊: 240°C,6s 手动焊: 300°C,3s	
焊接条件		Reflow soldering: 240 ° C, 6S	
Welding conditions	Tsol	manual solderin	g: 300 ° C,3S

# 光电参数(温度=25℃):

Electro-Optical Charasteristics (Temperature=25°C):

参数	符号	最小值	代表值	最大值	单位	测试条件
Parameter	Symbol	Min	Representativevalue	Max	Unit	Test conditions
光强						
Light intensity	IV	300	-	530	mcd	IF=20mA
半光强视角						
Half light angle	201/2	-	120	-	deg	IF=20mA
主波长						
Dominant wavelength	λD	620	-	625	nm	IF=20mA
正向电压						
Forward voltage	VF	1.8	-	2.4	V	IF=20mA
反向电流						
Reverse current	IR	-	-	3	uA	VR=7V





.....

# 亮度分档:

Brightness grading:

代码 Code	最小值 Min	最大值 Max	单位 Unit	测试条件 Test conditions
K25	300	400	1	IE-20m A
K26	400	530	mcd	IF=20mA

# 电压分档:

Voltage grading:

代码 Code	最小值 Min	最大值 Max	单位 Unit	测试条件 Test conditions
I1	1.8	2.0		
I2	2.0	2.2	V	IF=20mA
I3	2.2	2.4		

# 波长分档:


Wavelength grading:


代码	最小值	最大值	单位	测试条件
Code	Min	Max	Unit	Test conditions
R0	620	625	nm	IF=20mA





# 典型特性曲线


# **Typical Characteristics Curves**



















# 可靠性试验

# **Reliability Test Items And Conditions**

测试项目 Test items	测试条件 Testconditions	测试次数 Number of tests	参考标准 Reference standard	失效判定标准 Failure determination standard	失效 LED 数量 Number of failed LEDs Quantity
防潮等级 Moistuproof grade	1. 回流焊最高温度=260℃, 10 秒, 2 次回流焊; 2. 2. 回流焊之前存储条件: 30℃,相对湿度=70%, 168H; 1.Maximum temperature of reflow soldering=260℃, 10 seconds, 2 reflow soldering; 2. Storage conditions before reflow soldering: 30℃, relative humidity=70%, 168h;	-	JEITA ED- 4701 300.301	# 1	0/22
焊接信赖性 (无铅回流焊) Weldingreliability (lead free reflow soldering)	回流焊最高温度=245±5℃, 5 秒(无铅回流焊) Maximum temperature of reflow soldering =245 ± 5 ℃, 5 seconds (lead-freeReflow soldering)	-	JEITA ED-4701 303 303A	# 2	0/22
冷热循环 thermal cycling	-40°C 30分钟(minute)~25°C 5分钟(minute)~ 100°C 30分钟 (mi nute)~25°C 5分钟(minute )	300 个 循环(loop)	JESD22-A104	# 1	0/22
冷热冲击 Thermal Shock	-35℃ 15分钟(minute) 转换时间(Conversion time) 3分钟(minute)85℃ 15分钟(minute)	300 个 循环(loop)	JESD22-A106	# 1	0/22
高温存储 Hightemperature storage	Ta=100°C	1000 小时 (hour)	JESD22-A103	# 1	0/22
低温存储 Lowtemperature storage	Ta=-40°C	1000 小时 (hour)	JESD22-A119	# 1	0/22
常温老化 Normaltempera ture aging	Ta=25°C IF=20mA	1000 小时 (hour)	JESD22-A108	# 1	0/22


失效判断标准 Criteria For Judging Damage

标准	项目	测试条件	失效标准
Standard	Project	Test conditions	Failure criteria
	正向电压 (V <sub>F</sub> ) Forward voltage	$I_F=20mA$	>U.S.L*1.1
# 1	光强(IV) Light intensity	I <sub>F</sub> =20mA	<l.s.l*0.7< td=""></l.s.l*0.7<>
	反向电流(I <sub>R</sub> ) Reverse current	V <sub>R</sub> =5V	>U.S.L*2.0
# 2	焊接可靠性 Welding reliability	-	锡膏覆盖焊盘比例小于 95% The proportion of solder paste covering pad is less than 95%



# 外形尺寸

# **Outline Dimension**



## 备注 (NOTES):

- 1. 所有尺寸单位为毫米
  - All dimensions are in millimeters
- 2. 如有其他备注,尺寸公差为±0.1mm.


Tolerances are ±0.1mm unless otherwise note.



# 包装(1)

Packaging (1)


### 载带与圆盘尺寸 Belt and disk dimensions



注:

- 1. 尺寸单位为毫米(mm)。
- 1. Size unit is mm (mm).
- 2. 尺寸公差是±0.1mm。
- 2. The dimensional tolerance is  $\pm 0.1$ mm.

## ◆ 圆盘及载带卷出方向及空穴规格 Disk and carrier belt direction of roll and hole dimensions







# 包装(2)

Packaging (2)

# ◇ 防潮抗静电包装 Moisture Proof and Anti-Electrostatic Foil Bag



### ◇ 外包装箱 Cardboard Box



Capactiy 5 or 10 reels per box (内箱容量: 50或100卷)

# ◇ 标签说明: Label Explantion

LOT NO: 批次信息

PART NO: 产品型号

BIN CODE: 产品名称

WL: 波长范围

IV: 光强范围

VF: 电压范围





# 焊接指导(1)

## **Guideline for Soldering (1)**

### 1. 使用烙铁人手焊接

#### **Hand Soldering**

推荐使用功率低于 20W 的烙铁,焊接时烙铁的温度必须保持在 300℃以下,且每个电极只能进行一次焊接,每次焊接的持续时间不得超过 3 秒。

人手焊接过程中的不慎操作易引起 LED 产品的损坏,应当小心谨慎。

A soldering iron of less than 20W is recommended to be used in Hand Soldering. Please keep the temperature of the soldering iron under 300°C while soldering. Each terminal of the LED is to go for less than 3 second and for one time only.

Be careful because the damage of the product is often started at the time of the hand soldering.


### 2. 回流焊说明: 推荐使用以下焊接温度图进行。

**Reflow soldering instructions:** It is recommended to use the following welding temperature diagram.


回流次数应少于2次并冷却

Number of reflow process shall be less than 2 times and cooling 在第一次和第二次焊接过程之间,需要进行常温处理

Process to normal temperature is required between first and Second soldering process.



有铅制程



无铅制程



# 焊接指导(2)

# **Guideline for Soldering (2)**

### 3. 清洗:

#### Cleaning

在焊接后推荐使用酒精进行清洗,在温度不高于 30℃的条件下持续 3 分钟, 不高于 50℃的条件下持续 30 秒。使用其他类似溶剂清洗前,请先确认使用的溶剂不会对 LED 的封装和环氧树脂部分造成损伤。

超声波清洗也是有效的方法,一般最大功率不应超过 300W, 否则可能对 LED 造成损伤。请根据具体的情况预先测试清洗条件是否会对 LED 造成损伤。

It is recommended that alcohol be used as a solvent for cleaning after soldering. Cleaning is to go under 30°C for 3 minutes or 50°C for 30 seconds. When using other solvents, it should be confirmed beforehand whether the solvents will dissolve the package and the resin or not.

Ultrasonic cleaning is also an effective way for cleaning. But the influence of Ultrasonic cleaning on LED depends on factors such as ultrasonic power. Generally, the ultrasonic power should not be higher than 300W. Before cleaning, a pretest should be done to confirm whether any damage to LEDs will occur.

- \* **注意:** 此一般指导原则并不适用于所有 PCB 设计和焊接设备的配置。具体工艺受到诸多因素的影响,请根据特定的PCB设计和焊接设备来确定焊接方案。
- \* Note: This general guideline may not apply to all PCB designs and configurations of all soldering equipment.

  The technics in practise is influenced by many factors, it should be specialized base on the PCB designs and configurations of the soldering equipment..



# 使用注意事项(1)

### **Precautions (1)**

### 1. 贮存:

#### **Storage**

• 本产品使用密封防潮抗静电袋包装,并附有干燥剂,未开封的产品有一年的保存时间。

Moisture proof and anti-electrostatic package with moisture absorbent material is used, to keep moisture to a minimum.

- 开封前,产品须存放在温度不高于 30℃,湿度不高于 60%RH 的环境中。
  - Before opening the package, the product should be kept at  $30^{\circ}$ C or less and humidity less than 60% RH, and be used within a year.
- 开封后,产品须存放在温度不高于 30℃,湿度不高于 10%RH 的环境中,且应该在 168 小时(7 天) 内使用完。建议工作环境为温度不高于 30℃,湿度不高于 60%RH。
  - After opening the package, the product should be stored at  $30^{\circ}$ C or less and humidity less than 10%RH, and be soldered within 168 hours (7 days). It is recommended that the product be operated at the workshop condition of  $30^{\circ}$ C or less and humidity less than 60%RH.
- 对于尚未焊接的 LED,如果吸湿剂或包装失效,或者产品没有符合以上有效存储条件,烘焙可以起到一定的性能恢复效果。烘焙条件: 60±5) ℃,持续 24 小时。

If the moisture absorbent material has fade away or the LEDs have exceeded the storage time, baking treatment should be performed based on the following condition:  $(60\pm5)^{\circ}$ C for 24 hours.

#### 2. 静电:

#### Static Electricity

静电和电涌会导致产品特性发生改变,例如正向电压降低等,如果情况严重甚至会损毁产品。所以在使用时必须采取有效的防静电措施。

所有相关的设备和机器都应该正确接地,同时必须采取其他防止静电和电涌的措施。

使用防静电手环,防静电垫子,防静电工作服、工作鞋、手套,防静电容器,都是有效的防止静电和电涌的措施。

Static electricity or surge voltage damages the LEDs. Damaged LEDs will show some unusual characteristic such as the forward voltage becomes lower, or the LEDs do not light at the low current. even not light.

All devices, equipment and machinery must be properly grounded. At the same time, it is recommended that wrist bands or anti-electrostatic gloves, anti-electrostatic containers be used when dealing with the LEDs.



# 使用注意事项(2)

## **Precautions (2)**

### 3. 设计建议:


#### **Design Consideration**

设计电路时,通过 LED 的电流不能超过规定的最大值,同时,还需使用保护电阻,否则,微小的电压变 化将会引起较大的电流变化,可能导致产品损毁。

建议使用以下(A)电路,该电路能够很好的调节通过每个 LED 的电流; 不推荐使用(B)电路,该电路 在持续的电压驱动下,LED 的正向电压( $V_F$ )发生变化,电流会随之而发生变化,可能使某些 LED 承受高于规定的电流值。

In designing a circuit, the current through each LED must not exceed the absolute maximum rating specified for each LED. In the meanwhile, resistors for protection should be applied, otherwise slight voltage shift will cause big current change, burn out may happen.

It is recommended to use Circuit A which regulates the current flowing through each LED rather than Circuit B. When driving LEDs with a constant voltage in Circuit B, the current through the LEDs may vary due to the variation in Forward Voltage (V<sub>F</sub>) of the LEDs. In the worst case, some LED may be subjected to stresses in excess of the Absolute Maximum Rating.



LED 的特性容易因为自身的发热和环境的温度的改变而发生改变。温度的升高会降低 LED 的发光效率、 影响发光颜色等,所以在设计时应充分考虑散热的问题。

Thermal Design is paramount importance because heat generation may result in the Characteristics decline, such as brightness decreased, Color changed and so on. Please consider the heat generation of the LEDs when making the system design.



# 使用注意事项(3)


# **Precautions (3)**

### 4. 其他事项:

#### **Others**

直接用手拿取产品不但会污染封装树脂表面,也可能由于静电等因素导致产品性能的改变。过度的压力也可能直接影响封装内部的管芯和金线,因此请勿对产品施加过度压力,特别当产品处于高温状态下,例如在回流焊接过程中。

When handling the product, touching the encapsulant with bare hands will not only contaminate its surface, but also affect on its optical characteristics. Excessive force to the encapsulant might result in catastrophic failure of the LEDs due to die breakage or wire deformation. For this reason, please do not put excessive stress on LEDs, especially when the LEDs are heated such as during Reflow Soldering.



LED 的环氧树脂封装部分相当脆弱,请勿用坚硬、尖锐的物体刮、擦封装树脂部分。在用镊子夹取的时候也应当小心注意。

The epoxy resin of encapsulant is fragile, so please avoid scratch or friction over the epoxy resin surface. While handling the product with tweezers, do not hold by the epoxy resin, be careful.

不可用在PH<7的酸性场所。 Not suitable to operate in acidic envi-ronment.

### 5. 眼睛保护忠告:

### Safety Advice For Human Eyes

LED 发光时,请勿直视发光光源,特别是对于一些光强较高的 LED,强光可能伤害你的眼睛。

Viewing direct to the light emitting center of the LEDs, especially those of great Luminous Intensity, will cause great hazard to human eyes. Please be careful.