

PARA LIGHT ELECTRONICS CO., LTD. 4F, No.1, Lane 93, Chien Yi Road, Chung Ho City, Taipei, Taiwan.

4F, No.1, Lane 93, Chien Yi Road, Chung Ho City, Taipei, TaTel: 886-2-2225-3733Fax: 886-2-2225-4800E-mail: para@para.com.twhttp://www.para.com.tw

DATA SHEET

PART NO. : L-H31F204

REV: <u>A/1</u>

CUSTOMER'S APPROVAL :

DCC :

DRAWING NO. : DS-60-10-0092

DATE : 2010-12-03





L-H31F204

REV:A/1

PACKAGE DIMENSIONS

Color Description





Note:

1.All Dimensions are in millimeters.

6,35

2.6±0.5

0,50

5,08

- 2.Tolerance is ±0.25mm(0.010 ") Unless otherwise specified.
- 3.Protruded resin under flange is 1.5mm(0.059 ") max.
- 4.Lead spacing is measured where the leads emerge from the package.
- 5.Specification are subject to change without notice
- 6.A=L-359IGW-CA

DRAWING NO. : DS-60-10-0092

DATE : 2010-12-03

PA	RA
īg	ht

L-H31F204

REV:A/1

FEATURES

- * 3.0mm DIA LED LAMP
- * LOW POWER CONSUMPTION.
- * I.C. COMPATIBLE.
- * LONG LIFE SOLID STATE RELIABILITY.
- * PB FREE PRODUCTS(Compliant with EU's RoHS.)

CHIP MATERIALS


- * Dice Material : GaAlAs/GaAs & GaP/GaP
- * Light Color : Super Red & Super Green
- * Lens Color : White Diffused

ABSOLUTE MAXIMUM RATING : (Ta = 25° C)

SYMBOL	PARAME	Sup	erRed	SuperGreen		UNIT			
PAD	Power Dissipation	69 78		3	mW				
VR	Reverse Voltage			5		5		V	
lF	Average Forward Current				30 30		C	mA	
IPF	Peak Forward Current Per	Chip (Duty=0	0.1,1KHz)		120 120		0	mA	
	Derating Linear From 25 $^\circ$ (2			0.4	0.4		mA/°C	
Topr	Operating Temperature Rar		-25° C to 85° C						
Tstg	tg Storage Temperature Range					0°Cto	o 85°	С	
ELECTRO-OPTICAL CHARACTERISTICS : (Ta = 25° C)									
SYMBOL	DESCRIPTION	TEST C	ONDITION		MIN.	TYP.	MAX	ζ.	UNIT
Vf	Forward Voltage	IF=20mA	Super Re	ed		2.0	2.4	,	V
			SuperGre	en	2.1	2.6			
IR	Reverse Current	VR=5 V	Super Re	per Red			100)	μA
			SuperGre	en			100)	μ.
λd	Dominant Wavelength	IF=20mA	Super Red			643			nm
			SuperGre	en		570			
Δλ	Spectral Line Half-Width IF=20	IF=20mA	Super Red			20			nm
	,	SuperG		en		20			
2 <i>θ</i> 1/2	Half Intensity Angle	IF=20mA	R/G			120			deg
hy.	Luminous Intensity	IF=20mA	Super Red			30			mcd
lv			SuperGre			20	1		

DRAWING NO. : DS-60-10-0092

DATE : 2010-12-03



PARA ight

3.0 mm LED LAMP WITH LHY3301-10 HOLDER

L-H31F204

REV:A/1

Label Explanation

PAR.	RA ht A N		A LI	-			限公 ICS CO.,	
LOT		0. :					INSPE	CTED
BIN			•					
Q'	T	Y	•		PC	S		
N. V	V		•		Ę	y S		
PARA NO. : Refer to p13								
LOT	NO.	: L	L	Μ	7	В	001	
		А	В	С	D	Е	F	
BL	lonth PEC	⊃ ⊦ serie	I:HC	DLDE				

DRAWING NO. : DS-60-10-0092

DATE : 2010-12-03


PA	RA
īg	ht

L-H31F204


REV:A/1

-SOLDERING

SOLDERING CONDITIONS	REMARK
Bath temperature: 250° C Immersion time: with 5 sec, 1 time	 Solder no closer than 3mm from the base of the package Using soldering flux," RESIN FLUX" is recommended. Attached data of temperatuare cure for your reference
Soldering iron: 30W or smaller Temperature at tip of iron: 300℃ or lower Soldering time: within 3 sec.	 During soldering, take care not to press the tip of iron against the lead. (To prevent heat from being transferHi.effi Red directly to the lead, hold the lead with a pair of tweezers while soldering
•	package is fixed with a panel (See Fig.1)
	Bath temperature: 250℃ Immersion time: with 5 sec, 1 time Soldering iron: 30W or smaller Temperature at tip of iron: 300℃ or lower Soldering time: within 3 sec.




2) When soldering wire to the lead, work with a Fig (See Fig.2) to avoid stressing the package.



Regarding solution in the tinning oven for product-tinning, compound sub-solution made of tin & copper and sliver is proposed with the temperature of Celsius 260. The proportion of the alloyed solution is tin 95.5: copper 3.5: silver 0.5 by percentage. The time of tinning is constantly 3 seconds.

DRAWING NO. : DS-60-10-0092

DATE : 2010-12-03



- 4) Repositioning after soldering should be avoided as much as possible. If inevitable, be sure to preserve the soldering conditions with irons stated above: select a best-suited method that assures the least stress to the LED.
- 5) Lead cutting after soldering should be performed only after the LED temperature has returned to normal temperature.

– STORAGE

- 1) The LEDs should be stoHi.effi Red at 30° C or less and 70% RH or less after being shipped from PARA and the storage life limits are 3 months .
- 2) PARA LED lead frames are comprised of a stannum plated iron alloy. The silver surface may be affected by environments which contain corrosive gases and so on. Please avoid conditions which may cause the LEDs to corrode, tarnish or discolor. This corrosion or discoloration may cause difficulty during soldering operations. It is recommended that the LEDs be used as soon as possible.

Please avoid rapid transitions in ambient temperature, especially, in high humidity environments where condensation can occur.




L-H31F204

REV:A/1

-LED MOUNTING METHOD

3) When mounting the LED by using a case, as shown Fig.4, ensure that the mounting holds on the PC board match the pitch of the leads correctly-tolerance of dimensions of the respective components including the LED should be taken into account especially when designing the case, PC board, etc. to prevent pitch misalignment between the leads and board holes, the diameter of the board holes should be slightly larger than the size of the lead. Alternatively, the shape of the holes should be made oval. (See Fig.4)



4) Use LEDs with stand-off (Fig.5) or the tube or spacer made of resin (Fig.6) to position the LEDs.





Fig.5



DRAWING NO. : DS-60-10-0092

DATE : 2010-12-03

LED HOLDER 3.0 mm LHY3301-10 LAMP WITH L-H31F204 REV:A/1 FORMED LEAD 1) The lead should be bent at a point located at least 2mm away from the package. Bending should be performed with base fixed means of a jig or pliers (Fig.7) Fig.7 2) Forming lead should be carried our prior to soldering and never during or after soldering. 3) Form the lead to ensure alignment between the leads and the hole on board, so that stress against the LED is prevented. (Fig.8) tress Fig.8 -LEAD STRENGTH 1) Bend strength Do not bend the lead more than twice. (Fig.9) Fig.9 DRAWING NO. : DS-60-10-0092 DATE : 2010-12-03 Page:9

PARA ight

3.0 mm LED LAMP WITH LHY3301-10 HOLDER

L-H31F204

REV:A/1

Tensile strength (@Room Temperature)
 If the force is 1kg or less, there will be no problem. (Fig.10)

ok!

-HEAT GENERATION

 Thermal design of the end product is of paramount importance. Please consider the heat generation of the LED when making the system design. The coefficient of temperature increase per input electric power is affected by the thermal resistance of the circuit board and density of LED placement on the board, as well as other components. It is necessary to avoid intense heat generation and operate within the maximum ratings given in this specification.

The operating current should be decided after considering the ambient maximum temperature of LEDs.

-CHEMICAL RESISTANCE

- 1) Avoid exposure to chemicals as it may attack the LED surface and cause discoloration.
- When washing is requiHi.effi Red, refer to the following table for the proper chemical to be sued. (Immersion time: within 3 minutes at room temperature.)

SOLVENT	ADAPTABILITY				
Freon TE	\odot				
Chlorothene	\times				
Isopropyl Alcohol	\odot				
Thinner	\times				
Acetone	×				
Trichloroethylene	×				
\odot Licoble \checkmark Do not use					

NOTE: Influences of ultrasonic cleaning of the LED resin body differ depending on such factors as the oscillator output, size of the PC board and the way in which the LED is mounted. Therefore, ultrasonic cleaning should only be performed after confirming there is no problem by conducting a test under practical.

 \odot --Usable X--Do not use.

DRAWING NO. : DS-60-10-0092

DATE : 2010-12-03



L-H31F204

REV:A/1

-OTHERS

- 1) Care must be taken to ensure that the reverse voltage will not exceed the absolute maximum rating when using the LEDs with matrix drive.
- Flashing lights have been known to cause discomfort in people; you can prevent this by taking precautions during use. Also, people should be cautious when using equipment that has had LEDs incorporated into it.
- 3) The LEDs described in this brochure are intended to be used for ordinary electronic equipment (such as office equipment, communications equipment, measurement instruments and household appliances). Consult PARA's sales staff in advance for information on the applications in which exceptional quality and reliability are requiHi.effi Red , particularly when the failure or malfunction of the LEDs may directly jeopardize life or health (such as for airplanes, aerospace, submersible repeaters, nuclear reactor control systems, automobiles, traffic control equipment, life support systems and safety devices).
- 4) User shall not reverse engineer by disassembling or analysis of the LEDs without having prior written consent from PARA. When defective LEDs are found, the User shall inform PARA directly before disassembling or analysis.
- 5) The formal specifications must be exchanged and signed by both parties before large volume purchase begins.
- 6) The appearance and specifications of the product may be modified for improvement without notice.

