

# 深圳市晶友嘉电子有限公司



### SHENZHEN JINGYOUJIA ELECTRONIC CO., LTD

### CRYSTAL RESONATOR SPECIFICATIONS

# 声表面波谐振器承认书

客户 Customer:	立创商城		
型号 Product:	SB73		
客户料号 Code No:			
我司料号 Code No:	SB3931500TT		
频率 Frequency:	315.000MHz		
数量 Sample Quantity:			
日期 Date:	2021-7-15		

# 深圳市晶友嘉电子有限公司

SHENZHEN JINGYOUJIA ELECTRONIC CO., LTD 深圳市龙华区东环二路数字智能颖博园 B 栋 412

TEL: 86-755-32840201 32850080

FAX: 86-755-84269460

### 供应商确认栏:

制作 Handler	确认 Checked	核审 Approved
戴晓嘉	李晨	陈斌


### 客户承认栏:

承认 Checked	核审 Approved

### 1. Package Dimension

Unit: mm






Pin	Connection		
1	Input		
2	Case Ground		
3	Output		

## 2. Marking

**R433** 

## 3. Equivalent LC Model



#### 4. Performance

### 4.1 Maximum Rating

ltem:	Value
DC Voltage V <sub>DC</sub>	12V
Operation Temperature Range	-40℃ to +85℃
Storage Temperature Range	-40℃ to +85℃
RF Power Dissipation	0dBm


### 4.2 Electronic Characteristics

Item	Unit	Minimum	Typical	Maximum
Center Frequency (f <sub>c</sub> )	MHz	314.925	315.000	315.075
Insertion Loss	dB	_	1.8	2.2
Quality Factor				
Unloaded Q	_	_	13173	_
50Ω Loaded Q	_	_	2167	_
Temperature Stability				
Turnover Temperature (T <sub>0</sub> )	$^{\circ}$ C	25	-	55
Turnover Frequency (f <sub>0</sub> )	MHz		fc	
Frequency Temperature Coefficient (FTC)	ppm/°C²		0.032	_
Frequency Aging	ppm/yr	_	<±10	
DC Insulation Resistance	ΜΩ	1.0	_	_
RF Equivalent RLC Model				
Motional Resistance R₁	Ω	_	20	29
Motional Inductance L₁	μH	_	95.2	_
Motional Capacitance C₁	fF	_	1.7241	_
Shunt Static Capacitance C <sub>0</sub>	pF	1.90	2.15	2.40

#### Notes:

- a. Unless noted otherwise, case temperature T<sub>C</sub> = +25°C±2°C.
- b. The center frequency,  $f_C$ , is measured at the minimum insertion loss point with the resonator in the  $50\Omega$  test system.
- c. Frequency aging is the change in f<sub>C</sub> with time and is specified at +65°C or less. Aging may exceed the specification for prolonged temperatures above +65°C. Typically, aging is greatest the first year after manufacture, decreasing in subsequent years.
- d. Turnover temperature,  $T_0$ , is the temperature of maximum (or turnover) frequency,  $f_0$ . The nominal frequency at any case temperature,  $T_c$ , may be calculated from:  $f = f_0 [1 FTC (T_0 T_c)^2]$ .
- e. This equivalent RLC model approximates resonator performance near the resonant frequency and is provided for reference only. The capacitance C<sub>0</sub> is the static capacitance between Pin 1 and Pin 2 measured at low frequency (10MHz) with a capacitance meter. The measurement includes case parasitic capacitance.

### 4.3 Temperature Characteristics



#### 5. Remarks

- 5.1 SAW devices should not be used in any type of fluid such as water, oil, organic solvent, etc.
- 5.2 Be certain not to apply voltage exceeding the rated voltage of components.
- 5.3 Do not operate outside the recommended operating temperature range of components.
- 5.4 Sudden change of temperature shall be avoided, deterioration of the characteristics can occur.
- 5.5 Be careful of soldering temperature and duration of components when soldering.
- 5.6 Do not place soldering iron on the body of components.
- 5.7 Be careful not to subject the terminals or leads of components to excessive force.
- 5.8 SAW devices are electrostatic sensitive. Please avoid static voltage during operation and storage.
- 5.9 Ultrasonic cleaning shall be avoided. Ultrasonic vibration may cause destruction of components.