





ROHS

SPECIFICATIONS

Rated Current:3.0AMP
 Contact Resistance:20mΩ Max
 Withstand Voltage:1000V AC/DC
 Insulation Resistance:1000MΩ Min
 Operation Temperature:-40°c to +105°c
 Contact Material:Brass
 Contact Plating:Au Over Ni
 Insulator Material:Polyester(UL94V-0)
 Standard: PA6T
 Max.Processing Temp: 230°C for 30-60 seconds
 (260°C for 10 seconds)



Dimension antitheses list					
ITEM	PA	PB	PC	L	
Standard	5.70	31.7	3.30	40.70	
Alternate					

深圳市连盛精密连接器有限公司

PART NO. PH-01277

TITLE: 2.54PH 2H=2X2.5 鍍金反向四槽向內 2*10P DIP PA5.7 PB31.7 PC3.3 L=40.7 AU1U PA6T

OPERATION		DRAW		SCALE		FIT	
X.X	±0.30			UNIT	mm		
X.XX	±0.20	CHECK		SIZE	A4		
X.XXX	±0.10			SHEET	1/1		
Angle	±3°	APPROVE		PROJ.			
DIM	TOL						

REV	DATE	MODIFICATION DESCRIPTION	CHANGE
A0	2021.03.28	NEW DRAWING	
1			