Wide Input Voltage Low Dropout, Ultra-Low Iq Regulator

The NCP716B is 150 mA LDO Linear Voltage Regulator. It is a very stable and accurate device with ultra–low ground current consumption (4.7 μ A over the full output load range) and a wide input voltage range (up to 24 V). The regulator incorporates several protection features such as Thermal Shutdown and Current Limiting.

Features

- Operating Input Voltage Range: 2.5 V to 24 V
- Fixed Voltage Options Available: 3.0 V, 3.3 V and 5.0 V
- Ultra Low Quiescent Current: Max. 4.7 µA over Temperature
- ±2% Accuracy over Full Temperature Range
- Noise: 115 μ V_{RMS} from 200 Hz to 100 kHz
- Thermal Shutdown and Current Limit Protection
- Available in TSOP-5 Package
- This is a Pb-Free Device

Typical Applicaitons

- Portable Equipment
- Communication Systems
- Industrial Measurement Systems
- Home Automation Devices





Figure 1. Typical Application Schematic



ON Semiconductor®

www.onsemi.com



XXX = Specific Device Code

A = Assembly Location


Y = Year

N = Work Week

= Pb–Free Package

(Note: Microdot may be in either location)

PIN CONNECTIONS



ORDERING INFORMATION

See detailed ordering, marking and shipping information in the package dimensions section on page 7 of this data sheet.




Figure 2. Simplified Block Diagram

Table 1. PIN FUNCTION DESCRIPTION

Pin No.	Pin Name	Description
1	OUT	Regulated output voltage pin. A small 1.0 μF ceramic capacitor is needed from this pin to ground to assure stability.
2	GND	Power supply ground.
3	IN	Input pin. A small capacitor is needed from this pin to ground to assure stability.
4	N/C	No connection. This pin can be tied to ground to improve thermal dissipation or left disconnected.
5	N/C	No connection. This pin can be tied to ground to improve thermal dissipation or left disconnected.

Table 2. ABSOLUTE MAXIMUM RATINGS

Rating	Symbol	Value	Unit
Input Voltage (Note 1)	V _{IN}	-0.3 to 24	V
Output Voltage	V _{OUT}	-0.3 to 6	V
Output Short Circuit Duration	t _{SC}	Indefinite	s
Maximum Junction Temperature	T _{J(MAX)}	150	°C
Storage Temperature	T _{STG}	-55 to 150	°C
ESD Capability, Human Body Model (Note 2)	ESD _{HBM}	2000	V
ESD Capability, Machine Model (Note 2)	ESD _{MM}	200	V

Stresses exceeding those listed in the Maximum Ratings table may damage the device. If any of these limits are exceeded, device functionality should not be assumed, damage may occur and reliability may be affected.

1. Refer to ELECTRICAL CHARACTERISTICS and APPLICATION INFORMATION for Safe Operating Area.

2. This device series incorporates ESD protection and is tested by the following methods:

- - - ESD Human Body Model tested per EIA/JESD22-A114
 - ESD Machine Model tested per EIA/JESD22-A115
 - ESD Charged Device Model tested per EIA/JESD22-C101E
 - Latchup Current Maximum Rating tested per JEDEC standard: JESD78.

Table 3. THERMAL CHARACTERISTICS

Rating	Symbol	Value	Unit
Thermal Characteristics, TSOP–5 Thermal Resistance, Junction–to–Air	$R_{\theta JA}$	250	°C/W

Table 4. ELECTRICAL CHARACTERISTICS Voltage version 3.0 V

 -40° C \leq T_J \leq 125 $^{\circ}$ C; V_{IN} = 4.0 V; I_{OUT} = 1 mA, C_{IN} = C_{OUT} = 1.0 μ F, unless otherwise noted. Typical values are at T_J = +25 $^{\circ}$ C. (Note 5)

Parameter	Test Conditions		Symbol	Min	Тур	Max	Unit
Operating Input Voltage			V _{IN}	2.5		24	V
Output Voltage Accuracy	-40°C ≤ T _J ≤ 125°	°C	V _{OUT}	2.94	3.0	3.06	V
Line Regulation	V _{OUT} + 1 V ≤ V _{IN} ≤ 24 V, I _O	_{UT} = 0.1 mA	Reg _{LINE}		4	10	mV
Load Regulation	I _{OUT} = 0.1 mA to 150) mA	Reg _{LOAD}		0.0013	0.007	%/mA
Dropout Voltage (Note 3)	V _{OUT} = 0.97 V _{OUT(NOM)} , I _{OUT} = 150 mA		V_{DO}		700	1100	mV
Maximum Output Current	(Note 6)		I _{OUT}	150			mA
Ground Current	$I_{OUT} = 0 \text{ mA}, -40 < T_A < 125^{\circ}\text{C}$		I _{GND}		3.2	4.7	μΑ
Power Supply Rejection Ratio	$\begin{aligned} &V_{\text{IN}} = 4.0 \text{ V}, V_{\text{OUT}} = 3.0 \text{ V} + \\ &200 \text{ mVpp modulation} \\ &I_{\text{OUT}} = 1 \text{ mA}, C_{\text{OUT}} = 10 \mu\text{F} \end{aligned}$		PSRR		55		dB
Output Noise Voltage	V _{OUT} = 3.0 V, I _{OUT} = 150 mA f = 100 Hz to 100 kHz		V _N		80		μV_{rms}
Thermal Shutdown Temperature (Note 4)	Temperature increasing from T _J = +25°C		T _{SD}		180		°C
Thermal Shutdown Hysteresis (Note 4)	Temperature falling fro	m T _{SD}	T _{SDH}	-	10	_	°C

- 3. Characterized when V_{OUT} falls 3% below the nominal V_{OUT} = 3.0 V
- 4. Guaranteed by design and characterization.
- 5. Performance guaranteed over the indicated operating temperature range by design and/or characterization production tested at T_J = T_A = 25°C. Low duty cycle pulse techniques are used during testing to maintain the junction temperature as close to ambient as possible.
- 6. Please follow the Safe Operating Area.

Table 5. ELECTRICAL CHARACTERISTICS Voltage version 5.0 V

 -40° C \leq T_J \leq 125 $^{\circ}$ C; V_{IN} = 6.0 V; I_{OUT} = 1 mA, C_{IN} = C_{OUT} = 1.0 μ F, unless otherwise noted. Typical values are at T_J = +25 $^{\circ}$ C. (Note 9)

Parameter	Test Conditions		Symbol	Min	Тур	Max	Unit
Operating Input Voltage			V _{IN}	2.5		24	V
Output Voltage Accuracy	-40 °C \leq T _J \leq 125°C		V _{OUT}	4.90	5.0	5.10	V
Line Regulation	V _{OUT} + 1 V ≤ V _{IN} ≤ 24 V, I _O	_{UT} = 0.1 mA	Reg _{LINE}		4	10	mV
Load Regulation	I _{OUT} = 0.1 mA to 150	O mA	Reg _{LOAD}		0.0013	0.008	%/mA
Dropout Voltage (Note 7)	V _{OUT} = 0.97 V _{OUT(NOM)} , I _{OUT} = 150 mA		V_{DO}		600	955	mV
Maximum Output Current	(Note 10)		I _{OUT}	150			mA
Ground Current	I _{OUT} = 0 mA, -40 < T _A < 125°C		I _{GND}		3.2	4.7	μΑ
Power Supply Rejection Ratio	$ \begin{array}{c c} V_{IN} = 6.0 \text{ V}, V_{OUT} = 5.0 \text{ V} + \\ 200 \text{ mVpp modulation} \\ I_{OUT} = 1 \text{ mA}, C_{OUT} = 10 \mu\text{F} \end{array} $		PSRR		53		dB
Output Noise Voltage	V _{OUT} = 5.0 V, I _{OUT} = 150 mA f = 100 Hz to 100 kHz		V _N		115		μV_{rms}
Thermal Shutdown Temperature (Note 8)	Temperature increasing from T _J = +25°C		T _{SD}		180		°C
Thermal Shutdown Hysteresis (Note 8)	Temperature falling from T _{SD}		T _{SDH}	-	10	-	°C

- 7. Characterized when V_{OUT} falls 3% below the nominal V_{OUT} = 5.0 V
- 8. Guaranteed by design and characterization.
- Statistics by design and shared-controlled in the indicated operating temperature range by design and/or characterization production tested at T_J = T_A = 25°C. Low duty cycle pulse techniques are used during testing to maintain the junction temperature as close to ambient as possible.
- 10. Please follow the Safe Operating Area.

TYPICAL CHARACTERISTICS




Figure 3. Output Voltage vs. Temperature

Figure 4. Output Voltage vs. Temperature




Figure 5. Output Voltage vs. Output Current

Figure 6. Output Voltage vs. Output Current




Figure 7. Dropout Voltage vs. Output Current

Figure 8. Dropout Voltage vs. Output Current

TYPICAL CHARACTERISTICS




Figure 9. Ground Current vs. Input Voltage




Figure 10. Ground Current vs. Input Voltage




Figure 11. Spectral Noise Density vs. Frequency




Figure 12. Spectral Noise Density vs. Frequency




Figure 13. PSRR vs. Frequency





Figure 14. PSRR vs. Frequency

TYPICAL CHARACTERISTICS



NCP716BSN500T1G
Cin = Cout = 1 uF
Vin = step from 8 V to 7V
Iout = 150 mA
Ta = 25 °C
Imput Voltage

Cutput Voltage

Solar 256bs Alleger

(In policy Collection Collec

Figure 15. Line Transient Response

Figure 16. Line Transient Response







Figure 17. Load Transient Response

Figure 18. Load Transient Response






Figure 19. Turn-On Response

Figure 20. Turn-On Response

APPLICATIONS INFORMATION

The NCP716B is the member of new family of Wide Input Voltage Range Low Dropout Regulators which delivers Ultra Low Ground Current consumption, Good Noise and Power Supply Rejection Ratio Performance.

Input Decoupling (C_{IN})

It is recommended to connect at least $1.0\,\mu F$ Ceramic X5R or X7R capacitor between IN and GND pin of the device. This capacitor will provide a low impedance path for any unwanted AC signals or Noise superimposed onto constant Input Voltage. The good input capacitor will limit the influence of input trace inductances and source resistance during sudden load current changes.

Higher capacitance and lower ESR Capacitors will improve the overall line transient response.

Output Decoupling (COUT)

The NCP716B does not require a minimum Equivalent Series Resistance (ESR) for the output capacitor. The device is designed to be stable with standard ceramics capacitors with values of 1.0 μF or greater up to 10 μF . The X5R and X7R types have the lowest capacitance variations over temperature thus they are recommended.

Power Dissipation and Heat sinking

The maximum power dissipation supported by the device is dependent upon board design and layout. Mounting pad configuration on the PCB, the board material, and the ambient temperature affect the rate of junction temperature rise for the part. The maximum power dissipation the NCP716B can handle is given by:

$$P_{D(MAX)} = \frac{\left[T_{J(MAX)} - T_{A}\right]}{R_{\theta JA}}$$
 (eq. 1)

The power dissipated by the NCP716B for given application conditions can be calculated from the following equations:

$$P_D \approx V_{IN} (I_{GND}(I_{OUT})) + I_{OUT} (V_{IN} - V_{OUT})$$
 (eq. 2)

or

$$V_{IN(MAX)} \approx \frac{P_{D(MAX)} + (V_{OUT} \times I_{OUT})}{I_{OUT} + I_{GND}}$$
 (eq. 3)

For reliable operation, junction temperature should be limited to +125°C maximum.

Hints

VIN and GND printed circuit board traces should be as wide as possible. When the impedance of these traces is high, there is a chance to pick up noise or cause the regulator to malfunction. Place external components, especially the output capacitor, as close as possible to the NCP716B, and make traces as short as possible.

ORDERING INFORMATION


Device	Voltage Option	Marking	Package	Shipping [†]
NCP716BSN300T1G	3.0 V	6AA	TSOP-5 (Pb-Free)	3000 / Tape & Reel
NCP716BSN330T1G	3.3 V	6AC	TSOP-5 (Pb-Free)	3000 / Tape & Reel
NCP716BSN500T1G	5.0 V	6AV	TSOP-5 (Pb-Free)	3000 / Tape & Reel


[†]For information on tape and reel specifications, including part orientation and tape sizes, please refer to our Tape and Reel Packaging Specifications Brochure, BRD8011/D.




TSOP-5 **CASE 483 ISSUE N**

DATE 12 AUG 2020










NOTES:

- DIMENSIONING AND TOLERANCING PER ASME
- CONTROLLING DIMENSION: MILLIMETERS.
 MAXIMUM LEAD THICKNESS INCLUDES LEAD FINISH
 THICKNESS. MINIMUM LEAD THICKNESS IS THE
 MINIMUM THICKNESS OF BASE MATERIAL.
- DIMENSIONS A AND B DO NOT INCLUDE MOLD FLASH, PROTRUSIONS, OR GATE BURRS. MOLD FLASH, PROTRUSIONS, OR GATE BURRS SHALL NOT EXCEED 0.15 PER SIDE. DIMENSION A. OPTIONAL CONSTRUCTION: AN ADDITIONAL
- TRIMMED LEAD IS ALLOWED IN THIS LOCATION. TRIMMED LEAD NOT TO EXTEND MORE THAN 0.2 FROM BODY.

	MILLIMETERS			
DIM	MIN MAX			
Α	2.85	3.15		
В	1.35	1.65		
C	0.90	1.10		
D	0.25	0.50		
G	0.95	BSC		
Н	0.01	0.10		
J	0.10	0.26		
K	0.20	0.60		
М	0 °	10 °		
S	2.50	3.00		

SOLDERING FOOTPRINT*



^{*}For additional information on our Pb-Free strategy and soldering details, please download the ON Semiconductor Soldering and Mounting Techniques Reference Manual, SOLDERRM/D.

GENERIC MARKING DIAGRAM*





XXX = Specific Device Code XXX = Specific Device Code

= Assembly Location = Date Code = Year = Pb-Free Package

= Work Week W = Pb-Free Package

(Note: Microdot may be in either location)

*This information is generic. Please refer to device data sheet for actual part marking. Pb-Free indicator, "G" or microdot " ■", may or may not be present.

DOCUMENT NUMBER:	98ARB18753C	8ARB18753C Electronic versions are uncontrolled except when accessed directly from the Document Repose Printed versions are uncontrolled except when stamped "CONTROLLED COPY" in red.			
DESCRIPTION:	TSOP-5		PAGE 1 OF 1		

ON Semiconductor and unare trademarks of Semiconductor Components Industries, LLC dba ON Semiconductor or its subsidiaries in the United States and/or other countries. ON Semiconductor reserves the right to make changes without further notice to any products herein. ON Semiconductor makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does ON Semiconductor assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. ON Semiconductor does not convey any license under its patent rights nor the rights of others.

ON Semiconductor and the are trademarks of Semiconductor Components Industries, LLC dba ON Semiconductor or its subsidiaries in the United States and/or other countries. ON Semiconductor owns the rights to a number of patents, trademarks, copyrights, trade secrets, and other intellectual property. A listing of ON Semiconductor's product/patent coverage may be accessed at www.onsemi.com/site/pdf/Patent-Marking.pdf. ON Semiconductor reserves the right to make changes without further notice to any products herein. ON Semiconductor and see no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does ON Semiconductor assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. Buyer is responsible for its products and applications using ON Semiconductor products, including compliance with all laws, regulations and safety requirements or standards, regardless of any support or applications information provided by ON Semiconductor. "Typical" parameters which may be provided in ON Semiconductor data sheets and/or specifications can and do vary in different applications and actual performance may vary over time. All operating parameters, including "Typicals" must be validated for each customer application by customer's technical experts. ON Semiconductor does not convey any license under its patent rights nor the rights of others. ON Semiconductor products are not designed, intended, or authorized for use as a critical component in life support systems or any FDA Class 3 medical devices or medical devices with a same or similar classification in a foreign jurisdiction or any devices intended for implantation in the human body. Should Buyer purchase or use ON Semiconductor products for any such unintended or unauthorized application, Buyer shall indemnify and

PUBLICATION ORDERING INFORMATION

LITERATURE FULFILLMENT:
Email Requests to: orderlit@onsemi.com

ON Semiconductor Website: www.onsemi.com

TECHNICAL SUPPORT
North American Technical Support:
Voice Mail: 1 800-282-9855 Toll Free USA/Canada

Europe, Middle East and Africa Technical Support: a Phone: 00421 33 790 2910

Phone: 011 421 33 790 2910 For additional information, please contact your local Sales Representative