






Circuit diagram



PCB Layout (Pattern Side)



NO.1	
PART NO	vigor
1	90±30
2	130±30
3	180±30
4	250±30
5	350±50

NO.3-NO.4	
PART NO	NOTE
01~99	SERIAL NUMBER

NO.2	
PART NO	MATERIAL/QTY
S	SUS/1PC
D	SUS/2PCS

- Notes:
- Rating: 12V DC 50mA
 - Contact resistance: 50mΩ max
 - Insulation resistance: 100MΩ 250v AC for 1min
 - Dielectric strength: 250V AC(50/60hz) for 1min
 - Life test:100,000 Cycles
 - Travel:0.20±0.1mm

⑤	Terminal	—	3	Phosphor Bronze	Plating silver	—
④	Contact	—	1	SUS	Plating silver	—
③	Base	—	1	LCP	Black	—
②	Cover	—	1	Brass	Plating silver	—
①	Keystoke	—	1	LCP	Black	—
ITEM	PART NAME	TER'NO.	QTY.	MATERIAL	FINISHING	REMARK

APPROVALS		DATE	HROE® ELECTRONICS CO.,LTD			
DRAWN	LIUCAN	2020.5.16	TITLE:	Tact Switch		
CHECKED			PART NO.	K2-1847FT-A□□A-□□		
APPROVALS			UNIT: mm	SCALE: 1:1	PROJ:	
TOLERANCES ARE	30~以上: ±0.30 10~30 ±0.20 5~10 ±0.15 ~ 5 ±0.10	ANGLE ±2'	DRAWING NO.		SHEET 1 OF 1	

ECN NO.	REV.	DATE.	DESCRIPTION.	CHANGE.	CHECK.	APPRO.
	A		NEW			