

#### **Features**

\* 300W peak pulse power (8/20µs)

\* Protects one data or power line

\* Ultra low leakage: nA level

\* Operating voltage: 5V

\* Ultra low clamping voltage

\* Complies with following standards:

- IEC 61000-4-2 (ESD) immunity test

Air discharge: ±30kV

Contact discharge: ±30kV

- IEC61000-4-4 (Lightning) 20A (8/20ns)

**Ordering Information** 

Part Number	Qty per Reel	Reel Size
SD05C	3000	7"

### **Mechanical Characteristics**

\* Package: SOD-323\* Lead Finish: Matte Tin

\* Case Material: "Green" Molding Compound.

\* UL Flammability Classification Rating 94V-0


\* Moisture Sensitivity: Level 3 per J-STD-020

\* Terminal Connections: See Diagram Below

### **Applications**

- Cellular Handsets and Accessories
- \* Personal Digital Assistants
- Notebooks and Handhelds
- Portable Instrumentation
- \* Peripherals
- Pagers PeripheralsDesktop and Servers

#### **Dimensions and Pin Configuration**



Marking: 2B Or 05B




#### Absolute Maximum Ratings (Tamb=25°C unless otherwise specified)

Parameter	Symbol	Value	Unit	
Peak Pulse Power (8/20μs)	Ppk	300	W	
Peak Pulse Current (8/20µs)	IPP	20	A	
ESD per IEC 61000-4-2 (Air)	VESD	±30	kV	
ESD per IEC 61000-4-2 (Contact)	VESD	±30		
Operating Temperature Range	TJ	-55 to +125	°C	
Storage Temperature Range	Tstg	-55 to +150	°C	

#### Electrical Characteristics (TA=25°C unless otherwise specified)

Symbol	Parameter	
$V_{RWM}$	Nominal Reverse Working Voltage	
$I_R$	Reverse Leakage Current @ V <sub>RWM</sub>	
$V_{BR}$	Reverse Breakdown Voltage @ I <sub>T</sub>	
$I_T$	Test Current for Reverse Breakdown	
$V_{\rm C}$	Clamping Voltage @ I <sub>PP</sub>	
$I_{PP}$	Maximum Peak Pulse Current	
$C_{ESD}$	Parasitic Capacitance	
$V_R$	Reverse Voltage	
f	Small Signal Frequency	



Parameter	Symbol	Test Condition	Min	Тур	Max	Unit
Reverse Working Voltage	Vrwm				5	V
Breakdown Voltage	VBR	$I_T = 1 \text{mA}(\text{Pin}1\text{-Pin}2)$	6.0	7.0	8.0	V
Reverse Leakage Current	$I_R$	$V_{RWM} = 5.0V(Pin2-Pin1)$			0.1	μΑ
Clamping Voltage	Vc	I <sub>PP</sub> = 10A (8 x 20μs pulse) (Pin1-Pin2)		7.0		V
Clamping Voltage	Vc	$I_{PP} = 20A (8 \times 20 \square s \text{ pulse})$ (Pin1-Pin2)		9.0		V
Junction Capacitance	Cı	VR = 0V, f = 1MHz (Pin1-Pin2)		35		pF

计时电子版权所有



#### **Characteristic Curves**

Fig1. 8/20 µs Pulse Waveform




Fig2. ESD Pulse Waveform (according to IEC 61000-4-2)






Fig3. Power Derating Curve



www.techpublic.com.tw




# **Outline Drawing - SOD-323**



	DIMENSIONS				
	MILLIMETERS		INC	HES	
SYM	MIN	MAX	MIN	MAX	
Α	1.50	1.80	0.060	0.071	
В	1.20	1.40	0.045	0.054	
С	2.30	2.70	0.090	0.107	
D	- 4	1.10	-	0.043	
E	0.30	0.40	0.012	0.016	
F	0.10	0.25	0.004	0.010	
Н	-	0.10	-	0.004	

#### **Land Pattern - SOD-323**



SYM	DIMENSIONS		
STIVI	MILLIMETERS	INCHES	
А	3.15	0.120	
В	0.80	0.031	
С	0.80	0.031	

## **Marking Codes**

