



Circuit Diagram



PCB Layout (Pattern side)

PART NO	H	Q	H
A	4.3	Q	12
B	4.5	R	12.5
C	5	S	13
D	5.5	T	13.5
E	6	U	14
F	6.5	V	15
G	7	W	16
H	7.5	X	17
I	8	Y	18
J	8.5	Z	19
K	9		15.5
L	9.5		16.5
M	10		17.5
N	10.5		22
O	11		23
P	11.5		20

NO.1

PART NO	vigor
1	90±30
2	130±30
3	180±30
4	250±30
5	350±50

NO.2

PART NO	MATERIAL/QTY
S	SUS/1PC
C	C5210/1PC
D	SUS/2PCS
F	C5210/2PCS

NO.3

PART NO	NOTE
01~99	SERIAL NUMBER

NO.4-NO.5

ITEM	PART NAME	TER'NO.	QTY.	MATERIAL	FINISHING	REMARK
⑤	Terminal	—	4	Brass(0.30t)	Plating silver	—
④	Contact	—	1	F.Ag/SUS	—	—
③	Base	—	1	Nylon	Black	—
②	Cover	—	1	SPCC	Plating Nickel	—
①	Keystroke	—	1	Nylon	Black	—

APPROVALS	DATE	TITLE:
DRAWN J.X.Zhong	2013/5/30	TACT SWITCHS



ELECTRONICS CO., LTD

ECN NO.	REV.	DATE.	DESCRIPTION.	CHANGE.	CHECK.	APPRO.
—	A	—	NEW	—	—	—

APPROVALS	DATE	TITLE:
CHECKED	—	TACT SWITCHS
APPROVALS	—	—

TOLERANCES ARE	±0.30	±0.20	ANGLE	UNIT: mm	SCALE: 1:1	PROJ:	SHEET 1 OF 1
30~Ø以上	±0.30	±0.20	±2°	mm	1:1	—	—
10~30	±0.20	±0.15	—	—	—	—	—
5~10	±0.15	±0.10	—	—	—	—	—
~5	±0.10	—	—	—	—	—	—