

特性: Specifications;
 电器: Electrical;
 接触阻抗: Contact Resistance

30 millionms MAX

耐电压: Dielectric Withstanding Voltage:
 500v AC AT Sea Level

绝缘阻抗: Insulation Resistance:

1000 MEGA ohms MLN



机构: Mechanical:

接合为: Mating Force;

4.0 KG MAX 最大4Kg

拔出力: Umating Force;

0.7KG MIN.最少0.7KG



Recommended PCB Layout

PART NO	H
U-A-24DD-W-7	13.00
U-A-24DD-W-8	13.70
U-A-24DD-W-9	15.00

③	Base	—	1	NYLON	White
②	Terminal	—	4	Phosphor Bronze	Ag Plated
①	Housing	—	1	SPCC/Phosphor Bronze	Ni Plated
ITEM	PART NAME	TER'NO.	QTY.	MATERIAL	FINISHING

APPROVALS		DATE	TITLE:	
DRAWN	JIANKUN.LU	2015.03.18	USB CONNECTOR	

ECN NO.	REV.	DATE.	DESCRIPTION.	CHANGE.	CHECK.	APPRO.	TOLERANCES ARE	ANGLE	UNIT:	SCALE:	PROJ:
	A		NEW				30~0.15 10~0.25 5~0.10 ~5	±0.30 ±0.25 ±0.20 ±0.15	mm	1:1	PROJ: 1 OF 1