# **Single 2-Input OR Gate**

# MC74HC1G32

The MC74HC1G32 is a high speed CMOS 2-input OR gate fabricated with silicon gate CMOS technology.

The internal circuit is composed of multiple stages, including a buffer output which provides high noise immunity and stable output.

The MC74HC1G32 output drive current is 1/2 compared to MC74HC series.

#### **Features**

- High Speed:  $t_{PD} = 7 \text{ ns (Typ)}$  at  $V_{CC} = 5 \text{ V}$
- Low Power Dissipation:  $I_{CC} = 1 \mu A$  (Max) at  $T_A = 25^{\circ}C$
- High Noise Immunity
- Balanced Propagation Delays  $(t_{pLH} = t_{pHL})$
- Symmetrical Output Impedance ( $I_{OH} = I_{OL} = 2 \text{ mA}$ )
- Chip Complexity: < 100 FETs
- NLV Prefix for Automotive and Other Applications Requiring Unique Site and Control Change Requirements; AEC-Q100 Qualified and PPAP Capable
- These Devices are Pb–Free, Halogen Free/BFR Free and are RoHS Compliant






Figure 2. Logic Symbol

PIN ASSIGNMENT					
1	В				
2	А				
3	GND				
4	Υ				
5	V <sub>CC</sub>				



#### ON Semiconductor®

www.onsemi.com



SC-88A DF SUFFIX CASE 419A



**MARKING** 



TSOP-5 DT SUFFIX CASE 483



XX = Device CodeM = Date Code\* = Pb-Free Package

(Note: Microdot may be in either location)
\*Date Code orientation and/or position may vary
depending upon manufacturing location.



**CASE 318BQ** 



XXX = Specific Device Code

(Note: Microdot may be in either location)

#### **FUNCTION TABLE**

Inp	uts	Output
Α	В	Υ
L	L	L
L	Н	Н
Н	L	Н
Н	Н	Н

#### ORDERING INFORMATION

See detailed ordering, marking and shipping information in the package dimensions section on page 6 of this data

#### **MAXIMUM RATINGS**

Symbol	Parameter	Parameter			
V <sub>CC</sub>	DC Supply Voltage	SC-88A (NLV), TSOP-5 SC-88A, SC-74A	-0.5 to +7.0 -0.5 to +6.5	V	
V <sub>IN</sub>	DC Input Voltage		-0.5 to V <sub>CC</sub> +0.5	V	
V <sub>OUT</sub>	DC Output Voltage		-0.5 to V <sub>CC</sub> +0.5	V	
I <sub>IK</sub>	DC Input Diode Current		±20	mA	
I <sub>OK</sub>	DC Output Diode Current		±20	mA	
I <sub>OUT</sub>	DC Output Source/Sink Current		±12.5	mA	
I <sub>CC</sub> or I <sub>GND</sub>	DC Supply Current per Supply Pin or Ground Pin		±25	mA	
T <sub>STG</sub>	Storage Temperature Range		-65 to +150	°C	
TL	Lead Temperature, 1 mm from Case for 10 Seconds		260	°C	
TJ	Junction Temperature Under Bias		+150	°C	
$\theta_{\sf JA}$	Thermal Resistance (Note 1)	SC-88A SC-74A	377 320	°C/W	
$P_{D}$	Power Dissipation in Still Air at 85°C	SC-88A SC-74A	332 390	mW	
MSL	Moisture Sensitivity		Level 1		
F <sub>R</sub>	Flammability Rating	Oxygen Index: 28 to 34	UL 94 V-0 @ 0.125 in		
V <sub>ESD</sub>	ESD Withstand Voltage (Note 2)	Human Body Model Charged Device Model	2000 1000	V	
I <sub>LATCHUP</sub>	Latchup Performance (Note 3)	SC-88A (NLV), TSOP-5 SC-88A, SC-74A	±500 ±100	mA	

Stresses exceeding those listed in the Maximum Ratings table may damage the device. If any of these limits are exceeded, device functionality should not be assumed, damage may occur and reliability may be affected.

Measured with minimum pad spacing on an FR4 board, using 10 mm-by-1 inch, 20 ounce copper trace with no air flow per JESD51-7.
 HBM tested to ANSI/ESDA/JEDEC JS-001-2017. CDM tested to JESD22-C101-F. JEDEC recommends that ESD qualification to EIA/JESD22-A115A (Machine Model) be discontinued per JEDEC/JEP172A.

<sup>3.</sup> Tested to EIA/JESD78 Class II.

# **RECOMMENDED OPERATING CONDITIONS**

Symbol	Parameter	Min	Max	Unit
V <sub>CC</sub>	DC Supply Voltage	2.0	6.0	V
V <sub>IN</sub>	DC Input Voltage	0.0	V <sub>CC</sub>	V
V <sub>OUT</sub>	DC Output Voltage	0.0	V <sub>CC</sub>	V
T <sub>A</sub>	Operating Temperature Range	-55	+125	°C
t <sub>r</sub> , t <sub>f</sub>	Input Rise and Fall Time $SC-88A \ (NLV), \ TSOP-V_{CC}=2.0 \\ V_{CC}=3.0 \\ V_{CC}=4.5 \\ V_{CC}=6.0$	V 0 V 0 V 0	1000 600 500 400	ns
	Input Rise and Fall Time $SC-88A, SC-74\\ V_{CC}=2.0\\ V_{CC}=2.3\ V\ to\ 2.7\\ V_{CC}=3.0\ V\ to\ 3.6\\ V_{CC}=4.5\ V\ to\ 6.0$	V 0 V 0 V 0	20 20 10 5	ns/V

Functional operation above the stresses listed in the Recommended Operating Ranges is not implied. Extended exposure to stresses beyond the Recommended Operating Ranges limits may affect device reliability.

# DC ELECTRICAL CHARACTERISTICS


			v <sub>cc</sub>	Ţ	A = 25°	С	-40°C ≤ 1	Γ <sub>A</sub> ≤ 85°C	-55°C ≤ T	A ≤ 125°C	
Symbol	Parameter	Test Conditions	(V)	Min	Тур	Max	Min	Max	Min	Max	Unit
V <sub>IH</sub>	High-Level Input Voltage		2.0 3.0 4.5 6.0	1.5 2.1 3.15 4.20	- - -	- - -	1.5 2.1 3.15 4.20	- - - -	1.5 2.1 3.15 4.20	- - - -	V
V <sub>IL</sub>	Low-Level Input Voltage		2.0 3.0 4.5 6.0	- - -	- - -	0.5 0.9 1.35 1.80	- - - -	0.5 0.9 1.35 1.80	- - - -	0.5 0.9 1.35 1.80	V
V <sub>OH</sub>	High-Level Output Voltage	$V_{IN} = V_{IH} \text{ or } V_{IL}$ $I_{OH} = -20 \mu A$	2.0 3.0 4.5 6.0	1.9 2.9 4.4 5.9	2.0 3.0 4.5 6.0		1.9 2.9 4.4 5.9	- - - -	1.9 2.9 4.4 5.9	- - - -	V
		$V_{IN} = V_{IH}$ or $V_{IL}$ $I_{OH} = -2$ mA $I_{OH} = -2.6$ mA	4.5 6.0	4.18 5.68	4.31 5.80	1 1	4.13 5.63	- -	4.08 5.58	- -	
V <sub>OL</sub>	Low-Level Output Voltage	$V_{IN} = V_{IH} \text{ or } V_{IL}$ $I_{OL} = 20  \mu\text{A}$	2.0 3.0 4.5 6.0	- - -	0.0 0.0 0.0 0.0	0.1 0.1 0.1 0.1	- - -	0.1 0.1 0.1 0.1	- - -	0.1 0.1 0.1 0.1	٧
		$V_{IN} = V_{IH}$ or $V_{IL}$ $I_{OL} = 2 \text{ mA}$ $I_{OL} = 2.6 \text{ mA}$	4.5 6.0	-	0.17 0.18	0.26 0.26	- -	0.33 0.33	- -	0.40 0.40	
I <sub>IN</sub>	Input Leakage Current	V <sub>IN</sub> = 6.0 V or GND	6.0	-	-	±0.1	-	±1.0	-	±1.0	μΑ
I <sub>CC</sub>	Quiescent Supply Current	V <sub>IN</sub> = V <sub>CC</sub> or GND	6.0	-	-	1.0	-	10	-	40	μΑ

#### **AC ELECTRICAL CHARACTERISTICS**

			T <sub>A</sub> = 25°C		$-40^{\circ}C \le T_A \le 85^{\circ}C$		-55°C ≤ T <sub>A</sub> ≤ 125°C			
Symbol	Parameter	Test Conditions	Min	Тур	Max	Min	Max	Min	Max	Unit
t <sub>PLH</sub> ,	Propagation Delay,	V <sub>CC</sub> = 5.0 V C <sub>L</sub> = 15 pF	_	3.5	15	-	20	_	25	ns
t <sub>PHL</sub>	(A or B) to Y	$ \begin{array}{c ccccccccccccccccccccccccccccccccccc$		20 11 8 7	100 27 20 17		125 35 25 21	- - -	155 90 35 26	
t <sub>TLH</sub> ,	Output Transition Time	V <sub>CC</sub> = 5.0 V C <sub>L</sub> = 15 pF	_	3	10	-	15	-	20	ns
		$\begin{tabular}{lllllllllllllllllllllllllllllllllll$	- - -	25 16 11 9	125 35 25 21	1 1 1	155 45 31 26	- - -	200 60 38 32	
C <sub>IN</sub>	Input Capacitance		_	5	10	_	10	_	10	pF

		Typical @ 25°C, V <sub>CC</sub> = 5.0 V	
$C_{PD}$	Power Dissipation Capacitance (Note 4)	10	pF

<sup>4.</sup> C<sub>PD</sub> is defined as the value of the internal equivalent capacitance which is calculated from the operating current consumption without load. Average operating current can be obtained by the equation: I<sub>CC(OPR)</sub> = C<sub>PD</sub> • V<sub>CC</sub> • f<sub>in</sub> + I<sub>CC</sub>. C<sub>PD</sub> is used to determine the no–load dynamic power consumption; P<sub>D</sub> = C<sub>PD</sub> • V<sub>CC</sub><sup>2</sup> • f<sub>in</sub> + I<sub>CC</sub> • V<sub>CC</sub>.



Test	Switch Position	C <sub>L</sub> , pF	R <sub>L</sub> , Ω
t <sub>PLH</sub> / t <sub>PHL</sub>	Open		Х
t <sub>TLH</sub> / t <sub>THL</sub> (Note 5)	Open	See AC Characteristics Table	Х
t <sub>PLZ</sub> / t <sub>PZL</sub>	V <sub>CC</sub>	lable	1 k
t <sub>PHZ</sub> / t <sub>PZH</sub>	GND		1 k

X - Don't Care

\* $C_L$  includes probe and jig capacitance  $R_T$  is  $Z_{OUT}$  of pulse generator (typically 50 W) f = 1 MHz

Figure 3. Test Circuit




Figure 4. Switching Waveforms

		V <sub>mo</sub> , V				
V <sub>CC</sub> , V	V <sub>mi</sub> , V	t <sub>PLH</sub> , t <sub>PHL</sub>	$t_{PZL}, t_{PLZ}, t_{PZH}, t_{PHZ}$	$V_L, V$	V <sub>H</sub> , V	$V_Y$ , $V$
3.0 to 3.6	V <sub>CC</sub> /2	V <sub>CC</sub> /2	V <sub>CC</sub> /2	V <sub>OL</sub> + 0.1 (V <sub>OH</sub> – V <sub>OL</sub> )	V <sub>OL</sub> + 0.9 (V <sub>OH</sub> – V <sub>OL</sub> )	0.3
4.5 to 5.5	V <sub>CC</sub> /2	V <sub>CC</sub> /2	V <sub>CC</sub> /2	V <sub>OL</sub> + 0.1 (V <sub>OH</sub> – V <sub>OL</sub> )	V <sub>OL</sub> + 0.9 (V <sub>OH</sub> – V <sub>OL</sub> )	0.3

<sup>5.</sup>  $t_{TLH}$  and  $t_{THL}$  are measured from 10% to 90% of ( $V_{OH}$  –  $V_{OL}$ ), and 90% to 10% of ( $V_{OH}$  –  $V_{OL}$ ), respectively.

#### **ORDERING INFORMATION**

Device	Packages	Specific Device Code	Pin 1 Orientation (See below)	Shipping <sup>†</sup>
MC74HC1G32DFT1G	SC-88A	H4	Q2	3000 / Tape & Reel
NLVHC1G32DFT1G*	SC-88A	H4	Q2	3000 / Tape & Reel
MC74HC1G32DFT2G	SC-88A	H4	Q4	3000 / Tape & Reel
NLVHC1G32DFT2G*	SC-88A	H4	Q4	3000 / Tape & Reel
MC74HC1G32DTT1G	TSOP-5	H4	Q4	3000 / Tape & Reel
NLV74HC1G32DTT1G*	TSOP-5	H4	Q4	3000 / Tape & Reel
MC74HC1G32DBVT1G	SC-74A	H4	Q4	3000 / Tape & Reel

<sup>†</sup>For complete information on tape and reel specifications, including part orientation and tape sizes, please refer to our Tape and Reel Packaging Specifications Brochure, BRD8011/D.

# Pin 1 Orientation in Tape and Reel

**Direction of Feed** 

# 


Q4 Q3


Q4 Q3


<sup>\*</sup>NLV Prefix for Automotive and Other Applications Requiring Unique Site and Control Change Requirements; AEC-Q100 Qualified and PPAP Capable.




**DATE 18 JAN 2018** 







# **RECOMMENDED SOLDERING FOOTPRINT\***



\*For additional information on our Pb-Free strategy and soldering details, please download the ON Semiconductor Soldering and Mounting Techniques Reference Manual, SOLDERRM/D.

#### NOTES:

- DIMENSIONING AND TOLERANCING PER ASME
  Y14.5M, 1994.
  CONTROLLING DIMENSION: MILLIMETERS.
  MAXIMUM LEAD THICKNESS INCLUDES LEAD FINISH
  THICKNESS. MINIMUM LEAD THICKNESS IS THE
  MINIMUM THICKNESS OF BASE MATERIAL.
- DIMENSIONS A AND B DO NOT INCLUDE MOLD FLASH, PROTRUSIONS, OR GATE BURRS. MOLD FLASH, PROTRUSIONS, OR GATE BURRS SHALL NOT EXCEED 0.15 PER SIDE.

	MILLIMETERS				
DIM	MIN	MAX			
Α	0.90	1.10			
A1	0.01	0.10			
b	0.25	0.50			
С	0.10	0.26			
D	2.85	3.15			
E	2.50	3.00			
E1	1.35	1.65			
е	0.95 BSC				
L	0.20	0.60			
М	0 °	10°			

### **GENERIC MARKING DIAGRAM\***



XXX = Specific Device Code

Μ = Date Code = Pb-Free Package

(Note: Microdot may be in either location)

\*This information is generic. Please refer to device data sheet for actual part marking. Pb-Free indicator, "G" or microdot " ", may or may not be present. Some products may not follow the Generic Marking.

DOCUMENT NUMBER:	98AON66279G	Electronic versions are uncontrolled except when accessed directly from the Documen Printed versions are uncontrolled except when stamped "CONTROLLED COPY" in red.		
DESCRIPTION:	SC-74A		PAGE 1 OF 1	

ON Semiconductor and (III) are trademarks of Semiconductor Components Industries, LLC dba ON Semiconductor or its subsidiaries in the United States and/or other countries. ON Semiconductor reserves the right to make changes without further notice to any products herein. ON Semiconductor makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does ON Semiconductor assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. ON Semiconductor does not convey any license under its patent rights nor the rights of others.



#### SC-88A (SC-70-5/SOT-353) CASE 419A-02 **ISSUE L**

**DATE 17 JAN 2013** 



- TES:
  DIMENSIONING AND TOLERANCING
  PER ANSI Y14.5M, 1982.
  CONTROLLING DIMENSION: INCH.
  419A-01 OBSOLETE. NEW STANDARD 3.
- 419A-02.
  DIMENSIONS A AND B DO NOT INCLUDE MOLD FLASH, PROTRUSIONS, OR GATE BURRS.

	INCHES		MILLIMETERS	
DIM	MIN	MAX	MIN	MAX
Α	0.071	0.087	1.80	2.20
В	0.045	0.053	1.15	1.35
С	0.031	0.043	0.80	1.10
D	0.004	0.012	0.10	0.30
G	0.026 BSC		0.65 BSC	
Н		0.004		0.10
J	0.004	0.010	0.10	0.25
K	0.004	0.012	0.10	0.30
N	0.008 REF		0.20 REF	
S	0.079	0.087	2.00	2.20

# **GENERIC MARKING DIAGRAM\***



XXX = Specific Device Code

= Date Code

= Pb-Free Package

(Note: Microdot may be in either location)

\*This information is generic. Please refer to device data sheet for actual part marking. Pb-Free indicator, "G" or microdot "•", may or may not be present. Some products may not follow the Generic Marking.



# 0.50 0.0197 0.65 0.025 0.65 0.025 0.40 0.0157 1.9 mm 0.0748 SCALE 20:1

**SOLDER FOOTPRINT** 

STYLE 1: PIN 1. BASE 2. EMITTER 3. BASE 4. COLLECTOR 5. COLLECTOR	STYLE 2: PIN 1. ANODE 2. EMITTER 3. BASE 4. COLLECTOR 5. CATHODE	STYLE 3: PIN 1. ANODE 1 2. N/C 3. ANODE 2 4. CATHODE 2 5. CATHODE 1	STYLE 4: PIN 1. SOURCE 1 2. DRAIN 1/2 3. SOURCE 1 4. GATE 1 5. GATE 2	STYLE 5: PIN 1. CATHODE 2. COMMON ANODE 3. CATHODE 2 4. CATHODE 3 5. CATHODE 4

5. COLLECTOR	5. CATHODE	5. CATHODE I	5. GATE 2	5. CATHODE 4
STYLE 6: PIN 1. EMITTER 2 2. BASE 2 3. EMITTER 1 4. COLLECTOR 5. COLLECTOR 2/BASE 1	STYLE 7: PIN 1. BASE 2. EMITTER 3. BASE 4. COLLECTOR 5. COLLECTOR	STYLE 8: PIN 1. CATHODE 2. COLLECTOR 3. N/C 4. BASE 5. EMITTER	STYLE 9: PIN 1. ANODE 2. CATHODE 3. ANODE 4. ANODE 5. ANODE	Note: Please refer to datasheet for style callout. If style type is not called out in the datasheet refer to the device datasheet pinout or pin assignment.


DOCUMENT NUMBER:	98ASB42984B	Electronic versions are uncontrolled except when accessed directly from the Document Repositor Printed versions are uncontrolled except when stamped "CONTROLLED COPY" in red.		
DESCRIPTION:	SC-88A (SC-70-5/SOT-353)		PAGE 1 OF 1	

ON Semiconductor and (III) are trademarks of Semiconductor Components Industries, LLC dba ON Semiconductor or its subsidiaries in the United States and/or other countries. ON Semiconductor reserves the right to make changes without further notice to any products herein. ON Semiconductor makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does ON Semiconductor assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. ON Semiconductor does not convey any license under its patent rights nor the rights of others.



TSOP-5 **CASE 483 ISSUE N** 

**DATE 12 AUG 2020** 









#### NOTES:

- DIMENSIONING AND TOLERANCING PER ASME
- CONTROLLING DIMENSION: MILLIMETERS.
  MAXIMUM LEAD THICKNESS INCLUDES LEAD FINISH
  THICKNESS. MINIMUM LEAD THICKNESS IS THE
  MINIMUM THICKNESS OF BASE MATERIAL.
- DIMENSIONS A AND B DO NOT INCLUDE MOLD FLASH, PROTRUSIONS, OR GATE BURRS. MOLD FLASH, PROTRUSIONS, OR GATE BURRS SHALL NOT EXCEED 0.15 PER SIDE. DIMENSION A. OPTIONAL CONSTRUCTION: AN ADDITIONAL
- TRIMMED LEAD IS ALLOWED IN THIS LOCATION. TRIMMED LEAD NOT TO EXTEND MORE THAN 0.2 FROM BODY.

	MILLIMETERS		
DIM	MIN	MAX	
Α	2.85	3.15	
В	1.35	1.65	
C	0.90	1.10	
D	0.25	0.50	
G	0.95 BSC		
Н	0.01	0.10	
J	0.10	0.26	
K	0.20	0.60	
М	0 °	10 °	
S	2.50	3.00	

#### **SOLDERING FOOTPRINT\***



<sup>\*</sup>For additional information on our Pb-Free strategy and soldering details, please download the ON Semiconductor Soldering and Mounting Techniques Reference Manual, SOLDERRM/D.

#### **GENERIC MARKING DIAGRAM\***





XXX = Specific Device Code XXX = Specific Device Code

= Assembly Location = Date Code

= Year = Pb-Free Package

= Work Week W

= Pb-Free Package

(Note: Microdot may be in either location)

\*This information is generic. Please refer to device data sheet for actual part marking. Pb-Free indicator, "G" or microdot " ■", may or may not be present.

DOCUMENT NUMBER:	98ARB18753C	Electronic versions are uncontrolled except when accessed directly from the Document Reposite Printed versions are uncontrolled except when stamped "CONTROLLED COPY" in red.		
DESCRIPTION:	TSOP-5		PAGE 1 OF 1	

ON Semiconductor and (III) are trademarks of Semiconductor Components Industries, LLC dba ON Semiconductor or its subsidiaries in the United States and/or other countries. ON Semiconductor reserves the right to make changes without further notice to any products herein. ON Semiconductor makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does ON Semiconductor assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. ON Semiconductor does not convey any license under its patent rights nor the rights of others.

ON Semiconductor and the are trademarks of Semiconductor Components Industries, LLC dba ON Semiconductor or its subsidiaries in the United States and/or other countries. ON Semiconductor owns the rights to a number of patents, trademarks, copyrights, trade secrets, and other intellectual property. A listing of ON Semiconductor's product/patent coverage may be accessed at <a href="www.onsemi.com/site/pdf/Patent-Marking.pdf">www.onsemi.com/site/pdf/Patent-Marking.pdf</a>. ON Semiconductor reserves the right to make changes without further notice to any products herein. ON Semiconductor and see no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does ON Semiconductor assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. Buyer is responsible for its products and applications using ON Semiconductor products, including compliance with all laws, regulations and safety requirements or standards, regardless of any support or applications information provided by ON Semiconductor. "Typical" parameters which may be provided in ON Semiconductor data sheets and/or specifications can and do vary in different applications and actual performance may vary over time. All operating parameters, including "Typicals" must be validated for each customer application by customer's technical experts. ON Semiconductor does not convey any license under its patent rights nor the rights of others. ON Semiconductor products are not designed, intended, or authorized for use as a critical component in life support systems or any FDA Class 3 medical devices or medical devices with a same or similar classification in a foreign jurisdiction or any devices intended for implantation in the human body. Should Buyer purchase or use ON Semiconductor products for any such unintended or unauthorized application, Buyer shall indemnify and

#### **PUBLICATION ORDERING INFORMATION**

LITERATURE FULFILLMENT:
Email Requests to: orderlit@onsemi.com

ON Semiconductor Website: www.onsemi.com

TECHNICAL SUPPORT North American Technical Support: Voice Mail: 1 800-282-9855 Toll Free USA/Canada Phone: 011 421 33 790 2910

Europe, Middle East and Africa Technical Support:

Phone: 00421 33 790 2910

For additional information, please contact your local Sales Representative