![ON Semiconductor logo]

ON Semiconductor®

FDME910PZT

P-Channel PowerTrench® MOSFET
### -20 V, -8 A, 24 mΩ

Features

- Max $r_{DS(on)}$ = 24 mΩ at V_{GS} = -4.5 V, I_D = -8 A

- Max $r_{DS(on)}$ = 31 mΩ at V_{GS} = -2.5 V, I_D = -7 A

- Max $r_{DS(on)}$ = 45 mΩ at V_{GS} = -1.8 V, I_D = -6 A

- Low profile: 0.55 mm maximum in the new package MicroFET 1.6x1.6 Thin

- HBM ESD protection level > 2 kV typical (Note 3)

- Free from halogenated compounds and antimony oxides

- RoHS Compliant

General Description

This device is designed specifically for battery charging or load switching in cellular handset and other ultraportable applications. It features a MOSFET with low on-state resistance and zener diode protection against ESD. The MicroFET 1.6x1.6 Thin package offers exceptional thermal performance for its physical size and is well suited to switching and linear mode applications.


BOTTOM   **TOP**

MicroFET 1.6x1.6 Thin

MOSFET Maximum Ratings T_A = 25 °C unless otherwise noted

Symbol	Parameter			Ratings	Units
V_{DS}	Drain to Source Voltage			-20	V
V_{GS}	Gate to Source Voltage			±8	V
I_D	-Continuous	T_A = 25°C	(Note 1a)	-8	A
	-Pulsed			-32	
P_D	Power Dissipation	T_A = 25°C	(Note 1a)	2.1	W
	Power Dissipation	T_A = 25°C	(Note 1b)	0.7	
T_J, T_{STG}	Operating and Storage Junction Temperature Range			-55 to +150	°C

Thermal Characteristics

			Ratings	Units
$R_{\theta JA}$	Thermal Resistance, Junction to Ambient	(Note 1a)	60	°C/W
$R_{\theta JA}$	Thermal Resistance, Junction to Ambient	(Note 1a)	175	

Package Marking and Ordering Information

Device Marking	Device	Package	Reel Size	Tape Width	Quantity
E91	FDME910PZT	MicroFET 1.6x1.6 Thin	7 "	8 mm	5000 units

Electrical Characteristics T_J = 25 °C unless otherwise noted

Symbol	Parameter	Test Conditions	Min	Typ	Max	Units
Off Characteristics						
BV_{DSS}	Drain to Source Breakdown Voltage	I_D = -250 μA, V_{GS} = 0 V	-20			V
$\frac{\Delta BV_{DSS}}{\Delta T_J}$	Breakdown Voltage Temperature Coefficient	I_D = -250 μA, referenced to 25 °C		-16		mV/°C
I_{DSS}	Zero Gate Voltage Drain Current	V_{DS} = -16 V, V_{GS} = 0 V			-1	μA
I_{GSS}	Gate to Source Leakage Current	V_{GS} = ±8 V, V_{DS} = 0 V			±10	μA
On Characteristics						
$V_{GS(th)}$	Gate to Source Threshold Voltage	V_{GS} = V_{DS}, I_D = -250 μA	-0.4	-0.6	-1.5	V
$\frac{\Delta V_{GS(th)}}{\Delta T_J}$	Gate to Source Threshold Voltage Temperature Coefficient	I_D = -250 μA, referenced to 25 °C		2.7		mV/°C
$r_{DS(on)}$	Static Drain to Source On Resistance	V_{GS} = -4.5 V, I_D = -8 A		20	24	mΩ
		V_{GS} = -2.5 V, I_D = -7 A		25	31	
		V_{GS} = -1.8 V, I_D = -6 A		32	45	
		V_{GS} = -4.5 V, I_D = -8 A, T_J = 125°C		26	36	
g_{FS}	Forward Transconductance	V_{DD} = -5 V, I_D = -8 A		38		S
Dynamic Characteristics						
C_{iss}	Input Capacitance	V_{DS} = -10 V, V_{GS} = 0 V, f = 1 MHz		1586	2110	pF
C_{oss}	Output Capacitance			236	355	pF
C_{rss}	Reverse Transfer Capacitance			218	330	pF
Switching Characteristics						
$t_{d(on)}$	Turn-On Delay Time	V_{DD} = -10 V, I_D = -8 A, V_{GS} = -4.5 V, R_{GEN} = 6 Ω		9	18	ns
t_r	Rise Time			11	20	ns
$t_{d(off)}$	Turn-Off Delay Time			87	139	ns
t_f	Fall Time			46	74	ns
Q_g	Total Gate Charge	V_{GS} = -4.5 V, V_{DD} = -10 V, I_D = -8 A		15	21	nC
Q_{gs}	Gate to Source Charge			2.2		nC
Q_{gd}	Gate to Drain "Miller" Charge			3.6		nC
Drain-Source Diode Characteristics						
V_{SD}	Source to Drain Diode Forward Voltage	V_{GS} = 0 V, I_S = - 8 A (Note 2)	-0.57	-0.8	-1.2	V
		V_{GS} = 0 V, I_S = -1.8 A (Note 2)		-0.7	-1.2	V
t_{rr}	Reverse Recovery Time	I_F = -8 A, di/dt = 100 A/μs		17	31	ns
Q_{rr}	Reverse Recovery Charge			4.1	10	nC

Notes:

1. $R_{θJA}$ is determined with the device mounted on a 1 in² pad 2 oz copper pad on a 1.5 x 1.5 in. board of FR-4 material. $R_{θJC}$ is guaranteed by design while $R_{θCA}$ is determined by the user's board design.

a. 60 °C/W when mounted   on a 1 in² pad of 2 oz copper.

b. 175 °C/W when mounted on a minimum pad of 2 oz copper.

2. Pulse Test: Pulse Width < 300 μs, Duty cycle < 2.0%.

3. The diode connected between the gate and source serves only as protection ESD. No gate overvoltage rating is implied.

Typical Characteristics T_J = 25 °C unless otherwise noted


**Figure 1. On Region Characteristics**

Figure 2. Normalized On-Resistance vs Drain Current and Gate Voltage


Figure 3. Normalized On Resistance vs Junction Temperature


**Figure 4. On-Resistance vs Gate to Source Voltage**

**Figure 5. Transfer Characteristics**

Figure 6. Source to Drain Diode Forward Voltage vs Source Current

Typical Characteristics $T_J = 25\,°C$ unless otherwise noted

Figure 7. Gate Charge Characteristics

Figure 8. Capacitance vs Drain to Source Voltage

Figure 9. Gate Leakage Current vs Gate to Source Voltage

Figure 10. Forward Bias Safe Operating Area

Figure 11. Single Pulse Maximum Power Dissipation

Typical Characteristics T_J = 25 °C unless otherwise noted

Figure 12. Junction-to-Ambient Transient Thermal Response Curve

PUBLICATION ORDERING INFORMATION

❖ © Semiconductor Components Industries, LLC

www.onsemi.com