**ON Semiconductor** 

Is Now

# Onsemi

To learn more about onsemi<sup>™</sup>, please visit our website at <u>www.onsemi.com</u>

onsemi and ONSEMI. and other names, marks, and brands are registered and/or common law trademarks of Semiconductor Components Industries, LLC dba "onsemi" or its affiliates and/or subsidiaries in the United States and/or other countries. onsemi owns the rights to a number of patents, trademarks, copyrights, trade secrets, and other intellectual property. A listing of onsemi product/patent coverage may be accessed at www.onsemi.com/site/pdf/Patent-Marking.pdf. onsemi reserves the right to make changes at any time to any products or information herein, without notice. The information herein is provided "as-is" and onsemi makes no warranty, representation or guarantee regarding the accuracy of the information, product factures, availability, functionality, or suitability of its products for any particular purpose, nor does onsemi assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. Buyer is responsible for its products and applications using onsemi products, including compliance with all laws, regulations and asfety requirements or standards, regardless of any support or applications information provided by onsemi. "Typical" parameters which may be provided in onsemi data sheets and/or by customer's technical experts. onsemi products and actal performance may vary over time. All operating parameters, including "Typicals" must be validated for each customer application by customer's technical experts. onsemi products are not designed, intended, or authorized for use as a critical component in life support systems or any FDA Class 3 medical devices or medical devices with a same or similar classification in a foreign jurisdiction or any devices intended for implantation in the human body. Should Buyer purchase or use onsemi products for any such unintended or unauthorized application, Buyer shall indemnify and hold onsemi and its officers, employees, subsidiari

# PNP Epitaxial Silicon Transistor

# **KSA992**

## Features

- Audio Frequency Low-Noise Amplifier
- Complement to KSC1845
- These are Pb-Free Devices

### **MAXIMUM RATINGS** (Values are at $T_A = 25^{\circ}C$ unless otherwise noted.)

Symbol	Parameter	Value	Unit
V <sub>CBO</sub>	Collector-Base Voltage	-120	V
V <sub>CEO</sub>	Collector-Emitter Voltage	-120	V
V <sub>EBO</sub>	Emitter-Base Voltage	-5	V
Ι <sub>C</sub>	Collector Current	-50	mA
Ι <sub>Β</sub>	Base Current	-10	mA
TJ	Junction Temperature	150	°C
T <sub>STG</sub>	Storage Temperature	–55 to 150	°C

Stresses exceeding those listed in the Maximum Ratings table may damage the device. If any of these limits are exceeded, device functionality should not be assumed, damage may occur and reliability may be affected.

**THERMAL CHARACTERISTICS** (Values are at  $T_A = 25^{\circ}C$  unless otherwise noted.) (Note 1)

Symbol	Parameter	Value	Unit
PD	Power Dissipation	500	mW
	Derate Above 25°C	4	mW/°C
$R_{ hetaJA}$	Thermal Resistance, Junction-to-Ambient	250	°C/W

1. PCB size: FR-4, 76 mm x 114 mm x 1.57 mm (3.0 inch x 4.5 inch x 0.062 inch) with minimum land pattern size.




# **ON Semiconductor®**

#### www.onsemi.com



TO-92 3 4.825x4.76 TO-92 3 4.83x4.76 CASE 135AN LEADFORMED CASE 135AR

### MARKING DIAGRAM



### **ORDERING INFORMATION**

See detailed ordering and shipping information on page 4 of this data sheet.

# KSA992

# **ELECTRICAL CHARACTERISTICS** (Values are at $T_A = 25^{\circ}C$ unless otherwise noted.)

Symbol	Parameter	Conditions	Min	Тур	Max	Unit
I <sub>CBO</sub>	Collector Cut-Off Current	$V_{CB} = -120 \text{ V}, I_E = 0$	-	-	-50	nA
I <sub>CEO</sub>	Collector Cut-Off Current	$V_{CE} = -100 \text{ V}, \text{ I}_{B} = 0$	-	-	-1	μΑ
I <sub>EBO</sub>	Emitter Cut–Off Current	$V_{EB} = -5 V, I_{C} = 0$	-	-	-50	nA
h <sub>FE1</sub>	DC Current Gain	$V_{CE} = -6 \text{ V}, \text{ I}_{C} = -0.1 \text{ mA}$	150	500	-	
h <sub>FE2</sub>		$V_{CE} = -6 \text{ V}, \text{ I}_{C} = -1 \text{ mA}$	200	500	800	
V <sub>BE</sub> (on)	Base-Emitter On Voltage	$V_{CE} = -6 \text{ V}, \text{ I}_{C} = -1 \text{ mA}$	-0.55	-0.61	-0.65	V
V <sub>CE</sub> (sat)	Collector-Emitter Saturation Voltage	$I_{\rm C} = -10$ mA, $I_{\rm B} = -1$ mA	-	-0.09	-0.30	V
f <sub>T</sub>	Current Gain Bandwidth Product	$V_{CE} = -6 \text{ V}, \text{ I}_{C} = -1 \text{ mA}$	50	100	-	MHz
C <sub>ob</sub>	Output Capacitance	$V_{CB} = -30$ V, $I_E = 0$ , $f = 1$ MHz	-	2	3	pF
NF	Noise Figure	$V_{CE}$ = -5 V, I <sub>C</sub> = -1.0 mA, R <sub>S</sub> = 100 kΩ, f = 1 kHz	-	7	-	dB


Product parametric performance is indicated in the Electrical Characteristics for the listed test conditions, unless otherwise noted. Product performance may not be indicated by the Electrical Characteristics if operated under different conditions.

## h<sub>FE</sub> CLASSIFICATION

Classification	Р	F	FA	FB	E
h <sub>FE2</sub>	200~400	300~600	300~470	430~600	400~800

# KSA992

# **TYPICAL PERFORMANCE CHARACTERISTICS**



# KSA992

# TYPICAL PERFORMANCE CHARACTERISTICS (Continued)





Figure 7. Power Derating

#### **ORDERING INFORMATION**

Part Number	Top Mark	Package	Shipping <sup>†</sup>
KSA992FBU	A992	TO-92 3L (Pb-Free)	10000 Units / Bulk
KSA992FTA	A992	TO-92 3L (Pb-Free)	2000 / Tape & Ammo
KSA992FATA	A992	TO-92 3L (Pb-Free)	2000 / Tape & Ammo
KSA992FBTA	A992	TO-92 3L (Pb-Free)	2000 / Tape & Ammo


+For information on tape and reel specifications, including part orientation and tape sizes, please refer to our Tape and Reel Packaging Specifications Brochure, BRD8011/D.





© Semiconductor Components Industries, LLC, 2019





DOCUMENT NUMBER:	98AON13879G Electronic versions are uncontrolled except when accessed directly from the Document Repository. Printed versions are uncontrolled except when stamped "CONTROLLED COPY" in red.				
DESCRIPTION:	TO-92 3 4.83X4.76 LEADFORMED		PAGE 1 OF 1		
ON Semiconductor and M are trademarks of Semiconductor Components Industries. LLC dba ON Semiconductor or its subsidiaries in the United States and/or other countries.					

ON Semiconductor and ware trademarks of Semiconductor Components Industries, LLC dba ON Semiconductor or its subsidiaries in the United States and/or other countries. ON Semiconductor reserves the right to make changes without further notice to any products herein. ON Semiconductor makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does ON Semiconductor assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. ON Semiconductor does not convey any license under its patent rights nor the rights of others.

© Semiconductor Components Industries, LLC, 2019

ON Semiconductor and are trademarks of Semiconductor Components Industries, LLC dba ON Semiconductor or its subsidiaries in the United States and/or other countries. ON Semiconductor owns the rights to a number of patents, trademarks, copyrights, trade secrets, and other intellectual property. A listing of ON Semiconductor's product/patent coverage may be accessed at <u>www.onsemi.com/site/pdf/Patent-Marking.pdf</u>. ON Semiconductor reserves the right to make changes without further notice to any products herein. ON Semiconductor makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does ON Semiconductor assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. Buyer is responsible for its products and applications using ON Semiconductor products, including compliance with all laws, regulations and safety requirements or standards, regardless of any support or applications information provided by ON Semiconductor. "Typical" parameters which may be provided in ON Semiconductor date sheets and/or specifications can and do vary in different applications and actual performance may vary over time. All operating parameters, including "Typicals" must be validated for each customer application by customer's technical experts. ON Semiconductor does not convey any license under its patent rights nor the rights of others. ON Semiconductor products are not designed, intended, or authorized for use a a critical component in life support systems or any FDA Class 3 medical devices or medical devices with a same or similar classification in a foreign jurisdiction or any devices intended for implantation in the human body. Should Buyer purchase or use ON Semiconductor houteds for any such unintended or unauthorized application, Buyer shall indemnify and hold ON Semiconductor and its officers, employees, subsidiaries

#### PUBLICATION ORDERING INFORMATION

#### LITERATURE FULFILLMENT:

#### TECHNICAL SUPPORT

ON Semiconductor Website: www.onsemi.com

Email Requests to: orderlit@onsemi.com

North American Technical Support: Voice Mail: 1 800–282–9855 Toll Free USA/Canada Phone: 011 421 33 790 2910 Europe, Middle East and Africa Technical Support: Phone: 00421 33 790 2910 For additional information, please contact your local Sales Representative