

南京华鼎电子有限公司中国·南京市江宁区汤山镇

Tel: 025-84107685 Fax: 025-84107684

E-mail: servicehd@paralight.com.cn

DATA SHEET

PART NO.: C-362I

REV: _A/0_

CUSTOMER'S APPROVAL: __

DCC:

DRAWING NO.: DS-12-07-0003


DATE: 2007-01-11


Page: 1




C-362I REV:A / 0

PACKAGE DIMENSIONS







NOTES: 1. All dimensions are in millimeters. (inches)

- 2. Tolerance is \pm 0.25(0.010") unless otherwise specified.
- 3. We would like to offer you samples and mass production after you confirmed the DS and signed to return us

DRAWING NO. : DS-12-07-0003 DATE : 2007-01-11 Page : 2



C-362I REV:A / 0

FEATURES

9.20mm (0.36 inch) DIGIT HEIGHT COMMON CATHODE I.C. COMPATIBLE LOW POWER CONSUMPTION Pb FREE PRODUCTS BLACK FACE, WHITE SEGMENTS

Raw Material: GaAlAs/GaAs

ABSOLUTE MAXIMUM RATING : (Ta = 25°C) RED UNIT SYMBOL PARAMETER PD Power Dissipation Per Segment 60 m₩ ٧R Reverse Voltage Per Segment 5 ٧ Continuous Forward Current Per Segment **I**AF 30 mΑ Peak Forward Current Per Segment **IPF** 100 mΑ (1/10 Duty Cycle, 0.1ms Pulse Width) Derating Linear From 25°C Per Segment 0.33 mA/°C Operating Temperature Range Topr -35°C to 85°C Storage Temperature Range 35°C to 85°C Tstg


ELECTR	O-OPTICAL CHARACTERIST	ICS : (Ta = 25°(S)			
SYMBOL	PARAMETER	TEST CONDITION	MIN.	TYP.	MAX.	UNIT
VF	Forward Voltage , Per Segment	IF = 20mA		1.8	2.2	V
IR	Reverse Current, Per Segment	VR = 5V			100	μA
λР	Peak Emission Wavelength	IF = 20mA		660		nm
λD	Dominant Wavelength	IF = 20mA		643		nm
Δλ	Spectral Line Half-Width	IF = 20mA		20		nm
Iv	Luminous Intensity Per Segment	IF = 10mA	1.2	3.0		mcd


DRAWING NO. : DS-12-07-0003 DATE : 2007-01-11 Page : 3


HD-R/RD014




C-362I REV:A / 0









DRAWING NO.: DS-12-07-0003 DATE: 2007-01-11 Page: 4



C-362I REV:A / 0

	SC	1	D	FI	RI	N	G
ı	\mathbf{J}	,_	ப	_	•	11	u

METHOD	SOLDERING CONDITIONS	REMARK
		Solder no closer than 2mm from
DIP	Bath temperature: 250 max	the base of the package
SOLDERING	Immersion time: within 3 sec	Using soldering flux," RESIN FLUX"
		is recommended.
		During soldering, take care not to
	Soldering iron: 30W or smaller	press the tip of iron against the
SOLDERING		
	Temperature at tip of iron: 250°C or lower	PIN.
IRON		

Soldering time: within 3 sec.

(To prevent heat from being transferred directly to the PIN.)

1) When soldering the PIN of Display in a jig that the package is fixed with a panel (See flg.1), be careful not to stress the PIN with iron tip. When soldering Display in a condition that the package is fixed with a panel, be careful not to cling and stress the surface of Display on the panel to avoid damaging the Display.




Fig.1

Regarding solution in the tinning oven for product-tinning, compound sub-solution made of tin & copper and sliver is proposed with the temperature of Celsius 250. The proportion of the alloyed solution is tin 95.5: copper 3.5: silver 0.5 by percentage. The time of tinning is constantly 3 seconds.

DRAWING NO. : DS-12-07-0003 DATE : 2007-01-11 Page : 5