MSKSEMI 美森科













ESD

TVS

TSS

MOV

GDT

PIFD

AO4882-MS

Product specification





General Features

- V_{DS} = 40V I_D = 6A
- $R_{DS(ON)} < 30 \text{m}\Omega$ @ $V_{GS} = 10V$

Application

- Battery protection
- Load switch
- Uninterruptible power supply

Reference News

PACKAGE OUTLINE	Pin Configuration	Marking
S1 S2 SD2 SD2 SD2 SD2 SD2 SD2 SD2 SD2 SD2	D1 D1 D2 D2 80 70 60 50 10 20 30 40 S1 G1 S2 G2	MSKSEMI 4882 3SKJ82
SOP-8	N-Channel MOSFET	



Absolute Maximum Ratings (TA=25unless otherwise noted)

Symbol	Parameter	Rating	Units
Vos	Drain- Source Voltage	40	V
Vgs	Gate- Source Voltage	±20	V
I _D @ T _A = 25 C	Continuous Drain Current ¹	6	Α
ID@ TA= 7 0 C	Continuous Drain Current ¹	4	Α
Ідм	Pulsed Drain Current ²	36	Α
EAS	Single Pulse Avalanche Energy ³	31	mJ
las	Avalanche Current	25	Α
P □@ T A=25 °C	Total Power Dissipation ⁴	1.9	W
Тѕтс	Storage Temperature Range	-55 to 150	°C
TJ	Operating Junction Temperature Range	-55 to 150	°C
Reja	Thermal Resistance Junction-ambient¹(t≤10s)	40	°C/W
	Thermal Resistance Junction- ambient ¹	65	°C/W



Electrical Characteristics (TJ=25 °C, unless otherwise noted)

Symbol	Parameter	Conditions	Min.	Тур.	Max.	Unit
BVpss	Drain- Source Breakdown Voltage	V _{GS} =0V , I _D =250uA	40			V
△ BVDSS/ △ TJ	BVDSS Temperature Coefficient	Reference to 250 , ID=1mA		0.032		V/°C
		Vgs=10V, ID=6A		25	30	m O
RDS(ON)	Static Drain-Source On-Resistance ²	V _{GS} =4.5V , I _D =4A		35	45	m Ω
V _{GS(th)}	Gate Threshold Voltage		1.2	1.6	2.5	V
△ VGS(th)	V _{GS(th)} Temperature Coefficient	V _{GS} =V _{DS} , I _D =250uA		-4.8		Mv/℃
		V _{DS} =32V , V _{GS} =0V , T _J =250			1	
Ipss	Drain- Source Leakage Current	V _{DS} =32V , V _{GS} =0V , T _J =55C			5	ųA
Igss	Gate- Source Leakage Current	$V_{GS}=\pm20V$, $V_{DS}=0V$			±100	nA
gfs	Forward Transconductance	V _{DS} =5V , I _D =6A		32		S
Rg	Gate Resistance	V _{DS} =0V , V _{GS} =0V , f=1MHz		2.1		
Qg	Total Gate Charge (4.5V)			9.8		
Qgs	Gate- Source Charge	Vps=32V , Vgs=4.5V , Ip=6A		2.8		nC
Qgd	Gate- Drain Charge			3.9		
T _{d(on)}	Turn- On Delay Time			2.8		
Tr	Rise Time	V _{DD} =20V , V _{GS} =10V ,		40.4		
T _{d(off)}	Turn-Off Delay Time	Rg=3.3 lp=6A		22.8		ns
Tf	Fall Time			6.4		
Ciss	Input Capacitance			1013		
Coss	Output Capacitance	V _{DS} =15V , V _{GS} =0V , f=1MHz		107		pF
Crss	Reverse Transfer Capacitance			76		'
Is	Continuous Source Current ^{1,5}				8	Α
Isм	Pulsed Source Current ^{2,5}	$V_G=V_D=0V$, Force Current			36	Α
VsD	Diode Forward Voltage ²	Vgs=0V , Is=1A , TJ=250			1	V
trr	Reverse Recovery Time	IF=7A , dI/dt=100A/μs ,		10		nS
Qrr	Reverse Recovery Charge	T _J = 2 5 C		3.3		nC

Note:

- 1. The data tested by surface mounted on a 1 inch 2 FR-4 board with 2OZ copper.
- 2.The data tested by pulsed , pulse width \leq 300us , duty cycle \leq 2%
- 3. The EAS data shows Max. rating . The test condition is VDD=25V,VGS=10V,L=0.1mH,IAS=25A
- 4.The power dissipation is limited by 150 $^{\circ}\mathrm{C}$ junction temperature
- $5. The \ data \ is \ theoretically \ the \ same \ as \ ID \ and \ IDM \ , in \ real \ applications \ , should \ be \ limited \ by \ total \ power \ dissipation.$



Typical Characteristics




Fig.1 Typical Output Characteristics




Fig.3 Forward Characteristics of Reverse




Fig. 5 Normalized V_{GS(th)} vs. T_J




Fig.2 On-Resistance vs. G-S Voltage




Fig.4 Gate-Charge Characteristics





Fig.6 Normalized RDSON vs. TJ






Fig.7 Capacitance

Fig.8 Safe Operating Area




Fig.9 Normalized Maximum Transient Thermal Impedance




Fig.10 Switching Time Waveform







Fig.11 Unclamped Inductive Switching Waveform



PACKAGE MECHANICAL DATA








Symbol	Dimensions I	n Millimeters	Dimension	s In Inches
5 J 111 5 G 1	Min	Max	Min	Max
A	1.350	1.750	0.053	0.069
A1	0.100	0.250	0.004	0.010
A2	1.350	1.550	0.053	0.061
b	0.330	0.510	0.013	0.020
c	0.170	0.250	0.007	0.010
D	4.800	5.000	0.189	0.197
e	1.270((BSC)	0.050	(BSC)
Е	5. 800	6.200	0.228	0.244
E1	3.800	4.000	0.150	0.157
L	0.400	1.270	0.016	0.050
θ	0°	8°	0°	8°

Suggested Pad Layout



Note:

- 1.Controlling dimension:in millimeters.
- 2.General tolerance:±0.05mm.
- 3. The pad layout is for reference purposes only

REEL SPECIFICATION

P/N	PKG	QTY
AO4882-MS	SOP-8	3000



Attention

- Any and all MSKSEMI Semiconductor products described or contained herein do not have specifications that can handle applications that require extremely high levels of reliability, such as life-support systems, aircraft's control systems, or other applications whose failure can be reasonably expected to result in serious physical and/or material damage. Consult with your MSKSEMI Semiconductor representative nearest you before using any MSKSEMI Semiconductor products described or contained herein in such applications.
- MSKSEMI Semiconductor assumes no responsibility for equipment failures that result from using products at values that exceed, even momentarily, rated values (such as maximum ratings, operating condition ranges, or other parameters) listed in products specificationsof any andall MSKSEMI Semiconductor products described or contained herein.
- Specifications of any and all MSKSEMI Semiconductor products described or contained herein stipulate the performance, characteristics, and functions of the described products in the independent state, and are not guarantees of the performance, characteristics, and functions of the described products as mounted in the customer's products or equipment. To verify symptoms and states that cannot be evaluated in an independent device, the customer should always evaluate and test devices mounted in the customer'sproducts or equipment.
- MSKSEMI Semiconductor. strives to supply high-quality high-reliability products. However, any and all semiconductor products fail with someprobability. It is possiblethat these probabilistic failures could give rise to accidents or events that could endanger human lives, that could give rise to smoke or fire, or that could cause damage to other property. When designing equipment, adopt safety measures so that these kinds of accidents or events cannot occur. Such measures include but are not limited to protective circuits anderror prevention circuitsfor safedesign, redundant design, and structural design.
- In the event that any or all MSKSEMI Semiconductor products (including technical data, services) described or contained herein are controlled under any of applicable local export control laws and regulations, such products must not be exported without obtaining the export license from theauthorities concerned in accordance with the above law.
- No part of this publication may be reproduced or transmitted in any form or by any means, electronic or mechanical, including photocopying and recording, or any information storage or retrieval system, or otherwise, without the prior written permission of MSKSEMI Semiconductor.
- Information (including circuit diagrams and circuit parameters) herein is for example only; it is not guaranteed for volume production. MSKSEMI Semiconductor believes information herein is accurate and reliable, but no guarantees are made or implied regarding its use or any infringements of intellectual property rights or other rights of third parties.
- Any and all information described or contained herein are subject to change without notice due to product/technology improvement, etc. Whendesigning equipment, refer to the "Delivery Specification" for the MSKSEMI Semiconductor productthat you intend to use.