



# GL4435-8

## GL Silicon P-Channel Power MOSFET


### General Description:

The GL4435-8 uses advanced trench technology and design to provide excellent  $R_{DS(ON)}$  with low gate charge. It can be used in a wide variety of applications. The package form is SOP-8, which accords with the RoHS standard.

$V_{DSS}$	-30	V
$I_D$	-9.1	A
$P_D$	3.1	W
$R_{DS(ON)type}$	20	m $\Omega$


### Features:

- $R_{DS(ON)} < 30m\Omega @ V_{GS}=10V$  (Typ20m $\Omega$ )
- High density cell design for ultra low  $R_{dson}$
- Fully characterized avalanche voltage and current
- Excellent package for good heat dissipation



### Applications:

- Power switching application
- Hard switched and high frequency circuits
- Uninterruptible power supply



### Absolute (Tc= 25°C unless otherwise specified):

Symbol	Parameter	Rating	Units
$V_{DSS}$	Drain-to-Source Voltage	-30	V
$I_D$	Continuous Drain Current	-9	A
$I_{DM}$	Pulsed Drain Current	-50	A
$V_{GS}$	Gate-to-Source Voltage	$\pm 20$	V
$P_D$	Power Dissipation	3.1	W
$T_J, T_{stg}$	Operating Junction and Storage Temperature Range	155, -55 to 155	$^{\circ}C$



# GL4435-8

## GL Silicon P-Channel Power MOSFET

**Electrical Characteristics** ( $T_c = 25^\circ\text{C}$  unless otherwise specified) :

OFF Characteristics						
Symbol	Parameter	Test Conditions	Rating			Units
			Min.	Typ.	Max.	
$V_{DSS}$	Drain to Source Breakdown Voltage	$V_{GS}=0V, I_D=-250\mu A$	-30	--	--	V
$I_{DSS}$	Drain to Source Leakage Current	$V_{DS}=-30V, V_{GS}=0V, T_a=25^\circ\text{C}$	--	--	-1.0	$\mu A$
$I_{GSS(F)}$	Gate to Source Forward Leakage	$V_{GS}=+20V$	--	--	0.1	$\mu A$
$I_{GSS(R)}$	Gate to Source Reverse Leakage	$V_{GS}=-20V$	--	--	-0.1	$\mu A$

ON Characteristics <sup>a3</sup>						
Symbol	Parameter	Test Conditions	Rating			Units
			Min.	Typ.	Max.	
$R_{DS(ON)}$	Drain-to-Source On-Resistance	$V_{GS}=-10V, I_D=-9.1A$	--	20	30	$m\Omega$
		$V_{GS}=-4.5V, I_D=-6.9A$		25	40	$m\Omega$
$V_{GS(TH)}$	Gate Threshold Voltage	$V_{DS}=V_{GS}, I_D=-250\mu A$	-1.0	--	-3.0	V
Pulse width $t_p \leq 380\mu s, \delta \leq 2\%$						

Dynamic Characteristics <sup>a4</sup>						
Symbol	Parameter	Test Conditions	Rating			Units
			Min.	Typ.	Max.	
$g_{fs}$	Forward Transconductance	$V_{DS}=-15V, I_D=-9.1A$	10	--	--	S
$C_{iss}$	Input Capacitance	$V_{GS}=0V, V_{DS}=-15V$ $f=1.0\text{MHz}$	--	1600	--	pF
$C_{oss}$	Output Capacitance		--	350	--	
$C_{rss}$	Reverse Transfer Capacitance		--	300	--	

Resistive Switching Characteristics <sup>a4</sup>						
Symbol	Parameter	Test Conditions	Rating			Units
			Min.	Typ.	Max.	
$t_{d(ON)}$	Turn-on Delay Time	$V_{DD}=-15V, I_D=-1A$ $V_{GS}=-10V, R_G=6\Omega$	--	10	--	ns
$t_r$	Rise Time		--	15	--	
$t_{d(OFF)}$	Turn-Off Delay Time		--	110	--	
$t_f$	Fall Time		--	70	--	
$Q_g$	Total Gate Charge	$V_{DD}=-15V, I_D=-9.1A$ $V_{GS}=-10V$	--	30	--	nC
$Q_{gs}$	Gate to Source Charge		--	5.5	--	
$Q_{gd}$	Gate to Drain ( "Miller" )Charge		--	8	--	



# GL4435-8

## GL Silicon P-Channel Power MOSFET

Source-Drain Diode Characteristics						
Symbol	Parameter	Test Conditions	Rating			Units
			Min.	Typ.	Max.	
$I_S$	Continuous Source Current <sup>a2</sup> (Body Diode)		--	--	-9.1	A
$V_{SD}$	Diode Forward Voltage <sup>a3</sup>	$I_S = -2.1A, V_{GS} = 0V$	--	--	-1.2	V

Symbol	Parameter	Typ.	Units
$R_{\theta JC}$	Junction-to-Case <sup>a2</sup>	40	°C/W

<sup>a1</sup>: Repetitive Rating: Pulse width limited by maximum junction temperature.

<sup>a2</sup>: Surface Mounted on FR4 Board,  $t \leq 10\text{sec}$ .

<sup>a3</sup>: Pulse Test: Pulse Width  $\leq 300\mu\text{s}$ , Duty Cycle  $\leq 2\%$ .

<sup>a4</sup>: Guaranteed by design, not subject to production

### Test circuit & Thermal Characteristics




Figure 1: Switching Test Circuit




Figure 2: Switching Waveforms




Figure 3 Power Dissipation




Figure 4 Drain Current




Figure 5 Output Characteristics




Figure 6 Drain-Source On-Resistance



# GL4435-8

## GL Silicon P-Channel Power MOSFET




Figure 7 Transfer Characteristics




Figure 8 Drain-Source On-Resistance




Figure 9  $R_{dson}$  vs  $V_{GS}$




Figure 10 Capacitance vs  $V_{DS}$




Figure 11 Gate Charge




Figure 12 Source- Drain Diode Forward



# GL4435-8

## GL Silicon P-Channel Power MOSFET




Figure 13 Safe Operation Area




Figure 14 Normalized Maximum Transient Thermal Impedance