

LNB8304RDT0AG

N-Channel Logic Level Enhancement Mode MOSFET




DFN3333-8A

1. FEATURES

- Low RDS(on) trench technology.
- Low thermal impedance.
- Fast switching speed.
- We declare that the material of product are Halogen Free and compliance with RoHS requirements.

2. APPLICATION

- Power Routing
- DC/DC Conversion
- Motor Drives



3. ORDERING INFORMATION

| Device | Marking | Shipping |
|---------------|---------|----------------|
| LNB8304RDT0AG | N2R | 2000/Tape&Reel |

4. MAXIMUM RATINGS(Ta = 25°C unless otherwise stated)

| Parameter | | Symbol | Limits | Unit |
|--------------------------------|------------|--------|------------|------|
| Drain-to-Source Voltage | | VDSS | 30 | V |
| Gate-to-Source Voltage | | VGS | ±20 | V |
| Continuous Drain Current | TC = 25°C | ID | 75 | A |
| | TC = 100°C | | 45 | |
| Pulsed Drain Current (Note 1) | | IDM | 300 | |
| Avalanche Current | | IAS | 23 | |
| Avalanche Energy(L = 0.1mH) | | EAS | 26.45 | mJ |
| Power Dissipation | TC = 25°C | PD | 21 | W |
| | TC = 100°C | | 8.3 | |
| Operating Junction Temperature | | TJ | -55 ~ +150 | °C |
| Storage Temperature Range | | Tstg | -55 ~ +150 | |

1. Pulse width limited by maximum junction temperature.

2. 50°C/W when mounted on a 1 in² pad of 2 oz copper.

5. THERMAL CHARACTERISTICS

| Parameter | Symbol | Limits | Unit |
|--------------------------------------|------------------|--------|------|
| Maximum Junction-to-Ambient (Note 2) | R _{θJA} | 50 | °C/W |
| Maximum Junction-to-Case | R _{θJC} | 6 | |





6. ELECTRICAL CHARACTERISTICS

| Characteristic | Symbol | Min. | Typ. | Max. | Unit |
|---|---|---------|------|------|------|
| Static | | | | | |
| Drain-Source Breakdown Voltage (VGS = 0V, ID = 250μA) | V(BR)DSS | 30 | - | - | V |
| Gate-Source Threshold Voltage (VDS = VGS , ID = 250 uA) | VGS(th) | 1 | 1.7 | 3 | V |
| Gate-Body Leakage (VDS = 0 V, VGS = ±20 V) | IGSS | - | - | ±100 | nA |
| Zero Gate Voltage Drain Current (VDS = 24 V, VGS = 0 V) | IDSS | - | - | 1 | μA |
| Drain-Source On-Resistance(Note 3) (VGS = 10 V, ID = 27 A) (VGS = 4.5 V, ID = 24 A) | RDS(on) | - | - | 4 | mΩ |
| Dynamic | | | | | |
| Input Capacitance | (VDS = 15 V, VGS = 0 V, f = 1MHz) | Ciss | - | 2477 | - |
| Output Capacitance | | Coss | - | 330 | - |
| Reverse Transfer Capacitance | | Crss | - | 255 | - |
| Total Gate Charge(VGS=4.5V) | (VDS = 15 V, VGS = 10 V, ID = 15A) | Qg | - | 26 | - |
| Total Gate Charge(VGS=10V) | | Qg | - | 53 | - |
| Gate-Source Charge | | Qgs | - | 7 | - |
| Gate-Drain Charge | | Qgd | - | 10 | - |
| Turn-On Delay Time | (VDS=15 V, ID=24A, VGS= 10V, RGS = 2.7 Ω) | td(on) | - | 10 | - |
| Rise Time | | tr | - | 16.5 | - |
| Turn-Off Delay Time | | td(off) | - | 65 | - |
| Fall Time | | tf | - | 32 | - |
| Gate Resistance (VGS = 15mV, VDS = 0V, f = 1MHz) | Rg | - | 1 | - | Ω |
| Source-Drain Diode Ratings and Characteristics(TC= 25° C) | | | | | |
| Continuous Current | IS | - | - | 75 | A |
| Pulsed Current(Note 5) | ISM | - | - | 300 | A |
| Forward Voltage (IS=2A, VGS = 0V) | VSD | - | - | 1.3 | V |





3.Pulse test: PW≤ 300μs duty cycle ≤ 2%.

4.Pulse width limited by maximum junction temperature.

7.ELECTRICAL CHARACTERISTICS CURVES






7.ELECTRICAL CHARACTERISTICS CURVES(Con.)



8.OUTLINE AND DIMENSIONS

DFN3333-8A




| DFN3333-8A | | | |
|------------|-----------|------|------|
| DIM | MIN | NOR | MAX |
| A | 0.60 | 0.65 | 0.70 |
| A1 | 0.00 | 0.03 | 0.05 |
| b | 0.27 | 0.32 | 0.37 |
| D | 3.25 | 3.30 | 3.35 |
| E | 3.25 | 3.30 | 3.35 |
| D1 | 2.22 | 2.27 | 2.32 |
| E1 | 1.60 | 1.65 | 1.70 |
| e | 0.65BSC | | |
| L | 0.40 | 0.45 | 0.50 |
| L1 | 0.30 | 0.35 | 0.40 |
| A3 | 0.152REF. | | |

All Dimensions in mm

9.SOLDERING FOOTPRINT

DFN3333-8A



| DFN3333-8A | |
|------------|------|
| DIM | (mm) |
| C | 0.65 |
| X | 0.42 |
| X1 | 0.42 |
| X2 | 0.23 |
| X3 | 2.37 |
| Y | 0.70 |
| Y1 | 1.85 |
| Y2 | 3.70 |
| Y3 | 2.25 |