

Aug. 2017 Ver.1.0 TDK Corporation

Multilayer Low Pass Filter

For LTE

DEA Series 0.65x0.5mm [EIA 0202] TYPE


P/N: **DEA070960LT-4022A1** 



Aug. 2017 Ver.1.0 TDK Corporation

# **DEA070960LT-4022A1**

#### SHAPES AND DIMENSIONS



#### Dimensions (mm)

L	W	T	а	b	С	d
0.65	0.50	0.30	0.20	0.20	0.115	0.21
+/-0.05	+/-0.05	Max	+/-0.05	+/-0.05	+/-0.05	+/-0.05

#### Terminal functions

(1)	Input Port	(3)
(2)	Output Port	(4)

#### DC Cut

No. IN and OUT are connected, but between IN and GND, or between OUT and GND are not connected.

GND GND

#### TERMINATION FINISH

Material	
Ag	



Aug. 2017 Ver.1.0 TDK Corporation

# **DEA070960LT-4022A1**

# ELECTRICAL CHARACTERISTICS

(Measurement)

Parameter	Freque	nev	(MH2)	TDK Target Spec		
raianietei	Treque	псу	(141112)	Min.	Тур.	Max.
Insertion Loss (dB)	617	to	915	-	0.31	0.40
	915	to	960	1	0.31	0.40
Return Loss (dB)	617	to	915	10	15.6	-
(Input Port)	915	to	960	10	16.8	-
Attenuation (dB)	1560	to	1610	4	7.1	-
	1805	to	1830	15	21.9	1
	2110	to	2170	15	21.2	-
	2496	to	2547	15	20.3	-
	2640	to	2690	15	21.4	-
Characteristic Impedance (ohm)			50 (Nominal)			nal)

 $Ta = +25 + /-5 ^{\circ}C$ 

# MAXIMUM RATINGS

Parameter		TDK S	Spec	Conditions		
r ai ailletei	arameter			Conditions		
Operating temperature (°C)			+85 °C			
Storage temperature (°C)	-40 to -	+85 °C				
Power Handling (W)		-	4	CW Duty 50%		
		-				
Human Body Model : HBM	@Each Port (V)	-1000	1000	100pF / 1500ohm		
Machine Model : MM	@Each Port (V)	-150	150	200pF / 0ohm		
Charged Device Model : CDM	@Each Port (V)	-500	500	Relative humidity : 60%RH max		


Ambient temperature : +25+/-5°C



Aug. 2017 Ver.1.0 TDK Corporation

# **DEA070960LT-4022A1**

# FREQUENCY CHARACTERISTICS






Aug. 2017 Ver.1.0 TDK Corporation


# **DEA070960LT-4022A1**

# RECOMMENDED LAND PATTERN



Unit: [mm]

#### EVALUATION BOARD






Material & Layer	Thickness
Top Resist	-
Copper Surface Pattern	0.035mm
FR-4	0.10mm
Inner GND	0.018mm
FR-4	0.30mm
Copper Bottom GND	0.035mm

# ENVIRONMENT INFORMATION

RoHS Statement
RoHS Compliance

**TDK Corporation** 

# ■ RECOMMENDED REFLOW PROFILE



t: Time

	Drobe	ating	Soldering					
Preheating			Critical zone (T3 to T4) Peak					
Tei	mp.	Time	Temp. Time		Temp.	Time		
T1	T2	t1	Т3	t2	T4	t3 *		
150°C	200°C	60 to 120sec	217°C	60 to 120sec	240 to 260°C	30 sec Max		

\* t3 : Time within 5°C of actual peak temperature

The maximum number of reflow is 3.

Note: Lead free solder is recommended.

Recommended solder is Sn-3.0Ag-0.5Cu. (M705 by Senju Metal Industry)





Aug. 2017 Ver.1.0 TDK Corporation

# **DEA070960LT-4022A1**

# PACKAGING STYLE

#### **Reel Dimensions**





#### Dimensions (mm)

Α	В	С	D	E	F	G	Н	J	K	t
0.6	8.0	8.0	3.5	1.75	2.0	2.0	4.0	1.5	0.39	0.2
+/-0.03	+/-0.03	+0.3/-0.1	+/-0.05	+/-0.1	+/-0.05	+/-0.05	+/-0.1	+0.1/-0	MAX	+/-0.06

STANDARD PACKAGE QUANTITY
( pieces/reel )
10,000



#### REMINDERS FOR USING THESE PRODUCTS

Before using these products, be sure to request the delivery specifications.

# SAFETY REMINDERS

Please pay sufficient attention to the warnings for safe designing when using these products.

# **⚠** REMINDERS

The products listed on this specification sheet are intended for use in general electronic equipment (AV equipment, telecommunications equipment, home appliances, amusement equipment, computer equipment, personal equipment, office equipment, measurement equipment, industrial robots) under a normal operation and use condition.

The products are not designed or warranted to meet the requirements of the applications listed below, whose performance and/or quality require a more stringent level of safety or reliability, or whose failure, malfunction or trouble could cause serious damage to society, person or property. Please understand that we are not responsible for any damage or liability caused by use of the products in any of the applications below or for any other use exceeding the range or conditions set forth in this specification sheet.

- 1. Aerospace/Aviation equipment
- 2. Transportation equipment (cars, electric trains, ships, etc.)
- 3. Medical equipment
- 4. Power-generation control equipment
- 5. Atomic energy-related equipment
- 6. Seabed equipment
- 7. Transportation control equipment
- 8. Public information-processing equipment
- 9. Military equipment
- 10. Electric heating apparatus, burning equipment
- 11. Disaster prevention/crime prevention equipment
- 12. Safety equipment
- 13. Other applications that are not considered general-purpose applications

When using this product in general-purpose applications, you are kindly requested to take into consideration securing protection circuit/equipment or providing backup circuits, etc., to ensure higher safety.