**ON Semiconductor** 

Is Now

# Onsemi

To learn more about onsemi<sup>™</sup>, please visit our website at <u>www.onsemi.com</u>

onsemi and ONSEMI. and other names, marks, and brands are registered and/or common law trademarks of Semiconductor Components Industries, LLC dba "onsemi" or its affiliates and/or subsidiaries in the United States and/or other countries. onsemi owns the rights to a number of patents, trademarks, copyrights, trade secrets, and other intellectual property. A listing of onsemi product/patent coverage may be accessed at www.onsemi.com/site/pdf/Patent-Marking.pdf. onsemi reserves the right to make changes at any time to any products or information herein, without notice. The information herein is provided "as-is" and onsemi makes no warranty, representation or guarantee regarding the accuracy of the information, product factures, availability, functionality, or suitability of its products for any particular purpose, nor does onsemi assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. Buyer is responsible for its products and applications using onsemi products, including compliance with all laws, regulations and asfety requirements or standards, regardless of any support or applications information provided by onsemi. "Typical" parameters which may be provided in onsemi data sheets and/or by customer's technical experts. onsemi products and actal performance may vary over time. All operating parameters, including "Typicals" must be validated for each customer application by customer's technical experts. onsemi products are not designed, intended, or authorized for use as a critical component in life support systems or any FDA Class 3 medical devices or medical devices with a same or similar classification in a foreign jurisdiction or any devices intended for implantation in the human body. Should Buyer purchase or use onsemi products for any such unintended or unauthorized application, Buyer shall indemnify and hold onsemi and its officers, employees, subsidiari

# **General Purpose Amplifier**

# **NPN Silicon**

#### Features

• These Devices are Pb–Free, Halogen Free/BFR Free and are RoHS Compliant

#### MAXIMUM RATINGS

Rating	Symbol	Value	Unit
Collector-Emitter Voltage	V <sub>CEO</sub>	40	Vdc
Emitter-Base Voltage	V <sub>EBO</sub>	4.0	Vdc
Collector Current – Continuous	Ι <sub>C</sub>	100	mAdc

#### THERMAL CHARACTERISTICS

Characteristic	Symbol	Max	Unit
Total Device Dissipation FR–5 Board, (Note 1) $T_A = 25^{\circ}C$ Derate above 25°C	P <sub>D</sub>	225 1.8	mW mW/°C
Thermal Resistance, Junction-to-Ambient	$R_{\theta JA}$	556	°C/W
Total Device Dissipation Alumina Substrate, (Note 2) $T_A = 25^{\circ}C$ Derate above 25°C	P <sub>D</sub>	300 2.4	mW mW/°C
Thermal Resistance, Junction-to-Ambient	$R_{\thetaJA}$	417	°C/W
Junction and Storage Temperature	T <sub>J</sub> , T <sub>stg</sub>	-55 to +150	°C

Stresses exceeding those listed in the Maximum Ratings table may damage the device. If any of these limits are exceeded, device functionality should not be assumed, damage may occur and reliability may be affected.

1.  $FR-5 = 1.0 \times 0.75 \times 0.062$  in.

2. Alumina = 0.4 x 0.3 x 0.024 in. 99.5% alumina.



# **ON Semiconductor®**

www.onsemi.com





SOT-23 (TO-236) CASE 318 STYLE 6

#### MARKING DIAGRAM



GP = Device Code

M = Date Code\*

= Pb–Free Package

(Note: Microdot may be in either location) \*Date Code orientation and/or overbar may vary depending upon manufacturing location.

#### ORDERING INFORMATION

Device	Package	Shipping <sup>†</sup>
MMBT3416LT3G	SOT-23 (Pb-Free)	10,000/Tape & Reel

†For information on tape and reel specifications, including part orientation and tape sizes, please refer to our Tape and Reel Packaging Specifications Brochure, BRD8011/D.

#### **ELECTRICAL CHARACTERISTICS** (T<sub>A</sub> = 25°C unless otherwise noted)

Characteristic	Symbol	Min	Max	Unit			
OFF CHARACTERISTICS							
Collector-Emitter Breakdown Voltage ( $I_C = 1.0 \text{ mAdc}, I_B = 0$ )	V <sub>(BR)CEO</sub>	40	-	Vdc			
Emitter – Base Breakdown Voltage ( $I_E = 100 \ \mu Adc, I_C = 0$ )	V <sub>(BR)EBO</sub>	4.0	-	Vdc			
Collector Cutoff Current ( $V_{CB} = 25 \text{ Vdc}, I_E = 0$ )	I <sub>CBO1</sub>	-	100	nAdc			
Emitter Cutoff Current ( $V_{EB} = 5.0 \text{ Vdc}, I_C = 0$ )	I <sub>EBO</sub>	1	100	nAdc			
ON CHARACTERISTICS							
DC Current Gain ( $I_C = 2.0 \text{ mAdc}, V_{CE} = 4.5 \text{ Vdc}$ )	h <sub>FE</sub>	75	225	-			
Collector – Emitter Saturation Voltage ( $I_C = 50 \text{ mAdc}, I_B = 3.0 \text{ mAdc}$ )	V <sub>CE(sat)</sub>	-	0.3	Vdc			
Base – Emitter Saturation Voltage (I <sub>C</sub> = 50 mAdc, I <sub>B</sub> = 3.0 mAdc)	V <sub>BE(sat)</sub>	0.6	1.3	Vdc			
SMALL-SIGNAL CHARACTERISTICS							
Collector Cutoff Current ( $V_{CB} = 18 \text{ Vdc}, T_A = 100^{\circ}\text{C}$ )	I <sub>CBO2</sub>	-	15	μAdc			
Small–Signal Current Gain (I <sub>C</sub> = 2.0 mAdc, V <sub>CE</sub> = 4.0 Vdc, f = 1 kHz)	h <sub>FE</sub>	75	-	-			

Product parametric performance is indicated in the Electrical Characteristics for the listed test conditions, unless otherwise noted. Product performance may not be indicated by the Electrical Characteristics if operated under different conditions.

# EQUIVALENT SWITCHING TIME TEST CIRCUITS



Figure 1. Turn-On Time

Figure 2. Turn-Off Time

#### **TYPICAL NOISE CHARACTERISTICS**

 $(V_{CE} = 5.0 \text{ Vdc}, \text{ } \text{T}_{\text{A}} = 25^{\circ}\text{C})$ 



NOISE FIGURE CONTOURS



 $(V_{CE} = 5.0 \text{ Vdc}, T_A = 25^{\circ}\text{C})$ 



Noise Figure is defined as:

NF = 20 log<sub>10</sub> 
$$\left(\frac{e_n^2 + 4KTR_S + I_n^2R_S^2}{4KTR_S}\right)^{1/2}$$

- $e_n\,$  = Noise Voltage of the Transistor referred to the input. (Figure
- $I_n$  = Noise Current of the Transistor referred to the input. (Figure
- K = Boltzman's Constant (1.38 x 10<sup>−23</sup> j/°K)
- T = Temperature of the Source Resistance (°K)
- R<sub>S</sub> = Source Resistance (Ohms)

#### **TYPICAL STATIC CHARACTERISTICS**









30

35



Figure 12. Temperature Coefficients







Figure 11. "On" Voltages

### **TYPICAL DYNAMIC CHARACTERISTICS**









Figure 19A.



Figure 20.

#### DESIGN NOTE: USE OF THERMAL RESPONSE DATA

A train of periodical power pulses can be represented by the model as shown in Figure 19A. Using the model and the device thermal response the normalized effective transient thermal resistance of Figure 19 was calculated for various duty cycles.

To find  $Z_{\theta JA(t)},$  multiply the value obtained from Figure 19 by the steady state value  $R_{\theta JA}.$ 

#### Example:

The MPS3904 is dissipating 2.0 W peak under the following conditions:

 $t_1 = 1.0 \text{ ms}, t_2 = 5.0 \text{ ms}. (D = 0.2)$ 

Using Figure 19 at a pulse width of 1.0 ms and D = 0.2, the reading of r(t) is 0.22.

The peak rise in junction temperature is therefore

 $\Delta T = r(t) \times P_{(pk)} \times R_{\theta JA} = 0.22 \times 2.0 \times 200 = 88^{\circ}C.$ 

For more information, see AN-569.

The safe operating area curves indicate  $I_C-V_{CE}$  limits of the transistor that must be observed for reliable operation. Collector load lines for specific circuits must fall below the limits indicated by the applicable curve.

The data of Figure 20 is based upon  $T_{J(pk)} = 150^{\circ}C$ ;  $T_C$  or  $T_A$  is variable depending upon conditions. Pulse curves are valid for duty cycles to 10% provided  $T_{J(pk)} \leq 150^{\circ}C$ .  $T_{J(pk)}$  may be calculated from the data in Figure 19. At high case or ambient temperatures, thermal limitations will reduce the power that can be handled to values less than the limitations imposed by second breakdown.





© Semiconductor Components Industries, LLC, 2019

ON Semiconductor and are trademarks of Semiconductor Components Industries, LLC dba ON Semiconductor or its subsidiaries in the United States and/or other countries. ON Semiconductor owns the rights to a number of patents, trademarks, copyrights, trade secrets, and other intellectual property. A listing of ON Semiconductor's product/patent coverage may be accessed at <u>www.onsemi.com/site/pdf/Patent-Marking.pdf</u>. ON Semiconductor reserves the right to make changes without further notice to any products herein. ON Semiconductor makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does ON Semiconductor assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. Buyer is responsible for its products and applications using ON Semiconductor products, including compliance with all laws, regulations and safety requirements or standards, regardless of any support or applications information provided by ON Semiconductor. "Typical" parameters which may be provided in ON Semiconductor date sheets and/or specifications can and do vary in different applications and actual performance may vary over time. All operating parameters, including "Typicals" must be validated for each customer application by customer's technical experts. ON Semiconductor does not convey any license under its patent rights nor the rights of others. ON Semiconductor products are not designed, intended, or authorized for use a a critical component in life support systems or any FDA Class 3 medical devices or medical devices with a same or similar classification in a foreign jurisdiction or any devices intended for implantation in the human body. Should Buyer purchase or use ON Semiconductor houteds for any such unintended or unauthorized application, Buyer shall indemnify and hold ON Semiconductor and its officers, employees, subsidiaries

#### PUBLICATION ORDERING INFORMATION

#### LITERATURE FULFILLMENT:

#### TECHNICAL SUPPORT

ON Semiconductor Website: www.onsemi.com

Email Requests to: orderlit@onsemi.com

North American Technical Support: Voice Mail: 1 800–282–9855 Toll Free USA/Canada Phone: 011 421 33 790 2910 Europe, Middle East and Africa Technical Support: Phone: 00421 33 790 2910 For additional information, please contact your local Sales Representative