

# SM4728A~SM4777A


## Surface Mount Silicon Zener Diodes

### Features

- High peak reverse power dissipation
- Low leakage current

### Mechanical Data

- **Case:** SMAF
- **Terminals:** Solderable per MIL-STD-750, Method 2026




All Dimensions in mm

### Maximum Ratings

Parameter	Symbol	Value	Unit
Power Dissipation at $T_L = 75^\circ\text{C}$	$P_{\text{tot}}$	1	W
Forward Voltage at $I_F = 200 \text{ mA}$	$V_F$	1.2	V
Junction Temperature	$T_J$	- 55 to + 150	$^\circ\text{C}$
Storage Temperature Range	$T_{\text{Stg}}$	- 55 to + 150	$^\circ\text{C}$

### Maximum Continuous Power Derating



**TOP DYNAMIC**



# SM4728A~SM4777A

## Electrical Characteristics (Rating at $T_a = 25^\circ\text{C}$ unless otherwise specified)

Type	Marking Code	Zener Voltage Range <sup>1)</sup>			Zener Impedance		Reverse Current		Admissible Zener Current
		$V_{ZT}$ (at $I_{ZT}$ )			$I_{ZT}$	$Z_{ZT}$ (at $I_{ZT}$ )	$I_R$	at $V_R$	
		Min. (V)	Nom. (V)	Max. (V)	(mA)	Max. ( $\Omega$ )	Max. ( $\mu\text{A}$ )	(V)	$I_{ZM}$ (mA)
SM4728A	728A	3.10	3.3	3.50	75	10	100	1	285
SM4729A	729A	3.40	3.6	3.80	69	10	100	1	263
SM4730A	730A	3.70	3.9	4.10	64	9.0	50	1	243
SM4731A	731A	4.06	4.3	4.56	58	9.0	25	1	219
SM4732A	732A	4.50	4.7	4.93	53	8.0	10	1	203
SM4733A	733A	4.84	5.1	5.36	49	7.0	10	1	186
SM4734A	734A	5.32	5.6	5.92	45	5.0	10	2	170
SM4735A	735A	5.86	6.2	6.51	41	2.0	10	3	154
SM4736A	736A	6.46	6.8	7.18	37	3.5	10	4	140
SM4737A	737A	7.12	7.5	7.88	34	4.0	10	5	127
SM4738A	738A	7.79	8.2	8.67	31	4.5	10	6	116
SM4739A	739A	8.60	9.1	9.59	28	5.0	10	7	104
SM4740A	740A	9.50	10	10.5	25	7.0	10	7	95
SM4741A	741A	10.4	11	11.6	23	8.0	5	8	86
SM4742A	742A	11.4	12	12.6	21	9.0	5	9	79
SM4743A	743A	12.4	13	14.1	19	10	5	10	71
SM4744A	744A	14.25	15	15.75	17	14	5	11	61
SM4745A	745A	15.2	16	17.1	16	16	5	12	58
SM4746A	746A	16.8	18	19.2	14	20	5	13	52
SM4747A	747A	19.0	20	21.2	13	22	5	15	47
SM4748A	748A	20.8	22	23.3	12	23	5	17	43
SM4749A	749A	22.8	24	25.2	11	25	5	18	38
SM4750A	750A	25.3	27	28.9	9.5	35	5	21	35
SM4751A	751A	28.2	30	32.0	8.5	40	5	23	31
SM4752A	752A	31.3	33	34.9	7.5	45	5	25	28
SM4753A	753A	34.2	36	37.9	7.0	50	5	27	26
SM4754A	754A	37.2	39	41.5	6.5	60	5	30	24
SM4755A	755A	40.9	43	45.6	6.0	70	1	32	22
SM4756A	756A	44.9	47	49.8	5.5	80	1	35	20
SM4757A	757A	48.6	51	54.0	5.0	95	1	38	18
SM4758A	758A	53.6	56	58.6	4.5	110	1	42	17
SM4759A	759A	58.9	62	65.6	4.0	125	1	47	15
SM4760A	760A	64.6	68	71.7	3.7	150	1	52	14
SM4761A	761A	71.2	75	78.8	3.3	175	1	56	12
SM4762A	762A	77.9	82	87.0	3.0	200	1	62	11
SM4763A	763A	86.0	91	96.0	2.8	250	1	69	10
SM4764A	764A	95.0	100	105	2.5	350	1	76	9.5
SM4765A	765A	104	110	116	2.3	450	1	84	8.6
SM4766A	766A	114	120	127	2.0	550	1	91	7.8
SM4767A	767A	125	135	142	1.9	700	1	100	7.0
SM4768A	768A	140	150	157	1.7	900	1	110	6.3
SM4769A	769A	155	165	172	1.6	1100	1	120	5.8
SM4770A	770A	170	180	191	1.4	1200	1	135	5.2
SM4771A	771A	189	200	211	1.2	1400	1	150	4.7
SM4772A	772A	209	220	231	1.0	1600	1	165	4.3
SM4773A	773A	229	240	251	1.0	1800	1	180	3.9
SM4774A	774A	249	260	271	1.0	2000	1	190	3.7
SM4775A	775A	269	280	291	1.0	2100	1	205	3.4
SM4776A	776A	289	300	315	1.0	2300	1	230	3.1
SM4777A	777A	313	330	346	1.0	2500	1	250	2.8

<sup>1)</sup>  $V_{ZT}$  is tested with pulses ( 20 ms )

**TOP DYNAMIC**

