ON Semiconductor

Is Now

Onsemi

To learn more about onsemi[™], please visit our website at <u>www.onsemi.com</u>

onsemi and ONSEMI. and other names, marks, and brands are registered and/or common law trademarks of Semiconductor Components Industries, LLC dba "onsemi" or its affiliates and/or subsidiaries in the United States and/or other countries. onsemi owns the rights to a number of patents, trademarks, copyrights, trade secrets, and other intellectual property. A listing of onsemi product/patent coverage may be accessed at www.onsemi.com/site/pdf/Patent-Marking.pdf. onsemi reserves the right to make changes at any time to any products or information herein, without notice. The information herein is provided "as-is" and onsemi makes no warranty, representation or guarantee regarding the accuracy of the information, product factures, availability, functionality, or suitability of its products for any particular purpose, nor does onsemi assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. Buyer is responsible for its products and applications using onsemi products, including compliance with all laws, regulations and asfety requirements or standards, regardless of any support or applications information provided by onsemi. "Typical" parameters which may be provided in onsemi data sheets and/or by customer's technical experts. onsemi products and actal performance may vary over time. All operating parameters, including "Typicals" must be validated for each customer application by customer's technical experts. onsemi products are not designed, intended, or authorized for use as a critical component in life support systems or any FDA Class 3 medical devices or medical devices with a same or similar classification in a foreign jurisdiction or any devices intended for implantation in the human body. Should Buyer purchase or use onsemi products for any such unintended or unauthorized application, Buyer shall indemnify and hold onsemi and its officers, employees, subsidiari



ON Semiconductor[®]

FCPF190N60-F152

N-Channel SuperFET[®] II MOSFET 600 V, 20.2 A, 199 m Ω

Features

- 650 V @T_J = 150°C
- Max. R_{DS(on)} = 199 mΩ
- Ultra low gate charge (typ. Q_g = 57 nC)
- Low effective output capacitance (typ. C_{oss}.eff = 160 pF)
- 100% avalanche tested


Description

SuperFET®II MOSFET is ON Semiconductor's first generation of high voltage super-junction (SJ) MOSFET family that is utilizing charge balance technology for outstanding low on-resis-tance and lower gate charge performance. This advanced tech-nology is tailored to minimize conduction loss, provide superior switching performance, and withstand extreme dv/dt rate and higher avalanche energy. Consequently, SuperFET®II MOSFET is suitable for various AC/DC power conversion for system minia-turization and higher efficiency.

Aplications

- LCD / LED / PDP TV Lighting
- Solar Inverter
- AC-DC Power Supply





Absolute Maximum Ratings T_C = 25°C unless otherwise noted

Symbol	Parameter Drain to Source Voltage			FCPF190N60-F152	Unit V	
V _{DSS}				600		
V _{GSS}	Gate to Source Voltage	-DC		±20	V	
		-AC	(f >1Hz)	±30	- V	
ID	Drain Current	-Continuous (T _C = 25 ^o C)		20.2*	Α	
		-Continuous (T _C = 100 ^o C)		12.7*		
I _{DM}	Drain Current	- Pulsed	(Note 1)	60.6*	А	
E _{AS}	Single Pulsed Avalanche Energy		(Note 2)	400	mJ	
I _{AR}	Avalanche Current		(Note 1)	4.0	А	
E _{AR}	Repetitive Avalanche Energy		(Note 1)	2.1	mJ	
dv/dt	Peak Diode Recovery dv/dt (Note 3)			20	V/ns	
	MOSFET dv/dt			100	V/ns	
P _D	Dower Dissinction	$(T_{C} = 25^{\circ}C)$		39	W	
	Power Dissipation	- Derate above 25°C		0.31	W/ºC	
T _J , T _{STG}	Operating and Storage Temperature Range			-55 to +150	°C	
TL	Maximum Lead Temperature for Soldering Purpose, 1/8" from Case for 5 Seconds			300	°C	

*Drain current limited by maximum junction temperature

Thermal Characteristics

Symbol	Parameter	FCPF190N60-F152	Unit	
$R_{ ext{ heta}JC}$	Thermal Resistance, Junction to Case	3.2		
$R_{\theta CS}$	Thermal Resistance, Case to Heat Sink (Typical)	0.5	°C/W	
$R_{ ext{ heta}JA}$	Thermal Resistance, Junction to Ambient	62.5		


Publication Order Number: FCPF190N60-F152/D

Device Marking		Device	Package	Eco Status	Packaging	a Type	Qua	ntity
FCPF19	90N60	FCPF190N60-F152	TO-220F	Green 🥢	Tube		50	
Flectric	al Char	acteristics T _c = 25°C		notod				
Symbol		Parameter		Test Conditions	Min.	Тур.	Max.	Unit
Off Charac	ctoristic					199.	max.	Unit
			$V_{CC} = 0V$	I _D = 10mA, T _J = 25°C	600	-	-	V
BV _{DSS}	Drain to	Source Breakdown Voltage		$I_{\rm D} = 10$ mA, $T_{\rm J} = 150^{\circ}$ C		-	-	V
∆BV _{DSS} ∆TJ	Breakdo	own Voltage Temperature		$I_D = 10$ mA, Referenced to 25°C		0.67	-	V/°C
BV _{DS}	Drain-So Voltage	ource Avalanche Breakdowr	$V_{GS} = 0V,$	I _D = 20A	-	700	-	V
		Voltage		$V_{DS} = 480V, V_{GS} = 0V$			10	
DSS	Zero Ga	Zero Gate Voltage Drain Current		$V_{\rm DS} = 480V, T_{\rm C} = 125^{\circ}{\rm C}$			10	μA
GSS	Gate to	Body Leakage Current		$V, V_{DS} = 0V$	-	-	±100	nA
On Charac		, ,	00					
/ _{GS(th)}		reshold Voltage	Voo = Vo	_S , I _D = 250μA	2.5	-	3.5	V
RDS(on)		rain to Source On Resistance		$V, I_D = 10A$	-	0.17	0.199	Ω
S S S S S S S S S S S S S S S S S S S		Transconductance		$V, I_D = 10A$	-	21	-	S
			103 20	.,				
Dynamic (apacitance			-	2220	2950	pF
Piss			V _{DS} = 25 ¹	V _{DS} = 25V, V _{GS} = 0V		2220		pr pF
C _{oss}		Capacitance Transfer Capacitance	f = 1MHz		-	1630 85	2165 128	pF pF
S _{rss}		Capacitance	V 38(V _{DS} = 380V, V _{GS} = 0V, f = 1MHz		42	120	pF
C _{oss} eff.		e Output Capacitance				160	_	pF
		te Charge at 10V	-	$V_{DS} = 0V \text{ to } 480V, V_{GS} = 0V$ $V_{DS} = 380V, I_D = 10A$ $V_{GS} = 10V$ (Note 4)		57	74	nC
ଦୁ _{g(tot)} ଦୁ _{gs}		Source Gate Charge				9	-	nC
		Drain "Miller" Charge	VGS - 10			21	-	nC
ຊ _{gd} ESR		ent Series Resistance	f = 1MHz			1	_	Ω
			1 - 110112			I	_	52
Switching					-		50	1
d(on)		Delay Time	V 29(V _{DD} = 380V, I _D = 10A		20	50	ns
r		Rise Time		$V, R_{\rm g} = 4.7\Omega$	-	10	30	ns
d(off)		Delay Time				64	138	ns
f		Fall Time		(Nc	- • • • • • • • • • • • • • • • • • • •	5	20	ns
	-	le Characteristics		-		1		
S		m Continuous Drain to Source			-	-	20.2	A
SM		n Pulsed Drain to Source Di	1		-	-	60.6	A
/ _{SD}		Source Diode Forward Volta		$V_{GS} = 0V, I_{SD} = 10A$		-	1.2	V
rr		Recovery Time	$V_{GS} = 0V_{IE}$, I _{SD} = 10A	-	280	-	ns
ג _{רר}	Reverse	Recovery Charge	$u_{\rm F}/u_{\rm I} = 10$	υσημο	-	3.8	-	μC

8

1.4


60




www.onsemi.com 3

160


600




www.onsemi.com 4





FCPF190N60-F152 — N-Channel MOSFET



FCPF190N60-F152 — N-Channel MOSFET







ON Semiconductor and are trademarks of Semiconductor Components Industries, LLC dba ON Semiconductor or its subsidiaries in the United States and/or other countries. ON Semiconductor owns the rights to a number of patents, trademarks, copyrights, trade secrets, and other intellectual property. A listing of ON Semiconductor's product/patent coverage may be accessed at <u>www.onsemi.com/site/pdf/Patent-Marking.pdf</u>. ON Semiconductor reserves the right to make changes without further notice to any products herein. ON Semiconductor makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does ON Semiconductor assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. Buyer is responsible for its products and applications using ON Semiconductor products, including compliance with all laws, regulations and safety requirements or standards, regardless of any support or applications information provided by ON Semiconductor "Typical" parameters which may be provided in ON Semiconductor data sheets and/or specifications can and do vary in different applications and actual performance may vary over time. All operating parameters, including "Typicals" must be validated for each customer application by customer's technical experts. ON Semiconductor does not convey any license under its patent rights of others. ON Semiconductor products are not designed, intended, or authorized for use as a critical component in life support systems or any FDA Class 3 medical devices or medical devices with a same or similar classification in a foreign jurisdiction or any devices intended for implantation in the human body. Should Buyer purchase or use ON Semiconductor haves, damages, and expenses, and reasonable attorney fees arising out of, directly or indirectly, any claim of personal injury or death associated with such uninten

PUBLICATION ORDERING INFORMATION

LITERATURE FULFILLMENT:

Literature Distribution Center for ON Semiconductor 19521 E. 32nd Pkwy, Aurora, Colorado 80011 USA Phone: 303-675-2175 or 800-344-3860 Toll Free USA/Canada Fax: 303-675-2176 or 800-344-3867 Toll Free USA/Canada Email: orderlit@onsemi.com N. American Technical Support: 800–282–9855 Toll Free USA/Canada Europe, Middle East and Africa Technical Support: Phone: 421 33 790 2910

Japan Customer Focus Center Phone: 81–3–5817–1050 ON Semiconductor Website: www.onsemi.com

Order Literature: http://www.onsemi.com/orderlit

For additional information, please contact your local Sales Representative