



SCHMATIC (NON-SHORTING)

## SS-12F99-GXXX

直柄  
G-Switch P/N

Switch Height (mm)
G020=2.0 G030=3.0
G040=4.0 G050=5.0
G065=6.5 G080=8.0
G075=7.5 G080=8.0
G085=8.5 G090=9.0
G095=9.5 G100=10.0

### G-Switch Specification:

Electrical Specifications: 1.0A/DC24V  
 Contact resistance (CR):  $\leq 50\text{m}\Omega$   
 Insulation Resistance(IR):  $\geq 100\text{M}\Omega$  DC250V  
 Compressive strength (WV): AC250V 1minute  
 Operating temperature:  $-25^{\circ}\text{C}\sim+70^{\circ}\text{C}$   
 Storage humidity:  $<85\%\text{RH}$   
 Electrical life: 10,000Cycles.



**G-Switch Electronic (HongKong) CO.,Ltd.**

Unless otherwise specified, Tolerance:  
 X  $\pm 0.30$   
 X.X  $\pm 0.20$   
 X.XX  $\pm 0.15$   
 X.XXX  $\pm 0.10$   
 Angles  $\pm 3^{\circ}$

DESIGN	Bright Lee	DATE	2016.05.29
CHECKED		DATE	
APPROVED		DATE	
<a href="http://www.dg-switch.com">http://www.dg-switch.com</a>			
TEL:	0769-82388879		

DESIGN	Bright Lee	DATE	2016.05.29
CHECKED		DATE	
APPROVED		DATE	
<a href="http://www.dg-switch.com">http://www.dg-switch.com</a>			
TEL:	0769-82388879		

SS-12F99-GXXX

REV:	X1	SCALE:	4:1
SIZE:	A4	SHEET:	1/1
UNIT:	mm		



ROHS  
Compliant  
2002/95/EC

