

## KPESD5V0S1BB

Transient Voltage Suppressors for ESD protection

#### DESCRIPTION

The KPESD5V0S1BB is designed to protect voltage sensitive components from ESD and transient voltage events. Excellent clamping capability, low leakage, and fast response time, make these parts ideal for ESD protection on designs where board space is at a premium.

This device has been specifically designed to protect sensitive components which are connected to data and transmission lines from overvoltage caused by ESD (electrostatic discharge), CDE (Cable Discharge Events), and EFT (electrical fast transients).

#### **ORDERING INFORMATION**

- ♦Device: KPESD5V0S1BB
- ♦Package: SOD-523
- ♦Material: Halogen free
- ♦Packing: Tape & Reel
- ♦Quantity per reel: 3,000pcs

#### **FEATURES**

♦IEC61000-4-2 (ESD) ±15kV (air),

±8kV (contact)

- ♦IEC61000-4-4 (EFT) 40A (5/50ηs)
- ♦Peak power dissipation: 75W (8/20µs)
- ♦Protects one I/O line
- ♦Low clamping voltage
- ♦Working voltages : 5V
- ♦Low leakage current


#### **MACHANICAL DATA**

- ♦SOD-523 package
- ♦Packaging: Tape and Reel
- ♦Reel size: 7 inch
- ♦MSL3

#### APPLICATIONS

- ♦ High Speed Line :USB1.0/2.0, VGA, DVI, SDI,
- ♦ Serial and Parallel Ports
- ♦Notebooks, Desktops, Servers
- ♦Projection TV
- Cellular handsets and accessories
- ♦Portable instrumentation
- ♦Peripherals

#### **PIN CONFIGURATION**



#### **PACKAGE OUTLINE**






## KPESD5V0S1BB

Transient Voltage Suppressors for ESD protection

ABSOLUTE MAXIMUM RATING							
Symbol	Parameter	Value	Units				
V <sub>ESD</sub>	ESD per IEC 61000-4-2 (Air) ESD per IEC 61000-4-2 (Contact)	±30 ±30	kV				
P <sub>PP</sub>	Peak Pulse Power (8/20µs)	75	W				
Т <sub>орт</sub>	Operating Temperature	-40~150	°C				
T <sub>STG</sub>	Storage Temperature	-40~150	°C				

ELECTRICAL CHARACTERISTICS (Tamb=25°C)								
Symbol	Parameter	Test Condition	Min	Тур	Max	Units		
V <sub>RWM</sub>	Reverse Working Voltage				5.0	V		
V <sub>BR</sub>	Reverse Breakdown Voltage	I <sub>T</sub> = 1mA	5.6		9.0	V		
I <sub>R</sub>	Reverse Leakage Current	V <sub>RWM</sub> = 5V			1.0	μA		
Vc	Clamping Voltage	I <sub>PP</sub> = 1A, t <sub>p</sub> = 8/20µs			9.5	V		
Vc	Clamping Voltage	$I_{PPmax} = 5A$ , $t_p = 8/20 \mu s$			15.0	V		
CJ	Junction Capacitance	V <sub>R</sub> = 0V, f = 1MHz			15	pF		

### **ELECTRICAL CHARACTERISTICS CURVE**





# KPESD5V0S1BB Transient Voltage Suppressors for ESD protection

