

# 深圳市钜硕电子有限公司

## SHENZHEN JUSHUO ELECTRONIC CO.,LTD

样品图规

CUSTOMER(客户):		Customer Part NO. (客户部品号): LVDS05A-51P-300-3-10					
		Part Descripon(部品规格): 0.5*51P*300*A 3/3/10/10(0.035×0.3) (60字+20706+60白) 补强板225					
Item	项目	Specification	规格值	<p style="text-align: center;">AWM 20706 105C 60V VW-1 印字面</p> <p style="text-align: center;">IL 印字面</p> <p style="text-align: center;">L 无字面</p> <p style="text-align: center;">居中单面贴L285*W27MM黑色吸波材两端镭射 285MM±2</p> <p style="text-align: center;">无字面</p> <p style="text-align: center;">300±2</p> <p style="text-align: center;">印字面</p> <p style="text-align: center;">S1, S2镀金冲型 (JS14 自动)</p>			
NO. of conductors	导体芯数 N	51					
Pitch	间距 P	0.5±0.05					
Total Pitch	全间距 PT	25±0.08					
Total Length	总长度 L	300±2					
Insulation Length	绝缘长度 IL	294±2					
Margin Width	边缘宽度 M	2±0.08					
Total Width	总宽度 W	29±0.08					
Strip Length	线口长度 S1	3±0.5	镀金冲型				
Strip Length	线口长度 S2	3±0.5	镀金冲型				
Reinforeing tape length	补强板长度 B1	10±1					
Reinforeing tape length	补强板长度 B2	10±1					
Slanting	线口倾斜度 A	≤0.3					
Over lap	冲孔	/					
Terminal thickness	插入厚度 t1	0.32±0.02					
Thickness insulation	线身厚度 t	0.155±0.02					
Conductor thickness	导体厚度 Ct	0.035±0.01					
Conductor width	导体宽度 Cw	0.3±0.03					
Supporting Tapc Color	补强板颜色	蓝色 (Blue)				Storage condition(储存条件): Recommended(推荐)	
PET(Supporting Tapc Color)	补强板规格	0.225mm				Temp: 15° C~25° C(温度15° C~25° C) Humidity: 30~60RH%(湿度30~60RH%)	
PET(Insulation)	绝缘胶规格	0.06mm 印字		Discharge Date 发行日期	Review Date 修订日期	Drawing NO 图纸编号	
PET(Insulation)	绝缘胶规格	0.06mm 白色		2021-07-19			
Rev	版本	A		Drawing by 制图	Checked by 核对	Approved by 确认	
				JACK	John	Dean	

