



ZPDP38B-S60

PIN Photodiode

Descriptions

The ZPDP38B-S60 is a high-output, high-speed silicon PIN photodiode mounted in a sidelooking package. The photodiode is small size, low profile and easy mounting.

Features

- High-output power
- High-speed response
- Wide angular response
- Low-cost
- Pb.Free
- Sidelooking plastic package.

Applications

- Remote control sensors
- Optical switches
- Photocoupler



MAXIMUM RATINGS


Item	Symbol	Ratings	Unit
Reverse voltage	V_R	35	V
Operating temp	T_{opr}	-30~+70	°C
Storage temp	T_{stg}	-40~+80	°C
Soldering temp.* 1	T_{sol}	260	°C



Electro-Optical Characteristics

Item	Symbol	Condition	Min.	Typ.	Max.	Units
Short circuit current	I_{sc}	$EV = 1,000lx * 2$	--	20	--	μA
Dark current	I_d	$V_R = 10V$	--	--	100	nA
Spectral sensitivity	λ	--	880~1050			nm
Peak wavelength	λ_p			1000		nm
Half angle	$\Delta\theta$			± 35		deg



Typical Electrical/Optical/Characteristics Curves





Packing Quantity Specification

1. 1000PCS/1Bag, 5Bags/1Box
2. 10Boxes/1Carton