
# **Switching Diodes**

#### **FEATURES**

- ◆ For surface mount application
- ◆ Fast reverse recovery time
- ◆ Ideal for automated placements
- ◆ Lead free in comply with EU RoHS2011/65/EU directives



Marking:A7

Dated:05/2020

**Rev: 1.0** 

## Absolute Maximum Ratings at 25 °C


Parameter	Symbol	Limits	Units
Maximum Repetitive Peak Reverse Voltage	VRRM	85	V
Reverse Voltage	VR	75	V
Forward Current(double diode load)	lF	200	mA
Non-repetitive Peak Forward surge current at t=1s at t=1ms at t=1us	IFSM	0.5 1 4.5	А
Power Dissipation	PD	350	mW
Operating and Storage Temperature Range	Tj, Tstg	150,-65 ~ +150	°C


#### Characteristics at Ta = 25 °C


Parameter	Symbol	Limits	Units
Maximum Forward Voltage at IF=1mA at IF=10mA at IF=50mA at IF=150mA	VF	0.715 0.855 1 1.25	V
Peak Reverse Current at $V_R$ =25V at $V_R$ =75V at $V_R$ =25V,Tj=150 $^{\circ}$ C at $V_R$ =75V,Tj=150 $^{\circ}$ C	lR	30 1 30 50	uA
Typical Junction Capacitance f=1MHz,VR=4V	Сј	1.5	pF
Maximum Reverse Recovery Time	trr	4	ns




#### **RATINGS AND CHARACTERISTIC CURVES**













Dated:05/2020

## PACKAGE OUTLINE

### **SOT-23**



	Dimensions in millimeter			
Symbol	Min.	Тур.	Max.	
Α	0.900	1.025	1.150	
A1	0.000	0.050	0.100	
b	0.300	0.400	0.500	
С	0.080	0.115	0.150	
D	2.800	2.900	3.000	
E	1.200	1.300	1.400	
HE	2.250	2.400	2.550	
e	1.800	1.900	2.000	
L1	- 10	0.550REF	Alexander of the second	
L	0.300	The second second	0.500	
θ	00		80	



Recommended soldering pad

Dated:05/2020

**Rev: 1.0** 

## **Ordering Information**

Device	Package	Shipping
BAV99	SOT-23	3000/Reel&Tape(7 inch)

