



SCHEMATIC (NON-SHORTING)

SS-22J21-GXXX

直柄
G-Switch P/N

Switch Height (mm)
G020=2.0 G030=3.0
G040=4.0 G050=5.0
G065=6.5 G080=8.0
G075=7.5 G080=8.0
G085=8.5 G090=9.0
G095=9.5 G100=10.0

G-Switch Specification:

Electrical Specifications: 1.0A/DC24V
 Contact resistance (CR): $\leq 50\text{m}\Omega$
 Insulation Resistance(IR): $\geq 100\text{M}\Omega$ DC250V
 Compressive strength (WV): AC250V 1minute
 Operating temperature: $-25^{\circ}\text{C}\sim+70^{\circ}\text{C}$
 Storage humidity: $<85\%\text{RH}$
 Electrical life: 10,000Cycles.



G-Switch Electronic (HongKong) CO., Ltd.

Unless otherwise specified, Tolerance:
 X ± 0.30
 X.X ± 0.20
 X.XX ± 0.15
 X.XXX ± 0.10
 Angles ± 3

DESIGN	Bright Lee	DATE	2016.05.29	Mold code:
CHECKED		DATE		
APPROVED		DATE		
http://www.dg-switch.com				SS-22J21-GXXX
REV:	X1	SCALE:	4:1	UNIT: mm
SIZE:	A4	SHEET:	1/1	
TEL:	0769-82388879			

