# 承 认 书

#### SPECIFICATION FOR APPROVAL

客户(CUSTOMER):	
产品名称(PRODUCT NAME): <u>电磁式蜂鸣器(外部驱动)</u>	
型号(TYPE): <u>YS-MBZ12095C05R42K2700</u>	
客户料号(CUSTOMER NO):	
日期(DATE):2021-09-02	
客户确认:(签章)	
日期:	

# 东莞市锋鸣电子有限公司


电话: 0769-88036425 传真: 0769-85474556


制单: 李琳 业务: 宋浩亮 工程: 黄鑫


## FENGMING TECH OF DONGGUAN CO.,LTD

YS-MBZ12095C05R42K2700

DIMEMSIONS Unit:mm Tolerance: ±0.5








### **SPECIFICATIONS:**


Model NO	YS-MBZ12095C05R42K2700
Rated Voltage	5V
Operating Voltage	3.0~7.0V
Rated Current	Max. 50mA
Coil Resistance	$42\pm4\Omega$
sound Pressure level(dB/2400Hz/at 10cm)	Min.85dB
Resonant Frequency	2700Hz
Operating Temperature	-20℃~+70℃
Storage Temperature	-30℃~+80℃

#### **Acoustic Characteristics:**

The oscillation frequency, current consumption and sound pressure are measured by the measuring instruments shown below



In the measuring test, buzzer is placed as follows:



### **Typical Frequency Response Curve**

