

### **FEATURES**


- · Glass passivated chip junction
- Ideal for surface mounted applications
- · Low leakage
- High forward surge current capability.
- High temperature soldering guaranteed: 260°C/10 seconds at terminals.

### **MECHANICAL DATA**

- Case: Transfer molded plastic
- Epoxy: UL94V 0 rate flame retardant.
- · Polarity: Color band denotes cathode end
- Lead: Plated terminals solderable per MIL STD 202E method 208C
- Weight: 0.002 ounce, 0.057 gram

### MAXIMUM RATINGS AND ELECTRICAL CHARACTERISTICS

- Ratings at 25°C ambient temperature unless otherwise specified
- Single phase, half wave, 60Hz, resistive or inductive load.
- For capacitive load derate current by 20%



CatalogNumber	SYMBOLS	1N4001	1N4002	1N4003	1N4004	1N4005	1N4006	1N4007	UNITS
Maximum Repetitive Peak Reverse Voltage	$V_{RRM}$	50	100	200	400	600	800	1000	Volts
Maximum RMS Voltage	$V_{RMS}$	35	70	140	280	420	560	700	Volts
Maximum DC Blocking Voltage	$V_{DC}$	50	100	200	400	600	800	1000	Volts
Maximum Average Forward Rectified Current, at $T_A = 75^{\circ}C$	I <sub>(AV)</sub>	1.0							Amp
Peak Forward Surge Current 8.3ms single half sine-wave superimposed on rated load (JEDEC Method)	$I_{\mathrm{FSM}}$	30							Amps
Maximum Instantaneous Forward Voltage Drop at 1.0A	$V_{\mathrm{F}}$	1.1							Volts
Maximum DC Reverse Current at rated DC blocking voltage $\frac{T_C = 25^{\circ}C}{T_A = 125^{\circ}C}$	$I_R$	5.0 50							$\mu$ A
Maximum Full Load Reverse Current, full cycle average at $T_A = 75^{\circ}C$	$I_{R(AV)}$	30							$\mu$ A
Typical Junction Capacitance (Note 1)	$C_{J}$	15							pF
Typical Thermal Resistane (Note 2)	$R_{ heta JA}$	75							°C/w
Operating and Storage Temperature Range	$T_J, T_{STG}$	(-65 to +175)							$^{\circ}\!\mathbb{C}$


## **NOTES:**

- 1. Measured at 1.0 MHz and applied aberage voltage of 4.0 volts.
- 2. 6.0 X 6.0mm2 copper pads to each terminal.


www.yongyutai.com PAGE 1




FIG.1-TYPICAL FORWARD CURRENT DERATING CURVE AVERAGE FORWARD CURRENT, 1.0 0.8 3 0.6 0.4 Resistive or 0.2 0.375"(9.5mm) Lead Length 0 75 175 100 50 AMBIENT TEMPERATURE, ( C)










# FIG.5-TYPICAL JUNCTION CAPACITANCE



www.yongyutai.com PAGE 2