


# **3-TERMINAL 0.3A POSITIVE VOLTAGE REGULATORS**

This series of fixed-voltage monolithic integrated-circuit voltage regulators is designed for a wide range of applications. These applications include on-card regulation for elimination of noise and distribution problems associated with single-point regulation. In addition, they can be used with power-pass elements to make high current voltage regulators. Each of these regulators can deliver up to 100mA output current.

The internal limiting and thermal shutdown features of these regulators make them essentially immune to overload.

When used as a replacement for a zener diode-resistor combination, an effective improvement in output impedance can be obtained together with lower-bias current.




#### **Features**

- Output current Up to 300mA
- No External Components
- Internal Thermal Overload Protection
- •Internal Short-Circuit Limiting
- Output Voltage of 5V, 6V, 8V, 9V, 10V, 12V, 15V, 18V and 24V


# **ORDERING INFORMATION**

Device	Operating Temperature Range	Package	Packing
HT78HXXATZ	T <sub>A</sub> = -40° to 125° C	TO-92	Bulk
HT78HXXARTZ		TO-92	Taping
HT78HXXARZ		SO-8	Tape & Reel
HT78HXXARDZ		SOT-89	Tape & Reel


# **Pin Configuration**



**SO-8** 



**SOT-89** 





### Absolute Maximum Ratings

Charac	teristic	Symbol	Value	Unit
	HT78H05 ~ HT78H10		30	
Input voltage	HT78H12 ~ HT78H18	VI	35	V
	HT78H24		40	
	TO-92		625	
Power Dissipation	SOT-89	Pd	500	mW
	SOP-8		625	
Operating junction ter	mperature	Topr	-40 ~ +150	
Storage temperature		Tstg	-65 ~ +150	°C
Soldering temperatur	e and time	Tsol	260/10sec	


<sup>\*</sup> Stresses beyond those listed under "absolute maximum ratings" may cause permanent damage to the device. These are stress ratings only and functional operation of the device at these or any other conditions beyond those indicated under "recommended operating conditions" is not implied.

Exposure to absolute-maximum-rated conditions for extended periods may affect device reliability.

### RECOMMENDED OPERATING CONDITIONS

78	Hxx	Min.	Max.	Unit
	HT78H05	7	20	
	HT78H06	8	20	
	HT78H08	10.5	23	
	HT78H09	11.5	24	
Input voltage, VI	HT78H10	12.5	25	V
	HT78H12	14.5	27	
	HT78H15	17.5	30	
	HT78H18	20.5	33	
	HT78H24	26.5	39	
Output current, Io			300	mA
Operating virtual junction tem	perature, Tj	-40	125	°C

### TYPICAL APPLICATION



#### Notes

- 1. To specify an output voltage, substitute voltage for "XX"
- 2. Bypass capacitors are recommended for optimum stability and transient response and should be located as close as possible to the regulators.



### HT78H05 ELECTRICAL CHARACTERISTICS

(At specified virtual junction temperature, Vi=10V, lo=40mA (unless otherwise noted)

Characteistic	Symbol	Test cond	Test condition *		Тур.	Max.	Unit
		25°C		4.8	5	5.2	
Output voltage **	Vout	1 mA≤ lo≤ 40 mA 7V≤ VI≤ Vmax	-40 ~ 125°C	4.75	5	5.25	V
		1 mA≤lo≤ 70 mA		4.75	5	5.25	
Line regulation	Reg line	7≤ VI≤ 20V	25°C		32	150	m\/
Line regulation	Reg line	8≤ VI≤ 20V	250		26	100	. mV
	Reg load	1 mA≤ lo≤ 100 mA	25°C		15	60	mV
Load regulation	Reg load	1 mA≤ lo≤ 40 mA			8	30	
Bias current			25°C		3.8	6	mA
bias current	l <sub>B</sub>		125°C			5.5	- mA
Bias current change	ΔI <sub>B</sub>	9≤ VI≤ 20V	-40 ~ 125°C			1.5	mA
bias current change	ΔiB	1 mA≤ lo≤ 40 mA	40 ~ 125 C			0.1	- mA
Output noise voltage	V	10 Hz≤ f≤ 100 kHz	25°C		42		μV
Ripple rejection	RR	8≤ VI≤ 20V f=120 Hz	25°C	41	49		dB
Dropout voltage	V <sub>D</sub>		25°C		1.7		V

#### Notes

Thermal effects must be taken into account separately.

<sup>\*.</sup> Pulse testing techniques are used to maintain the junction temperature as close to the ambient temperature as possible.

<sup>\*\*.</sup> This specification applies only for DC power dissipation permitted by absolute maximum ratings.



### HT78H06 ELECTRICAL CHARACTERISTICS

(At specified virtual junction temperature, Vi=12V, lo=40mA (unless otherwise noted)

Characteistic	Symbol	Test cond	ition *	Min	Тур.	Max.	Unit	
			25°C	5.75	6	6.25		
Output voltage **	Vout	1 mA≤ lo≤ 40 mA 8V≤ VI≤ 20V	-40 ~ 125°C	5.7	6	6.3	V	
		1 mA≤lo≤ 70 mA		5.7	6	6.3		
Line regulation	Reg line	8≤ VI≤ 20V	25°C -		35	175	m\/	
Line regulation	Regille	9≤ VI≤ 20V			29	125	. mV	
Land an autotion	Reg load	1 mA≤ lo≤ 100 mA	25°C		16	80	mV	
Load regulation	Keg load	1 mA≤ lo≤ 40 mA	23 0		9	40		
Bias current		I <sub>B</sub>		25°C		3.9	6	A
Dias current	ıR		125°C			5.5	- mA	
Bias current change	ΔI <sub>B</sub>	9≤ VI≤ 20V	-40 ~ 125°C			1.5	A	
bias current change	ΔiB	1 mA≤ lo≤ 40 mA	40 ~ 125 C			0.1	- mA	
Output noise voltage	V	10 Hz≤ f≤ 100 kHz	25°C		46		μV	
Ripple rejection	RR	9≤ VI≤ 19V f=120 Hz	25°C	40	48		dB	
Dropout voltage	V <sub>D</sub>		25°C		1.7		V	

#### Notes

Thermal effects must be taken into account separately.

<sup>\*.</sup> Pulse testing techniques are used to maintain the junction temperature as close to the ambient temperature as possible.

<sup>\*\*.</sup> This specification applies only for DC power dissipation permitted by absolute maximum ratings.



# HT78H08 ELECTRICAL CHARACTERISTICS

(At specified virtual junction temperature, Vi=14V, lo=40mA (unless otherwise noted)

Characteistic	Symbol	Test cond	ition *	Min	Тур.	Max.	Unit
			25°C	7.7	8	8.3	
Output voltage **	Vout	1 mA≤ lo≤ 40 mA 10.5V≤ VI≤ 23V	-40 ∼ 125°C	7.6	8	8.4	V
		1 mA≤lo≤ 70 mA		7.6	8	8.4	
Line regulation	Reg line	10.5≤ VI≤ 23V	25°C		42	175	mV
Line regulation	Neg IIIIe	11≤ VI≤ 23V	250		36	125	IIIV
	Reg load	1 mA≤ lo≤ 100 mA	25°C		18	80	. mV
Load regulation	Reg load	1 mA≤ lo≤ 40 mA			10	40	
	ı		25°C		4	6	
Bias current	<b> </b> B		125℃			5.5	mA
Diagram at all and	A I-	11≤ VI≤ 23V	40 405°0			1.5	
Bias current change	Δl <sub>B</sub>	1 mA≤ lo≤ 40 mA	40 ~ 125℃			0.1	- mA
Output noise voltage	V <sub>N</sub>	10 Hz≤ f≤ 100 kHz	25°C		54		μV
Ripple rejection	RR	13≤ VI≤ 23V f=120 Hz	25°C	37	46		dB
Dropout voltage	V		25°C		1.7		V

#### Notes

\*. Pulse testing techniques are used to maintain the junction temperature as close to the ambient temperature as possible.

Thermal effects must be taken into account separately.

All characteristics are measured with a 0.33  $\mu$ F capacitor across the input and a 0.1  $\mu$ F capacitor across the output.

\*\*. This specification applies only for DC power dissipation permitted by absolute maximum ratings.



# HT78H09 ELECTRICAL CHARACTERISTICS

(At specified virtual junction temperature, Vi=14V, lo=40mA (unless otherwise noted)

Characteistic	Symbol	Test cond	ition *	Min	Тур.	Max.	Unit
			25°C	806	9	9.4	
Output voltage **	Vout	1 mA≤ lo≤ 40 mA 12V≤ VI≤ 24V	-40 ~ 125°C	8.55	9	9.45	V
		1 mA≤lo≤ 70 mA		8.55	9	9.45	
Line regulation	Reg line	12≤ VI≤ 24V	25°C		45	175	m\/
Line regulation	ixeg iiile	13≤ VI≤ 24V	250		40	125	mV
Load regulation	Reg load	1 mA≤ lo≤ 100 mA	25°C		19	90	. mV
Load regulation	Reg load	1 mA≤ lo≤ 40 mA			11	40	
			25°C		4.1	6	
Bias current	<b> </b>   B		125°C			5.5	mA
Dies summert als annu	۸۱-	13≤ VI≤ 24V	40 405°O			1.5	
Bias current change	Δl <sub>B</sub>	1 mA≤ lo≤ 40 mA	40 ~ 125℃			0.1	- mA
Output noise voltage	V <sub>N</sub>	10 Hz≤ f≤ 100 kHz	25°C		58		μΝ
Ripple rejection	RR	13≤ VI≤ 23V f=120 Hz	25°C	38	45		dB
Dropout voltage	V		25°C		1.7		V

#### Notes

\*. Pulse testing techniques are used to maintain the junction temperature as close to the ambient temperature as possible.

Thermal effects must be taken into account separately.

All characteristics are measured with a 0.33  $\mu$ F capacitor across the input and a 0.1  $\mu$ F capacitor across the output.

\*\*. This specification applies only for DC power dissipation permitted by absolute maximum ratings.



# HT78H10 ELECTRICAL CHARACTERISTICS

(At specified virtual junction temperature, Vi=16V, lo=40mA (unless otherwise noted)

Characteistic	Symbol	Test condi	ition *	Min	Тур.	Max.	Unit
			25°C	9.6	10	10.4	
Output voltage **	Vout	1 mA≤ lo≤ 40 mA 13V≤ VI≤ 25V	-40 ~ 125°C	9.5	10	10.5	V
		1 mA≤lo≤ 70 mA		9.5	10	10.5	
Line regulation	Reg line	13≤ VI≤ 25V	25°C		51	175	mV
Line regulation	Neg IIIIe	14≤ VI≤ 25V	250		42	125	iliv
Load regulation	Reg load	1 mA≤ lo≤ 100 mA	25°C		20	90	mV
Load regulation	Load regulation Reg load	1 mA≤ lo≤ 40 mA			11	40	
	ı		25°C		4.2	6	
Bias current	B B		125°C			5.5	mA
Bias current change	ΔI <sub>B</sub>	14≤ VI≤ 25V	-40 ~ 125°C			1.5	mΛ
bias current change	ΔIR	1 mA≤ lo≤ 40 mA	-40 ~ 125 C			0.1	- mA
Output noise voltage	V <sub>N</sub>	10 Hz≤ f≤ 100 kHz	25°C		62		μΝ
Ripple rejection	RR	15≤ VI≤ 25V f=120 Hz	25°C	37	44		dB
Dropout voltage	$V_{D}$		25°C		1.7		V

#### Notes

<sup>\*.</sup> Pulse testing techniques are used to maintain the junction temperature as close to the ambient temperature as possible.

Thermal effects must be taken into account separately.

<sup>\*\*.</sup> This specification applies only for DC power dissipation permitted by absolute maximum ratings.



# HT78H12 ELECTRICAL CHARACTERISTICS

(At specified virtual junction temperature, Vi=17V, lo=40mA (unless otherwise noted)

Characteistic	Symbol	Test condi	ition *	Min	Тур.	Max.	Unit
			25°C	11.5	12	12.5	
Output voltage **	Vout	1 mA≤ lo≤ 40 mA 14V≤ VI≤ 27V	-40 ~ 125°C	11.4	12	12.6	V
	1 mA≤lo≤ 70 mA	11.4	12	12.6			
Line regulation	Reg line	14.5≤ VI≤ 27V	25°C -		55	250	m\/
Line regulation	Neg IIIIe	16≤ VI≤ 27V			49	200	mV
Load regulation	Reg load	1 mA≤ lo≤ 100 mA	25°C		22	100	. mV
Load regulation	iveg load	1 mA≤ lo≤ 40 mA			13	50	
	I		25°C		4.3	6.5	
Bias current	B B		125°C			6	mA
Bias current change	ΔI <sub>B</sub>	16≤ VI≤ 27V	-40 ∼ 125°C			1.5	mA
bias current change	ΔIR	1 mA≤ lo≤ 40 mA	-40 ~ 125 C			0.1	IIIA
Output noise voltage	V <sub>N</sub>	10 Hz≤ f≤ 100 kHz	25°C		70		μΝ
Ripple rejection	RR	15≤ VI≤ 25V f=120 Hz	25°C	37	42		dB
Dropout voltage	V <sub>D</sub>		25°C		1.7		V

#### Notes

<sup>\*.</sup> Pulse testing techniques are used to maintain the junction temperature as close to the ambient temperature as possible.

Thermal effects must be taken into account separately.

<sup>\*\*.</sup> This specification applies only for DC power dissipation permitted by absolute maximum ratings.



# HT78H15 ELECTRICAL CHARACTERISTICS

(At specified virtual junction temperature, Vi=19V, lo=40mA (unless otherwise noted)

Characteistic	Symbol	Test condi	ition *	Min	Тур.	Max.	Unit
			25°C	14.4	15	15.6	
Output voltage **	Vout	1 mA≤ lo≤ 40 mA 17.5V≤ VI≤ 30V	-40 ~ 125°C	14.25	15	15.75	V
		1 mA≤lo≤ 70 mA	14.25	15	15.75		
Line regulation	Reg line	17.5≤ VI≤ 30V	. 25℃		65	300	mV
Line regulation	ixeg iiiie	19≤ VI≤ 30V	250		58	250	III V
Load regulation	Reg load	1 mA≤ lo≤ 100 mA	25°C		25	150	. mV
Load regulation	Load regulation Reg load	1 mA≤ lo≤ 40 mA			15	75	
	ı		25°C		4.2	6.5	
Bias current	B B		125°C			6	mA
Bias current change	ΔI <sub>B</sub>	19≤ VI≤ 30V	-40 ∼ 125°C			1.5	mΛ
bias current change	ΔIB	1 mA≤ lo≤ 40 mA	-40 ~ 125 C			0.1	- mA
Output noise voltage	V <sub>N</sub>	10 Hz≤ f≤ 100 kHz	25°C		82		μΝ
Ripple rejection	RR	18.5≤ VI≤ 28.5V f=120 Hz	25°C	37	44		dB
Dropout voltage	$V_{D}$		25°C		1.7		V

#### Notes

<sup>\*.</sup> Pulse testing techniques are used to maintain the junction temperature as close to the ambient temperature as possible.

Thermal effects must be taken into account separately.

<sup>\*\*.</sup> This specification applies only for DC power dissipation permitted by absolute maximum ratings.



# HT78H18 ELECTRICAL CHARACTERISTICS

(At specified virtual junction temperature, Vi=23V, lo=40mA (unless otherwise noted)

Characteistic	Symbol	Test cond	lition *	Min	Тур.	Max.	Unit
			25°C	17.3	18	18.7	
Output voltage **	Vout	1 mA≤ lo≤ 40 mA 20.5V≤ VI≤ 33V	-40 ~ 125°C	17.1	18	18.9	V
		1 mA≤lo≤ 70 mA		17.1	18	18.9	
Line regulation	Reg line	20.5≤ VI≤ 33V	_ 25°C -		70	360	m\/
Line regulation	Regille	22≤ VI≤ 33V			64	300	. mV
	Reg load	1 mA≤ lo≤ 100 mA	. 25°C		27	180	- mV
Load regulation	Reg load	1 mA≤ lo≤ 40 mA			19	90	
	ı		25°C		4.7	6.5	
Bias current	<b> </b> B		125°C			6	mA
D'an annual abanca	A.I.	22≤ VI≤ 33V	40 405°0			1.5	
Bias current change	Δl <sub>B</sub>	1 mA≤ lo≤ 40 mA	40 ∼ 125°C			0.1	- mA
Output noise voltage	V	10 Hz≤ f≤ 100 kHz	25°C		82		μΝ
Ripple rejection	RR	21.5≤ VI≤ 31.5V f=120 Hz	25°C	32	36		dB
Dropout voltage	V <sub>D</sub>		25°C		1.7		V

#### Notes

Thermal effects must be taken into account separately.

<sup>\*.</sup> Pulse testing techniques are used to maintain the junction temperature as close to the ambient temperature as possible.

<sup>\*\*.</sup> This specification applies only for DC power dissipation permitted by absolute maximum ratings.



# HT78H24 ELECTRICAL CHARACTERISTICS

(At specified virtual junction temperature, Vi=26V, lo=40mA (unless otherwise noted)

Characteistic	Symbol	Test cond	lition *	Min	Тур.	Max.	Unit
			25°C	23	24	25	
Output voltage **	Vout	1 mA≤ lo≤ 40 mA 26.5V≤ VI≤ 39V	-40 ~ 125°C	22.8	24	25.2	V
		1 mA≤lo≤ 70 mA		22.8	24	25.2	
Line regulation	Reg line	26.5≤ VI≤ 39V	_ 25°C _		95	480	m\/
Line regulation	Neg IIIIe	29≤ VI≤ 39V			78	400	mV
Landan sulation	Reg load	1 mA≤ lo≤ 100 mA	25°C		41	240	. mV
Load regulation	iveg load	1 mA≤ lo≤ 40 mA			28	120	
	ı		25°C		4.8	6.5	
Bias current	B B		125°C			6	mA
Bias current change	ΔI <sub>B</sub>	28≤ VI≤ 39V	-40 ∼ 125°C			1.5	mΛ
bias current change	ΔIB	1 mA≤ lo≤ 40 mA	-40 ~ 125 C			0.1	- mA
Output noise voltage	V	10 Hz≤ f≤ 100 kHz	25°C		82		μΝ
Ripple rejection	RR	27.5≤ VI≤ 37.5V f=120 Hz	25°C	30	33		dB
Dropout voltage	V <sub>D</sub>		25°C		1.7		V


#### Notes


- \*. Pulse testing techniques are used to maintain the junction temperature as close to the ambient temperature as possible.

  Thermal effects must be taken into account separately.
  - All characteristics are measured with a 0.33  $\mu$ F capacitor across the input and a 0.1  $\mu$ F capacitor across the output.
- \*\*. This specification applies only for DC power dissipation permitted by absolute maximum ratings.



# • TO-92








# SO-8

# D SUFFIX SOIC (MS - 012AA)



### **NOTES:**

- 1. Dimensions A and B do not include mold flash or protrusion.
- 2. Maximum mold flash or protrusion 0.15 mm (0.006) per side for A; for B 0.25 mm (0.010) per side.



_		
	Dimension, mm	
Symbol	MIN	MAX
A	4.8	5
В	3.8	4
C	1.35	1.75
D	0.33	0.51
F	0.4	1.27
G	1.27	
Н	5.72	
J	0 °	8°
K	0.1	0.25
M	0.19	0.25
P	5.8	6.2
R	0.25	0.5