


<b>GLASS PASSIVATED BRIDGE RECTIFIERS</b>	<p>REVERSE VOLTAGE - <b>50 to 1000</b>Volts</p> <p>FORWARD CURRENT - <b>4.0</b> Amperes</p>
<p><b>FEATURES</b></p> <ul style="list-style-type: none"> <li>● Surge overload rating -150 amperes peak</li> <li>● Ideal for printed circuit board</li> <li>● Reliable low cost construction utilizing molded plastic technique</li> <li>● Plastic material has U/L flammability classification 94V-0</li> <li>● Mounting position:Any</li> </ul>	 <p style="text-align: center;">Dimensions in inches and (millimeters)</p>

## MAXIMUM RATINGS AND ELECTRICAL CHARACTERISTICS

Rating at 25°C ambient temperature unless otherwise specified.  
 Single phase, half wave ,60Hz, resistive or inductive load.  
 For capacitive load, derate current by 20%

CHARACTERISTICS	SYMBOL	GBU4005	GBU401	GBU402	GBU404	GBU406	GBU408	GBU410	UNIT	
Maximum Recurrent Peak Reverse Voltage	V <sub>RRM</sub>	50	100	200	400	600	800	1000	V	
Maximum RMS Voltage	V <sub>RMS</sub>	30	70	140	280	420	560	700	V	
Maximum DC Blocking Voltage	V <sub>DC</sub>	50	100	200	400	600	800	1000	V	
Maximum Average Forward Rectified Current @ T <sub>c</sub> =100°C (without heatsink)	I <sub>(AV)</sub>					4.0				A
Peak Forward Surge Current 8.3ms Single Half Sine-Wave Super Imposed on Rated Load (JEDEC Method)	I <sub>FSM</sub>					2.4				A
Maximum Forward Voltage at 4.0A DC	V <sub>F</sub>					1.1				V
Maximum DC Reverse Current at Rated DC Blocking Voltage	I <sub>R</sub>					10.0				uA
						500				
I <sup>2</sup> t Rating for Fusing (t<8.3ms)	I <sup>2</sup> t					93				A <sup>2</sup> s
Typical Junction Capacitance Per Element (Note1)	C <sub>J</sub>					45				pF
Typical Thermal Resistance (Note2)	R <sub>θJC</sub>					2.2				°C/W
Operating Temperature Range	T <sub>J</sub>					-55 to +150				°C
Storage Temperature Range	T <sub>STG</sub>					-55 to +150				°C

NOTES: 1.Measured at 1.0MHz and applied reverse voltage of 4.0V DC.  
 2.Device mounted on 50mm\*50mm\*1.6mm cu plate heatsink.

FIG.1-FORWARD CURRENT DERATING CURVE




FIG.2-MAXIMUM NON-REPETITIVE SURGE CURRENT




FIG.3-TYPICAL JUNCTION CAPACITANCE




FIG.4-TYPICAL FORWARD CHARACTERISTICS




FIG.5-TYPICAL REVERSE CHARACTERISTICS

