

## N-Channel Enhancement Mode Field Effect Transistor

### Product Summary



- $V_{DS}$  30V
- $I_D$  50A
- $R_{DS(ON)}$  ( at  $V_{GS}=10V$ ) <6.0 mohm
- $R_{DS(ON)}$  ( at  $V_{GS}=4.5V$ ) <8.0 mohm
- 100% UIS Tested
- 100%  $\nabla V_{DS}$  Tested

### General Description


- Trench Power LV MOSFET technology
- Excellent package for heat dissipation
- High density cell design for low  $R_{DS(ON)}$

### Applications

- High current load applications
- Load switching
- Hard switched and high frequency circuits
- Uninterruptible power supply
- **Marking** : Q50N03B



**DFN3.3X3.3**



### Absolute Maximum Ratings ( $T_A=25^\circ\text{C}$ unless otherwise noted)

Parameter		Symbol	Limit	Unit
Drain-source Voltage		$V_{DS}$	30	V
Gate-source Voltage		$V_{GS}$	$\pm 20$	V
Drain Current	$T_C=25^\circ\text{C}$	$I_D$	50	A
	$T_C=100^\circ\text{C}$		35	
Pulsed Drain Current <sup>A</sup>		$I_{DM}$	190	A
Total Power Dissipation	$T_C=25^\circ\text{C}$	$P_D$	30	W
	$T_C=100^\circ\text{C}$		15	W
Single Pulse Avalanche Energy <sup>B</sup>		$E_{AS}$	225	mJ
Thermal Resistance Junction-to-Case <sup>C</sup>		$R_{\theta JC}$	5	$^\circ\text{C}/\text{W}$
Junction and Storage Temperature Range		$T_J, T_{STG}$	-55~+175	$^\circ\text{C}$

## Electrical Characteristics (T<sub>J</sub>=25°C unless otherwise noted)

Parameter	Symbol	Conditions	Min	Typ	Max	Units
<b>Static Parameter</b>						
Drain-Source Breakdown Voltage	BV <sub>DSS</sub>	V <sub>GS</sub> = 0V, I <sub>D</sub> =250μA	30			V
Zero Gate Voltage Drain Current	I <sub>DSS</sub>	V <sub>DS</sub> =30V, V <sub>GS</sub> =0V			1	μA
Gate-Body Leakage Current	I <sub>GSS</sub>	V <sub>GS</sub> = ±20V, V <sub>DS</sub> =0V			±100	nA
Gate Threshold Voltage	V <sub>GS(th)</sub>	V <sub>DS</sub> = V <sub>GS</sub> , I <sub>D</sub> =250μA	1.0	1.5	2.5	V
Static Drain-Source On-Resistance	R <sub>DS(ON)</sub>	V <sub>GS</sub> = 10V, I <sub>D</sub> =15A		4.9	6.0	mΩ
		V <sub>GS</sub> = 4.5V, I <sub>D</sub> =15A		6.3	8.0	
Diode Forward Voltage	V <sub>SD</sub>	I <sub>S</sub> =20A, V <sub>GS</sub> =0V			1.2	V
Maximum Body-Diode Continuous Current	I <sub>S</sub>				50	A
<b>Dynamic Parameters</b>						
Input Capacitance	C <sub>iss</sub>	V <sub>DS</sub> =15V, V <sub>GS</sub> =0V, f=1MHZ		2150		pF
Output Capacitance	C <sub>oss</sub>			435		
Reverse Transfer Capacitance	C <sub>rss</sub>			252		
<b>Switching Parameters</b>						
Total Gate Charge	Q <sub>g</sub>	V <sub>GS</sub> =10V, V <sub>DS</sub> =15V, I <sub>D</sub> =20A		52.8		nC
Gate-Source Charge	Q <sub>gs</sub>			12.3		
Gate-Drain Charge	Q <sub>gd</sub>			10.8		
Reverse Recovery Charge	Q <sub>rr</sub>	I <sub>F</sub> =25A, di/dt=100A/us		28		
Reverse Recovery Time	t <sub>rr</sub>			27		
Turn-on Delay Time	t <sub>D(on)</sub>	V <sub>GS</sub> =10V, V <sub>DD</sub> =20V, I <sub>D</sub> =4A, R <sub>L</sub> =1Ω R <sub>GEN</sub> =3Ω		9		ns
Turn-on Rise Time	t <sub>r</sub>			15.5		
Turn-off Delay Time	t <sub>D(off)</sub>			29		
Turn-off fall Time	t <sub>f</sub>			9		

A. Pulse Test: Pulse Width ≤ 300us, Duty cycle ≤ 2%.

B. T<sub>J</sub>=25°C, V<sub>DS</sub>=30V V<sub>DD</sub>=25V V<sub>GS</sub>=10V L=1mH.

C. R<sub>θJA</sub> is the sum of the junction-to-case and case-to-ambient thermal resistance, where the case thermal reference is defined as the solder mounting surface of the drain pins. R<sub>θJC</sub> is guaranteed by design, while R<sub>θJA</sub> is determined by the board design. The maximum rating presented here is based on mounting on a 1 in 2 pad of 2oz copper.

## Typical Performance Characteristics




Figure1. Output Characteristics




Figure2. Transfer Characteristics




Figure3. Capacitance Characteristics




Figure4. Gate Charge




Figure5. Drain-Source on Resistance




Figure6. Drain-Source on Resistance




Figure7. Safe Operation Area






Figure8. Switching wave

## DFN3.3X3.3 Package information



A	B	C	C1
3.25±0.05	3.25±0.05	0.8±0.05	0.2±0.02
C2	D	E	F
0.05Max	1.9±0.1	2.35±0.15	0.45±0.05
G	H	e	
0.3±0.05	0.35±0.05	0.65±0.05	
: mm			

