

SMD Power Inductor

CDRH10D68R/T125



特点

- Ferrite drum core construction
- Magnetically shielded
- L×W×H:10.6×10.6×7.0 mm Max.
- Product weight: 2.7g(Ref.)
- Moisture Sensitivity Level: 1
- Qualified with AEC-Q200



环境规格

- Operating Temperature: -40°C to +125°C (including self-heating)
- Storage temperature range: -40°C~+125°C


包装

- Carrier tape and reel packaging


用途

- High temp and high reliability automotive applications


外形尺寸 - [mm]



推荐焊盘尺寸 - [mm]



接线图 (底面)





电气特性规格

品名	电感值 [within] (μ H) ※1	直流电阻 (20℃) Max. (Typ.) (m Ω)	饱和电流 (A) Max. (Typ.) ※2	温度上升电流 (A) Max. (Typ.) ※3
CDRH10D68RT125NP-1R5NC	1.50 \pm 30%	6.10 (4.90)	11.00 (15.00)	10.50 (12.00)
CDRH10D68RT125NP-2R2NC	2.20 \pm 30%	7.10 (5.70)	10.50 (13.60)	9.50 (11.60)
CDRH10D68RT125NP-3R3NC	3.30 \pm 30%	8.50 (6.80)	7.80 (10.30)	8.30 (9.40)
CDRH10D68RT125NP-4R7NC	4.70 \pm 30%	9.90 (7.90)	7.15 (8.52)	7.60 (8.52)
CDRH10D68RT125NP-6R2NC	6.20 \pm 30%	14.20 (11.30)	5.95 (7.40)	6.45 (7.30)
CDRH10D68RT125NP-7R5NC	7.50 \pm 30%	16.40 (13.00)	5.50 (7.00)	5.55 (6.30)
CDRH10D68RT125NP-100PC	10.00 \pm 25%	21.40 (17.10)	4.40 (5.70)	4.40 (4.90)
CDRH10D68RT125NP-150PC	15.00 \pm 25%	30.60 (24.50)	3.60 (4.68)	3.60 (4.05)
CDRH10D68RT125NP-220PC	22.00 \pm 25%	39.10 (31.30)	3.10 (4.15)	3.10 (3.51)
CDRH10D68RT125NP-330PC	33.00 \pm 25%	59.10 (47.30)	2.60 (3.13)	2.60 (2.92)
CDRH10D68RT125NP-470PC	47.00 \pm 25%	88.30 (70.60)	2.00 (2.62)	2.00 (2.34)
CDRH10D68RT125NP-680PC	68.00 \pm 25%	125 (100)	1.80 (2.20)	1.80 (2.06)
CDRH10D68RT125NP-101PC	100 \pm 25%	175 (140)	1.50 (1.73)	1.50 (1.68)
CDRH10D68RT125NP-151PC	150 \pm 25%	250 (200)	1.23 (1.46)	1.23 (1.40)
CDRH10D68RT125NP-221PC	220 \pm 25%	370 (296)	1.00 (1.25)	1.00 (1.16)
CDRH10D68RT125NP-331PC	330 \pm 25%	465 (372)	0.80 (0.97)	0.91 (1.04)
CDRH10D68RT125NP-471PC	470 \pm 25%	703 (562)	0.68 (0.83)	0.72 (0.82)
CDRH10D68RT125NP-681PC	680 \pm 25%	1030 (828)	0.60 (0.68)	0.61 (0.68)
CDRH10D68RT125NP-102PC	1000 \pm 25%	1560 (1253)	0.45 (0.56)	0.49 (0.55)

※1. Inductance measuring condition: at 100kHz.

※2. Saturation current: The value of D.C. current when the inductance decreases to 65% of it's nominal value.



※3. Temperature rise current: The value of D.C. current when the temperature rise is $\Delta t=40^{\circ}\text{C}$ ($T_a=20^{\circ}\text{C}$).

SMD Power Inductor

CDRH10D68R/T125



回流焊耐热与推荐温度曲线图



注：记载内容如有变更，恕不另行通知。订货时请联系您最近的销售办事处以获取最新产品信息。

SMD Power Inductor

CDRH10D68R/T125




直流饱和电流&温度上升曲线图

— L (20°C) — L (125°C) — ΔT


1. CDRH10D68RT125NP-1R5NC

L (μH) ΔT(°C)




2. CDRH10D68RT125NP-2R2NC

L (μH) ΔT(°C)




3. CDRH10D68RT125NP-3R3NC

L (μH) ΔT(°C)




4. CDRH10D68RT125NP-4R7NC

L (μH) ΔT(°C)




5. CDRH10D68RT125NP-6R2NC

L (μH) ΔT(°C)




6. CDRH10D68RT125NP-7R5NC

L (μH) ΔT(°C)




7. CDRH10D68RT125NP-100PC

L (μH) ΔT(°C)




8. CDRH10D68RT125NP-150PC

L (μH) ΔT(°C)



9. CDRH10D68RT125NP-220PC

L (μH) ΔT(°C)



注：记载内容如有变更，恕不另行通知。订货时请联系您最近的销售办事处以获取最新产品信息。


SMD Power Inductor

CDRH10D68R/T125




10. CDRH10D68RT125NP-330PC

L (μH) $\Delta\text{T}(\text{°C})$




11. CDRH10D68RT125NP-470PC

L (μH) $\Delta\text{T}(\text{°C})$




12. CDRH10D68RT125NP-680PC

L (μH) $\Delta\text{T}(\text{°C})$




13. CDRH10D68RT125NP-101PC

L (μH) $\Delta\text{T}(\text{°C})$




14. CDRH10D68RT125NP-151PC

L (μH) $\Delta\text{T}(\text{°C})$




15. CDRH10D68RT125NP-221PC

L (μH) $\Delta\text{T}(\text{°C})$




16. CDRH10D68RT125NP-331PC

L (μH) $\Delta\text{T}(\text{°C})$




17. CDRH10D68RT125NP-471PC

L (μH) $\Delta\text{T}(\text{°C})$



18. CDRH10D68RT125NP-681PC

L (μH) $\Delta\text{T}(\text{°C})$



注：记载内容如有变更，恕不另行通知。订货时请联系您最近的销售办事处以获取最新产品信息。

SMD Power Inductor


CDRH10D68R/T125



19. CDRH10D68RT125NP-102PC

L (μH)

ΔT ($^{\circ}\text{C}$)



有关销售办事处的信息，请[点击这里](#)。