

67-21/G6C-AP1Q2B/2T

Features

- P-LCC-2 package.
- White package.
- Optical indicator.
- Colorless clear window.
- Wide viewing angle.
- Suitable for vapor-phase reflow, Infrared reflow and wave solder processes.
- Computable with automatic placement equipment.
- Available on tape and reel (8mm Tape).
- The product itself will remain within RoHS compliant version.

Descriptions

• The 67-21 series is available in soft orange, green, blue and yellow. Due to the package design, the LED has wide viewing angle and optimized light coupling by inter reflector. This feature makes the ideal for light pipe application. The low current requirement makes this device ideal for portable equipment or any other application where power is at a premium.

Applications

- Automotive: backlighting in dashboard and switch.
- Telecommunication: indicator and backlighting in telephone and fax.
- Flat backlight for LCD, switch and symbol.
- Light pipe application.
- General use.

Revision

: 1

LifecyclePhase:正式發行

Device Selection Guide

Chip	E . 24 . 1 C. 1	Pagin Color		
Material	Emitted Color	Resin Color		
AlGaInP	Brilliant Yellow Green	Water Clear		

Everlight Electronics Co., Ltd. http://www.everlight.com Rev. 1 Page: 1 of 10

Device No.: DES-671-291 prepared date:13-Oct-2005 Prepared by: ForrestChen Release Date: 2008-09-20 00:15:47.0

Expired Period: Forever










EVERLIGHT ELECTRONICS CO.,LTD.


Technical Data Sheet

TOP View LEDs


67-21/G6C-AP1Q2B/2T


Package Dimensions







Polarity





For reflow soldering (Proposal)





Note: The tolerances unless mentioned is ± 0.1 mm, Unit = mm

Everlight Electronics Co., Ltd.

Device No.: DES-671-291

Revision : 1

http://www.everlight.com

Rev. 1

Page: 2 of 10

prepared date:13-Oct-2005

Prepared by: ForrestChen Release Date:2008-09-20 00:15:47.0

Expired Period: Forever

LifecyclePhase:正式發行



67-21/G6C-AP1Q2B/2T

Absolute Maximum Ratings (Ta=25)

Parameter	Symbol	Rating	Units
Reverse Voltage	VR	5	V
Forward Current	ĪF	40	mA
Operating Temperature	Topr	-40 ~ +85	
Storage Temperature	Tstg	-40 ~ +100	
Electrostatic Discharge(HBM)	ESD	2000	V
Power Dissipation	Pd	100	mW
Peak Forward Current (Duty 1/10 @1KHz)	IFP	80	mA
Soldering Temperature	Tsol	Reflow Soldering : 260 Hand Soldering : 350	for 10 sec.

Electro-Optical Characteristics (Ta=25)

Parameter	Symbol	Min.	Тур.	Max.	Unit	Condition
Luminous intensity	Iv	45		112	mcd	I _F =20mA
Viewing Angle	2 1/2		120		deg	I _F =20mA
Peak Wavelength	p	-	575		nm	I _F =20mA
Dominant Wavelength	d	569.5		577.5	nm	I _F =20mA
Spectrum Radiation Bandwidth			20		nm	I _F =20mA
Forward Voltage	VF	1.75		2.35	V	I _F =20mA
Reverse Current	Ir			10	μA	$V_R=5V$

Notes:

Revision

1. Tolerance of Luminous Intensity ±11%

2.Tolerance of Dominant Wavelength ±1nm

3.Tolerance of Forward Voltage ±0.1V

Everlight Electronics Co., Ltd. http://www.everlight.com Rev. 1 Page: 3 of 10

Device No. :DES-671-291 prepared date:13-Oct-2005 Prepared by: ForrestChen Release Date:2008-09-20 00:15:47.0

LifecyclePhase:正式發行 Expired Period: Forever



67-21/G6C-AP1Q2B/2T

Bin Range Of Dominant Wavelength

Group	Bin Code	Min.	Max.	Unit	Condition
A	C16	569.5	571.5		I _F =20mA
	C17	571.5	573.5		
	C18	573.5	575.5	nm	
	C19	575.5	577.5		

Bin Rang Of Luminous Intensity

Bin	Min	Max	Unit	Condition	
P1	45.0	57.0			
P2	57.0	72.0	1	IF=20mA	
Q1	72.0	90.0	mcd		
Q2	90.0	112.0	1		

Bin Rang Of Forward Voltage

		,			
Group	Bin	Min	Max	Unit	Condition
В	0	1.75	1.95		IF=20mA
	1	1.95	2.15	V	
	2	2.15	2.35		

Notes:

1.Tolerance of Luminous Intensity ±11%

2. Tolerance of Dominant Wavelength ±1nm

3.Tolerance of Forward Voltage ±0.1V

Everlight Electronics Co., Ltd. http://www.everlight.com Rev. 1 Page: 4 of 10

Device No. :DES-671-291 prepared date:13-Oct-2005 Prepared by: ForrestChen Revision : 1 Release Date:2008-09-20 00:15:47.0

LifecyclePhase:正式發行 Expired Period: Forever





EVERLIGHT ELECTRONICS CO.,LTD.


Technical Data Sheet TOP View LEDs


67-21/G6C-AP1Q2B/2T

Typical Electro-Optical Characteristics Curves











10¹



Forward Current Derating Curve





10²

Everlight Electronics Co., Ltd.

Device No.: DES-671-291

Revision : 1

LifecyclePhase:正式發行

http://www.everlight.com

Rev. 1

Page: 5 of 10

prepared date:13-Oct-2005

Prepared by: ForrestChen Release Date: 2008-09-20 00:15:47.0

Expired Period: Forever




67-21/G6C-AP1Q2B/2T

Label explanation


CAT: Luminous Intensity Rank

HUE: Dom. Wavelength Rank

REF: Forward Voltage Rank



Reel Dimensions



Note: The tolerances unless mentioned is ± 0.1 mm, Unit = mm

Everlight Electronics Co., Ltd.

Device No.: DES-671-291

Revision : 1

http://www.everlight.com

Rev. 1

Page: 6 of 10

prepared date:13-Oct-2005

Prepared by: ForrestChen Release Date:2008-09-20 00:15:47.0


Expired Period: Forever

LifecyclePhase:正式發行




67-21/G6C-AP1Q2B/2T

Carrier Tape Dimensions: Loaded quantity 2000 PCS per reel.



Note: The tolerances unless mentioned is ± 0.1 mm Unit = mm

Moisture Resistant Packaging



Everlight Electronics Co., Ltd.

Device No. :DES-671-291

Revision: 1

LifecyclePhase:正式發行

100. .DES 071 23

http://www.everlight.com

Rev. 1

Page: 7 of 10

prepared date:13-Oct-2005

Prepared by: ForrestChen Release Date:2008-09-20 00:15:47.0

Expired Period: Forever



67-21/G6C-AP1Q2B/2T

Reliability Test Items And Conditions

The reliability of products shall be satisfied with items listed below.

Confidence level: 90%

LTPD: 10%

No.	Items	Test Condition	Test Hours/Cycles	Sample Size	Ac/Re
1	Reflow Soldering	Temp.: 260 ±5 Min. 5sec.	6 min	22 PCS.	0/1
2	Temperature Cycle	H: +100 15min 5 min L: -40 15min	300 Cycles	22 PCS.	0/1
3	Thermal Shock	H: +100 5min 10 sec L: -10 5min	300 Cycles	22 PCS.	0/1
4	High Temperature Storage	Temp. : 100	1000 Hrs.	22 PCS.	0/1
5	Low Temperature Storage	Temp. : -40	1000 Hrs.	22 PCS.	0/1
6	DC Operating Life	IF = 20 mA	1000 Hrs.	22 PCS.	0/1
7	High Temperature / High Humidity	85 / 85%RH	1000 Hrs.	22 PCS.	0/1

Everlight Electronics Co., Ltd.

prepared date:13-Oct-2005

http://www.everlight.com

Rev. 1 Page: 8 of 10

Device No. :DES-671-291

: 1

Revision

Prepared by: ForrestChen

LifecyclePhase:正式發行 Expired Period: Forever

Release Date:2008-09-20 00:15:47.0

67-21/G6C-AP1Q2B/2T

Precautions For Use

1. Over-current-proof

Customer must apply resistors for protection, otherwise slight voltage shift will cause big current change (Burn out will happen).


- 2. Storage
- 2.1 Do not open moisture proof bag before the products are ready to use.
- 2.2 Before opening the package: The LEDs should be kept at 30 or less and 90%RH or less.
- 2.3 After opening the package: The LED's floor life is 1 year under 30 or less and 60% RH or less.

 If unused LEDs remain, it should be stored in moisture proof packages.
- 2.4 If the moisture absorbent material (silica gel) has faded away or the LEDs have exceeded the storage time, baking treatment should be performed using the following conditions.

 Baking treatment: 60±5 for 24 hours.
- 3. Soldering Condition

Revision

3.1 Pb-free solder temperature profile



- 3.2 Reflow soldering should not be done more than two times.
- 3.3 When soldering, do not put stress on the LEDs during heating.
- 3.4 After soldering, do not warp the circuit board.

Everlight Electronics Co., Ltd. http://www.everlight.com Rev. 1 Page: 9 of 10

Device No. :DES-671-291 prepared date:13-Oct-2005 Prepared by: ForrestChen Release Date:2008-09-20 00:15:47.0

LifecyclePhase:正式發行 Expired Period: Forever




67-21/G6C-AP1Q2B/2T

4. Soldering Iron

Each terminal is to go to the tip of soldering iron temperature less than 350 for 3 seconds within once in less than the soldering iron capacity 25W. Leave two seconds and more intervals, and do soldering of each terminal. Be careful because the damage of the product is often started at the time of the hand solder.

5.Repairing

Repair should not be done after the LEDs have been soldered. When repairing is unavoidable, a double-head soldering iron should be used (as below figure). It should be confirmed beforehand whether the characteristics of the LEDs will or will not be damaged by repairing.



EVERLIGHT ELECTRONICS CO., LTD.

Revision

Office: No 25, Lane 76, Sec 3, Chung Yang Rd, Tucheng, Taipei 236, Taiwan, R.O.C

Tel: 886-2-2267-2000, 2267-9936

Fax: 886-2267-6244, 2267-6189, 2267-6306

Rev. 1

Page: 10 of 10

http://www.everlight.com

Everlight Electronics Co., Ltd. http://www.everlight.com

> prepared date:13-Oct-2005 Prepared by: ForrestChen

Device No.: DES-671-291 Release Date:2008-09-20 00:15:47.0 : 1

LifecyclePhase:正式發行 **Expired Period: Forever**