




## P-Channel Enhancement Mode Field Effect Transistor

### Product Summary

- $V_{DS}$  -20V
- $I_D$  -55A
- $R_{DS(ON)}$  (at  $V_{GS}=-4.5V$ ) <8.3mohm
- $R_{DS(ON)}$  (at  $V_{GS}=-2.5V$ ) <10 mohm
- $R_{DS(ON)}$  (at  $V_{GS}=-1.8V$ ) <15 mohm
- 100% UIS Tested
- 100%  $\nabla V_{DS}$  Tested



**DFN3.3X3.3**

### General Description

- Trench Power LV MOSFET technology
- Excellent package for heat dissipation
- High density cell design for low  $R_{DS(ON)}$

### Applications

- High current load applications
- Load switching
- Hard switched and high frequency circuits
- Uninterruptible power supply

Marking : Q55P02

### Absolute Maximum Ratings ( $T_A=25^\circ C$ unless otherwise noted)

Parameter	Symbol	Limit	Unit
Drain-source Voltage	$V_{DS}$	-20	V
Gate-source Voltage	$V_{GS}$	$\pm 10$	V
Drain Current  $T_A=25^\circ C$	$I_D$	55	A
$T_A=100^\circ C$		35	
Pulsed Drain Current <sup>A</sup>	$I_{DM}$	160	A
Single Pulse Avalanche Energy <sup>B</sup>	$E_{AS}$	75	mJ
Total Power Dissipation  $T_c=25^\circ C$	$P_D$	38	W
$T_A=25^\circ C$		3.2	
Thermal Resistance Junction-to-Case	$R_{\theta JC}$	3.3	$^\circ C / W$
	$R_{\theta JA}$	39	
Junction and Storage Temperature Range	$T_J, T_{STG}$	-55~+150	$^\circ C$

**Electrical Characteristics (T<sub>j</sub>=25°C unless otherwise noted)**

Parameter	Symbol	Conditions	Min	Typ	Max	Units
<b>Static Parameter</b>						
Drain-Source Breakdown Voltage	BV <sub>DSS</sub>	V <sub>GS</sub> = 0V, I <sub>D</sub> =250μA	-20			V
Zero Gate Voltage Drain Current	I <sub>DSS</sub>	V <sub>DS</sub> =-20V, V <sub>GS</sub> =0V			1	μA
Gate-Body Leakage Current	I <sub>GSS</sub>	V <sub>GS</sub> = ±10V, V <sub>DS</sub> =0V			±100	nA
Gate Threshold Voltage	V <sub>GS(th)</sub>	V <sub>DS</sub> = V <sub>GS</sub> , I <sub>D</sub> =-250μA	-0.4	-0.62	-1.0	V
Static Drain-Source On-Resistance	R <sub>DS(ON)</sub>	V <sub>GS</sub> = -4.5V, I <sub>D</sub> =-15A		6.5	8.3	mΩ
		V <sub>GS</sub> = -2.5V, I <sub>D</sub> =-10A		8.0	10.0	
		V <sub>GS</sub> = -1.8V, I <sub>D</sub> =-8.0A		10.3	15	
Diode Forward Voltage	V <sub>SD</sub>	I <sub>S</sub> =-20A, V <sub>GS</sub> =0V		-0.7	-1.2	V
Maximum Body-Diode Continuous Current	I <sub>S</sub>				-55	A
<b>Dynamic Parameters</b>						
Input Capacitance	C <sub>iss</sub>	V <sub>DS</sub> =-10V, V <sub>GS</sub> =0V, f=1MHZ		3150		pF
Output Capacitance	C <sub>oss</sub>			625		
Reverse Transfer Capacitance	C <sub>rss</sub>			555		
<b>Switching Parameters</b>						
Total Gate Charge	Q <sub>g</sub>	V <sub>GS</sub> =-4.5V, V <sub>DS</sub> =-10V, I <sub>D</sub> =-20A		45		nC
Gate-Source Charge	Q <sub>gs</sub>			8.1		
Gate-Drain Charge	Q <sub>gd</sub>			11.5		
Reverse Recovery Charge	Q <sub>rr</sub>	I <sub>F</sub> =-12A, di/dt=100A/us		26		ns
Reverse Recovery Time	t <sub>rr</sub>			29		
Turn-on Delay Time	t <sub>D(on)</sub>			15		
Turn-on Rise Time	t <sub>r</sub>	V <sub>GS</sub> =-4.5V, V <sub>DD</sub> =-10V, I <sub>D</sub> =-12A, R <sub>L</sub> =1Ω R <sub>GEN</sub> =3Ω		21		ns
Turn-off Delay Time	t <sub>D(off)</sub>			96		
Turn-off fall Time	t <sub>f</sub>			166		

A. Pulse Test: Pulse Width≤300us, Duty cycle ≤2%.

B. T<sub>j</sub>=25°C, V<sub>DD</sub>=20V, V<sub>G</sub>=10V, L=0.5mH, R<sub>g</sub>=25Ω


**Typical Performance Characteristics**


Figure1. Output Characteristics




Figure2. Transfer Characteristics




Figure3. Capacitance Characteristics




Figure4. Gate Charge




Figure5. Drain-Source on Resistance




Figure6. Drain-Source on Resistance




Figure7. Safe Operation Area






Figure8. Switching wave

DFN3.3X3.3 Package information



A	B	C	C1
$3.25 \pm 0.05$	$3.25 \pm 0.05$	$0.8 \pm 0.05$	$0.2 \pm 0.02$
C2	D	E	F
0.05Max	$1.9 \pm 0.1$	$2.35 \pm 0.15$	$0.45 \pm 0.05$
G	H	e	
$0.3 \pm 0.05$	$0.35 \pm 0.05$	$0.65 \pm 0.05$	
: mm			

