



Rating :

15A 250V AC T105 UL cUL  
10A 250V AC VDE 3C KC

Insert And Extract Force: 1.36kgf~6.8kgf

Operating Life: ≥5000 cycles

Withstand Voltage: Between all terminals: 2500VAC (50-60Hz) 1min  
terminals to Base: 3750V AC (50-60Hz) 1min  
Leakage Current : 1mA

Insulation Resistance: ≥100MΩ 500V DC

Body Materil: NYLON 66 94V0

器具插座

器具开关

1. Rating:

CQC 6A 250V AC T105  
cUL 10A 125V AC / 6A 250V AC T105  
VDE 6(4)A 250V AC T85/55  
KC 6(4)A 250V AC

2. Circuit Diagram: 2P ON-OFF

3. Terminal Strength: ≥80N

4. Electrical life: ≥10000 cycles

5. Withstand Voltage: Withstand Voltage: 1500VAC 1min  
Terminals to Button: 3000VAC 1min  
Leakage Current: 1mA

6. Current resistance: ≤50mΩ (initial)

7. Insulation resistance: ≥100MΩ

8. Body Materil: NYLON 66 94V0

A4				普通公差	深圳市华灿天禄电子有限公司						
A3				COMMON TOLERANCE :							
A2				UP TO 5	±0.20	单位	mm	投影	Ac Inlet C14型	比例	Free
A1				ABOVE 5 TO 30	±0.30	UNIT		PROJECTED	品名		
REV.	DATE	REVISION DESCRIPTION	ISSUE	ANGULAR	±5°	绘图	黄旭程	核对	型号	DB-14	
						日期	2016.7.28	核准	料号	DB-14-2P+RS	
						DATE		APPROVAL BY	PART NO.		