承 认 书

APPROVAL SHEET

产品名称:	电感器		
Part Name	Inductor		
客户料号:			
Customer Part No.			
产品规格:	VLU0406-330KB		
Specification	VEGO+00 OOOKB		
规格书编号	VLU0406-YH161003		
Document No.	VESC+00 111101000		
版 本 号:	01		
Version No.			
日期:	2021/9/16		
DATE	202 1707 10		

制造			客户		
Manufacturer			Customer		
拟制	(本語物)	确认	检验	审核	批准
Draft by	Checked by	Approve by	Check by	Checked by	Approval by
蒋晓敏	黄美艳黄	张惠霞			



履历表 Resume

版本	修 改 明 细	日期
Version No.	Modify Details	Date
01	首次发行 Initial issue	2021-9-16

序号 No.	目 录 TABLE OF CONTENTS			
1	概述 Summary			
2	型号规格表示办法 How To Order			
3	结构及尺寸 Structure And Dimensions			
4	材料清单 Material list			
5	电气性能 Performance Specification			
6	工作温度范围 Operation temperature			
7	贮存方法 Storage Methods			
8	使用注意事项 Precautions For Use			

1. 概述 Summary

除非另有规定,测量和测试的大气条件的标准范围如下:环境温度 15 ℃至 35 ℃相对湿度 25%至 85%,大气压 86 kPa to 106 kPa。

对结果有任何疑问的,应当在下列范围内进行测量:环境温度 20 ℃±2 ℃相对湿度 60%至 70%,大气压 86 kPa to 106 kPa。

Unless otherwise specified, the standard range of atmospheric conditions for measurements and tests are as follows: ambient temperature: 15° C to 35° C relative humidity 25% to 85%.air pressure 86kPa to 106kPa.


If there is any doubt about the results, measurement shall be made within the following limits: ambient temperature: 20 $^{\circ}$ C±2 $^{\circ}$ C relative humidity 60% to 70%.air pressure 86kPa to 106kPa.

2. 型号规格表示办法 How To Order

- ① 产品代号,Product symbol
- ② 尺寸规格, Dimension
- ③ 电感量标称值, Inductance
- ④ 电感量公差代码, Tolerance code, N ±30%,M ±20%,K ±10%
- ⑤ 包装代码,T-编带盒盘;B-散装,Packing code: T-Tape & box;B-Bulk
- ⑥ 标准代码,空缺-标准品,标示-定制品,

Standard code, Vacant-Standard product, Indicate-custom product

3. 结构及尺寸 Structure And Dimensions





单位 Unit: mm

1. 套管包裹与本体顶部齐平;

Α	В	d	F	L1	L2
5.5MAX	8.5MAX	0.5±0.1	2.0±0.5	15±2.0	15±2.0

4. 材料清单 Material list:

No.	组件	材料	型号规格	UL 档案号码	
INO.	Component Material		Part No.	UL file No.	
1	磁芯	镍锌铁氧体	DRW4.2*6.3FSOor equivalent	不适用	
1	Core	Ni-Zn Ferrite	DRW4.2 0.3F3Ooi equivalent	Not Applicable	
2	线材	漆包	2UEW, Φ0.21mm,155°C,40.5Ts(ref.)	E194410	
	Wire	Enameled wire	20ΕW, Φ0.2 IIIIII, 155 €,40.518(Iei.)	L194410	
3	套管	热缩套管	ULΦ5.0 mm	E180908	
3	Tube	Heat Shrinkable Tube	<u> </u>	L 180908	
	引脚	镀锡铜包钢线		不适用	
4		CD line	0.50mm	Not Applicable	
	PINS	CP line			

5. 电气性能 Performance Specification

项目 Item	符号	标准 Spec.	测试条件 Test condition	测试仪器 Test instrument
电感量 Inductance	L	33µH±10%	1KHz,1V	MICOTEST 6377+6220 or equivalent
饱和电流 Saturation current	Isat	0.91A ΔL/L ≤10%	1KHz,1V	MICOTEST 6377+6220 or equivalent
直流电阻 Direct-current Resistance	DCR	0.26Ω MAX	at25℃	CH3205AC or equivalent

6. 工作温度范围(包含元件自身发热)Operation temperature (Including self-heating temperature rise.) -25~+85℃。

7. 贮存方法 Storage Methods

7.1 存储期限 Storage Period

为保证端子电极的焊接特性和包装材料处于良好状态,请于本公司发货后 6 个月内使用本产品。同时,由于端子电极的焊接特性会随时间发生变化,如果贮存时间超过 6 个月,请首先确认其焊接特性后再安装使用。

To maintain the solderability of terminal electrodes and to keep the packing material in good condition, product should be used within 6 months from the time of delivery. And the solderability of products electrodes may decrease as time passes, so in case of storage over 6 months, solderability shall be checked before actual usage.

- 7.2 存储条件 Storage Conditions
 - (1)存放货物的仓库应满足以下条件 Store products in a warehouse in compliance with the following condition:

温度(Temperature): -5 ~ +35℃ 相对湿度(Humidity): 30~70%RH

②不要使产品遭受温度和湿度的快速变化。

Do not subject products to rapid changes in temperature and humidity.

③不要将产品存放在化学环境中,如硫酸气体或碱性气体中,否则会降低电极端子的焊接 特性和使电感器腐蚀。

Do not store the products in chemical atmosphere such as one containing sulfurous acid gas or alkaline gas, that will causes poor solderability and corrosion of inductors.

(4)为了避免受潮气、灰尘等物质的影响,产品应保管于货架上。

Store products on pallets to protect from humidity, dust, etc

(5)产品应避免热冲击、振动以及直接光照等等。

Avoid heat shock, vibration, direct sunlight, etc.

8. 使用注意事项 Precautions For Use

8.1 本公司产品适用于 AV 设备、OA 设备、家电、信息服务等一般电子设备中。

Our products are designed and promoted for use in general electronic devices such as audio-video equipment, office automation equipment, home appliance and information service.

8.2 当本公司的产品使用在一般电子设备以外的领域时,对于此所引发的设备失效我司将不承担任何法律责任。

In case of using the product for the purpose other than general electronics devices, we shall not be held liable for any dysfunctions in or damage to the equipment with which the product is used.

8.3 本承认书只保证我司产品作为一个单体时的质量情况,当我司产品被安装到贵司产品上时,请贵司对使用在贵司电路上的产品情况进行了有效评价和确认。

Our specification limits the quality of the component as a single unit. Please ensure the component is thoroughly evaluated in your application circuit.

8.4 不要对产品施加过大的振动或机械冲击;

Do not apply excessive vibration or mechanical shock to products.

8.5 为防止断线,请不要使用锋利的物体接触线圈,如镊子;

Do not touch wire with sharp objects such as tweezers to prevent wire breakage.

8.6 在产品贴装时不要使用过大的压力,避免磁芯断裂。

Do not apply excessive stress to products mounted on boards to prevent core breakage.