

This document was generated on 07/01/2021 PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:	<u>0565790519</u>		
Status:	Active		
Overview:	USB Products and	Solutions	
		eptacle, Right-Angle, Through Hole Solder Tails and Shell Tabs,	
Lead-Free			
Documents:			
3D Model		Product Specification PS-56579-015-001 (PDF)	
Drawing (PDF)		RoHS Certificate of Compliance (PDF)	
<u>3D Model (PDF)</u>			- V
			- Series image - Reference only
General			
Product Family		I/O Connectors	EU ELV
Series		56579	Not Relevant
Application		Wire-to-Board	Not Kelevalit
Component Type		Receptacle	EU RoHS China RoHS
Overview		USB Products and Solutions	Compliant
Product Name		USB 2.0, USB OTG (On-The-Go)	REACH SVHC
Туре		Mini-AB (OTG)	Not Contained Per -
UPC		822348297177	D(2020)9139-DC (19
<u>.</u>			Jan 2021)
Physical		N/A	Halogen-Free
Boot Color		N/A	<u>Status</u>
Circuits (Loaded)		5	Not Low-Halogen
Circuits (maximum)		5	For more information, please visit Contact US
Color - Resin Gender		Gray Female	China ROHS Green Image
Lock to Mating Part		Yes	ELV Not Relevant
Material - Metal		High Performance Alloy (HPA), Phosphor Bronze	RoHS Phthalates Not Contained
Material - Plating Mating		Gold	
Material - Plating Termination		Tin	
Material - Resin		High Temperature Thermoplastic	Oceands Depte in this Ocean
Net Weight		584.300/mg	Search Parts in this Series
Number of Rows		1	<u>56579</u> Series
Orientation		Right Angle	
PC Tail Length		1.80mm	Mates With
PCB Locator		Yes	<u>592053301</u> , <u>592049405</u>
PCB Retention		Yes	
PCB Thickness - Recommended		0.80mm	
Packaging Type		Tray	
Panel Mount		No	
Pitch - Mating Interf		0.80mm	
Pitch - Termination Interface		0.80mm	
Plating min - Mating Plating min - Termination		0.762µm	
		1.016µm	
Polarized to Mating Part Polarized to PCB		Yes Yes	
Polarized to PCB		1	
Surface Mount Compatible (SMC)		I No	
Temperature Range - Operating		-20° to +85°C	
Termination Interface: Style		Through Hole	
Waterproof / Dustproof		No	
Wire Size AWG		N/A	
Electrical			
Current - Maximum	per Contact	1.0A	

Full Shield

Current - Maximum per Contact Shield Type

Shielded Voltage - Maximum Yes 30V AC (RMS)/DC

Material Info

Reference - Drawing Numbers Product Specification Sales Drawing

PS-56579-015-001 SD-56579-014

This document was generated on 07/01/2021 PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION