

This document was generated on 07/05/2021 PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: 056	<u>5790576</u>			
Status: Active			EU ELV	
	Mini USB, AB-Receptacle, Right-Angle, Surface Mount Solder Tails and Shell Tabs, with Cover Tape, Lead-Free		Not Relevant <u>EU RoHS</u> Compliant	China RoHS
	-		REACH SVHC	
General			Not Contained Per	-
Product Family		I/O Connectors	D(2020)9139-DC (1	9
Series		56579	Jan 2021)	
Application		Wire-to-Board	Halogen-Free	
Component Type		Receptacle	Status	
Overview		usb	Not Low-Halogen	
Product Name		USB 2.0, USB OTG (On-The-Go)		n, please visit <u>Contact US</u>
Туре		Mini-AB (OTG)		in, ploade their <u>bonnadt be</u>
UPC		822348392223	China ROHS	Green Image
OFC		022340392223	ELV	Not Relevant
Physical			RoHS Phthalates	Not Contained
Boot Color		N/A		
Circuits (Loaded)		5		
Circuits (maximum)		5		
Color - Resin		Gray	Search Parts in this Series	
Gender			<u>56579</u> Series	
		Female		
Lock to Mating Part		Yes	Mates With	
Material - Metal		High Performance Alloy (HPA), Phosphor Bronze		Plug USB OTG mini-B
Material - Plating Mating		Gold		
Material - Plating Termination		Tin	Plug	
Material - Resin		High Temperature Thermoplastic		
Net Weight		0.565/g		
Number of Rows		1		
Orientation		Right Angle		
PCB Locator		No		
PCB Retention		Yes		
PCB Thickness - Recommended		0.80mm		
Packaging Type		Embossed Tape on Reel		
Panel Mount		No		
Pitch - Mating Interface		0.80mm		
Pitch - Termination Interface		0.80mm		
Plating min - Mating Plating min - Termination		0.762µm		
Plating min - Termination		1.016µm		
Polarized to Mating Part		Yes		
Polarized to PCB		Yes		
Ports		1		
Surface Mount Compatible (SMC)		Yes		
Temperature Range - Operating		-20° to +85°C		
Termination Interface: Style		Surface Mount		
Waterproof / Dustproof		No		
Wire Size AWG		N/A		
Electrical				
	act	1.0.4		
Current - Maximum per Contact		1.0A		
Shield Type Shielded		Full Shield		
Voltage - Maximum		Yes 30V AC (RMS)/DC		
Solder Process Data				
	mporaturo (accondo)	002		
Duration at Max. Process Temperature (seconds)				
Lead-freeProcess Capability		REFLOW		
Max. Cycles at Max. Process Temperature		001		

Material Info

Reference - Drawing Numbers Product Specification Sales Drawing

PS-56579-015-001 SD-56579-015, SD-56579-016

This document was generated on 07/05/2021 PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION