

■ Moisture sensitivity level(MSL): Level 3

#### Specifications


				Abso	olute Ma	ximum R	atings (Ta=25	°C)			Electr	ical and	d Optica	I Chara	acteristi	cs (Ta=	=25⁰C)					
Part No.	Chip Structure	Emitting	Power	Forward	Peak Forward	Reverse		Storage Temp.		Voltage V <sub>F</sub>	Reverse	Current I <sub>R</sub>			aveleng coordinat	-	Lumino	ous Inte	nsity I			
		Color	Dissipation	Current	Current	Voltage		-	Тур.	١ <sub>F</sub>	Max.	V <sub>R</sub>	Min.*2	Тур.	Max.*2	I <sub>F</sub>	Min.	Тур.	١ <sub>F</sub>			
			P <sub>D</sub> (mW)	I <sub>F</sub> (mA)	I <sub>FP</sub> (mA)	$V_{R}(V)$	T <sub>opr</sub> (°C)	T <sub>stg</sub> (°C)	(V)	(mA)	(µA)	(V)	(nm)	(nm)	(nm)	(mA)	(mcd)	(mcd)	(mA)			
SML-A12V8T			54	20					2.2				624	630	636		16	40				
SML-A12U8T		Red		20					2.2				614	620	626		25	63				
SML-A12UT(J)			75	30					2.0				-	624	-		36					
SML-A12D8T			Orange 75 Yellow 72 Yellow	Orongo	Orongo	54	20			-40~+85	-40~+100	2.2		10		601	605	609		40	100	100
SML-A12DT(J)					30			-40 - +03	-40 - 1100	2.0 20	00	10		-	606	-			36 20	00		
SML-A12WT(J)	AlGaInP			-		30	400*1				2.0 20	20			587	500	593	20	30		20	
SML-A12Y8T				reliow	renow		00	100* <sup>1</sup>	5					5	586	590	594		25	63 25		
SML-A12M8T					54	20					2.2				568	572	576		10	25		
SML-A12MT(J)		( addition of the second se		65	25			-30~+85	-40~+85	2.1		100		567	570	573		14	40			
SML-A12P8T	1		54						2.2		10		556	560	564		2.5	6.3				
SMLA12EC6T		68	Green 6	68 20	20			40 67		3.0		100	00	520	527	535			56			
SMLA13BC8T	InGaN		66	-4	-40~+85	-40~+100		5	4.0		465	470	475	5	22	36	5					
SMLA12WBC7W *3	1	White	33	10	50				2.9		10		(x,y)	(0.30,	0.30)			56				

\*1 : 1/10,1kHz \*2 : Measurement tolerance:  $\pm 1$ nm, \*3: Brightness for white color is noted with chromaticity coordinate(x,y). Red text :Not Recommended for New designs

EXCELED<sup>™</sup> is ROHM's pending trademark.


## Electrical Characteristics Curves

## Reference




## Fig.3 Luminous Intensity - Forward Current






## Electrical Characteristics Curves

## Reference



#### Fig.3 Luminous Intensity - Forward Current




Ta=25⁰C

10 12 14 16 18 20 22 24 26 28 30

FORWARD CURRENT : I<sub>F</sub> [mA]

Fig.4 Derating





RELATIVE LUMINOUS INTENSITY

1.4

1.2

1

0.8

0.6

0.4

0.2


0

0 2 4 6 8

## Electrical Characteristics Curves


# Reference

[Data Sheet]




3 Ta=25⁰C 2.8 SMLA12EC6T RELATIVE LUMINOUS INTENSITY SMLA13BC8T SMLA12WBC7W 2.6 2.4 2.2 2 1.8 1.6 1.4 1.2 1 0.8 0.6 0.4 0.2 0 0 2 6 8 10 12 18 20 4 14 16 FORWARD CURRENT : I<sub>F</sub> [mA]

25 24 23 22 21 20 19 18 17 16



Reference

[Data Sheet]




# Rank Reference of Brightness\*

#### \*Measurement tolerance:±10%


Red(V,U)														(Ta	=25ºC, I <sub>F</sub>	=20mA)
Rank	G	Н	J	К	L	М	Ν	Р	Q	R	S	Т	U	V	W	Х
lv (mcd)	1.0~1.6	1.6~2.5	2.5~4.0	4.0~6.3	6.3~10	10~16	16~25	25~40	40~63	63~100	100~160	160~250	250~400	400~630	630~1000	1000~1600
SML-A12V8T																
SML-A12U8T																
SML-A12UT (J)																
Orange(D)														(Ta	=25°C, I <sub>F</sub>	=20mA)
Rank	G	Н	J	K	L	М	Ν	Р	Q	R	S	Т	U	V	W	Х
	1.0~1.6	1.6~2.5	2.5~4.0	4.0~6.3	6.3~10	10~16	16~25	25~40	40~63	63~100	100~160	160~250	250~400	400~630	630~1000	1000~1600
SML-A12D8T																
SML-A12DT(J)																
Yellow(Y, \	N)													(Ta	=25°C, I <sub>F</sub>	=20mA)
Rank	G	Н	J	K	L	М	Ν	Р	Q	R	S	Т	U	V	W	Х
lv (mcd)	1.0~1.6	1.6~2.5	2.5~4.0	4.0~6.3	6.3~10	10~16	16~25	25~40	40~63	63~100	100~160	160~250	250~400	400~630	630~1000	1000~1600
SML-A12Y8T																
SML-A12WT(J)																
Yellowish (	Greer	n/Gre	en(M	,P)										(Ta	=25ºC, I <sub>F</sub>	=20mA)
Rank	G	Н	J	K	L	М	Ν	Р	Q	R	S	Т	U	V	W	Х
lv (mcd)	1.0~1.6	1.6~2.5	2.5~4.0	4.0~6.3	6.3~10	10~16	16~25	25~40	40~63	63~100	100~160	160~250	250~400	400~630	630~1000	1000~1600
SML-A12MT(J)																
SML-A12M8T																
SML-A12P8T																
Green(E)													(Ta	a=25ºC,	I <sub>F</sub> =5mA)	_
Rank	G	Н	J	K	L	М	Ν	Р	Q	R	S	Т	U	V	W	
lv (mcd)	0.9~1.4	1.4~2.2	2.2~3.6	3.6~5.6	5.6~9	9~14	14~22	22~36	36~56	56~90	90~140	140~220	220~360	360~560	560~900	
SMLA12EC6T																
Blue(B)													(Ta	a=25°C, 3	I <sub>F</sub> =5mA)	_
Rank	G	Н	J	К	L	М	Ν	Р	0	R	S	Т	U	V	W	
lv (mcd)	0.9~1.4	1.4~2.2	2.2~3.6	3.6~5.6	5.6~9	9~14	14~22	22~36	36~56	56~90	90~140	140~220	220~360	360~560	560~900	
SMLA13BC8T																
White(WB)	)												(Ta	a=25ºC, 1	I <sub>F</sub> =5mA)	•
Rank	G	Н	J	К	L	М	Ν	Р	0	R	S	Т	U	V	W	
lv (mcd)	0.9~1.4	1.4~2.2	2.2~3.6	3.6~5.6	5.6~9	9~14	14~22	22~36	36~56			140~220	<u> </u>	360~560	560~900	
SMLA12WBC7W																

# Chromaticity Diagram



				(Т	a = 2	5℃、1	[f=5n	nA)	
	ł	F		Н		ł	(	С	
Х	у	Х	у	Х	у	Х	у	Х	у
0.280	0.248	0.283	0.305	0.287	0.295	0.304	0.330	0.330	0.318
0.296	0.276	0.304	0.330	0.307	0.315	0.330	0.360	0.356	0.351
0.283	0.305	0.307	0.315	0.311	0.294	0.330	0.318	0.361	0.385
0.264	0.267	0.287	0.295	0.296	0.276	0.311	0.294	0.330	0.360
Moa	Mascurament tolerance : +0.02								

Measurement tolerance :  $\pm 0.02$ 



#### Packing Specification

Complying with IPC/JEDEC J-STD-033.

## Precaution (Surface Mount Device)

#### 1. Storage

If the product is heated during the reflow under the condition of hygroscopic state,

it may vaporize and expand which will influence the performance of the product.

Therefore, the package is waterproof. Please use the product following the conditions:

•Using Conditions

Classification	Temperature Humidity		Expiration Date	Remark		
①Before using	Before using 5~30°C		Within 1 year from Receiving	Storage with waterproof package		
②After opening package	5~30℃	Below 70%RH	Within 168h	Please storing in the airtight container with our desiccant (silica gel)		

#### Baking

Bake the product in case of below:

①The expiration date is passed.

(2) The color of 5% and 10% on humidity indicator card is not green.

(Even if the product is before expiration date.)

#### Baking Conditions

Tempera	Temperature Tim		Humidity			
60±3℃		12~24h	Below 20%RH			
Remark	•Reel and so please	ducts in reel. embossed tape try not to apply end bake once.	are easy to be deformed when baking, stress on it.			

#### 2. Application Methods

#### 2 – 1. Precaution for Drive System and Off Mode

Design the circuit without the electric load exceeding the ABSOLUTE MAXIMUM RATING that applies on the products. If drive by constant voltage, it may cause current deviation of the LED and result in deviation of luminous intensity, so we recommend to drive by constant current.

(Deviation of VF Value will cause deviation of current in LED.) Furthermore, for off mode, please do not apply voltage neither forward nor reverse. Especially, for the products with the Ag-paste used in the die bonding, there's high possibility to cause electro migration and result in function failure.

#### <u>2 – 2. About Derating</u>

It is considered that derating characteristics will not result in LED chip's electrical destruction. Even within the derating, the reliability and luminous life can be affected depending on operating conditions and ambient environment. So we would be appreciate it if you can confirm with your application again.

#### 2 – 3. About product life

Depending on operating conditions and environment(applied current, ambient temperature and humidity, corrosive gas), decreasing of luminosity and change of chromaticity may occur even within the specification conditions.

Please contact our sales office if you use it for the following applications.

1)It requires long luminosity life

②It is always lit

#### 2 – 4. Applied Stress on Product

No resin hardening agent such as filler is used in the sealing resin of the product.

Therefore, please pay attention to the overstress on it which may influence its reliability.

#### <u>2 – 5. Usage</u>

The Product is LED. We are not responsible for the usage as the diode such as Protection Chip, Rectifier, Switching and so on.

#### 3. Others

#### <u>3 – 1. Surrounding Gas</u>

Notice that if it is stored under the condition of acid gas (chlorine gas, sulfured gas) or alkali gas (ammonia), it may result in low soldering ability (caused by the change in quality of the plating surface ) or optical characteristics changes (light intensity, chrominance) and change in quality of cause die bonding (Ag-paste) materials. All of the above will function failure of the products.

Therefore, please pay attention to the storage environment for mounted product (concern the generated gas of the surrounding parts of the products and the atmospheric environment).

#### <u>3 – 2. Electrostatic Damage</u>

The product is part of semiconductor and electrostatic sensitive, there's high possibility to be damaged by the electrostatic discharge. Please take appropriate measures to avoid the static electricity from human body and earthing of production equipment. Especially, InGaN type LEDs have lower resistance value of electrostatic discharge and it is recommended to introduce the ESD protection circuit. The resistance values of electrostatic discharge (actual values) vary with products, therefore, please call our Sales staffs for inquiries.

3 – 3. Electromagnetic Wave

Applications with strong electromagnetic wave such as, IH cooker, will influence the reliability of LED, therefore please evaluate before using it.

## 4. Mounting

#### 4 – 1. Soldering

•No resin hardening agent such as filler is used in the sealing resin of the product. Therefore, resin expansion and moisture absorption at humidity will cause heat stress during soldering process and finally has bad influence on the product's reliability.

•The product is not guaranteed for flow soldering.

•Do not expose the product in the environment of high temperature (over 100°C) or rapid temperature shift (within 3°C/sec. of temperature gradient) during the flow soldering of surrounding parts. In case of carrying out flow soldering of surrounding parts without recommended conditions, please contact us for inquiries.

•Please set appropriate reflow temperature based on our product usage conditions and specification.

•The max for reflowing is 2 times, please finish the second reflow soldering and flow soldering with other parts within the usage limitation after open the moistureproof package.

•Compare with N2 reflow, during air reflow, because of the heat and surrounding conditions, it may cause the discoloration of the resin.

•For our product that has no solder resist, because of its solder amount and soldering conditions, one of its specific characteristics is that solder will penetrate into LED. Thus, there's high possibility that will influence its reliability.Therefore, please be informed, concerning it before using it.

#### 4 – 2. Automatic Mounting

#### 4 - 2 - 1 . Suction nozzle


Excessive load may cause damage inside the LED product, so select an optimal suction nozzle according to the material and shape of the LED product.

4-2-2. Mini Package (Smaller than 1608 size)

•Vibration may result in low mounting rate since it will cause the static electricity of product and adhere to top cover tape. Therefore, the magnet should be set on parts feeder cassette of the mounter to control the product stabilization. In addition, it is recommended to set ionizer to prevent electrostatic charge.

#### 4 – 3. Mounting Location

The stress like bending stress of circuit board dividing after mounting, may cause LED package crack or damage of LED internal junction, therefore, please concern the mounting direction and position to avoid bending or screwing with great stress of the circuit board.



Stress strength according to he mounting position: A > B > C > D

#### 4-4. Mechanical Stress after Mounting


The mechanical stress may damage the LED after Circuit Mounting,

so please pay attention to the touch on product.

4 – 5. Soldering Pattern for Recommendation

We recommend the soldering pattern that shows on the right. It will be different according to mounting situation of circuit board, therefore,


please concern before designing.



4 – 6. Reflow Profile

For reflow profile, please refer to the conditions below:(※) ■Meaning of marks, Conditions

Mark	Meanings	Conditions					
Ts <sub>max</sub>	Maximum of pre-heating temperature	180℃					
Ts <sub>min</sub>	Minimum of pre-heating temperature	140°C					
t <sub>s</sub>	Time from Tsmin to Tsmax	Over 60sec.					
Τ <sub>L</sub>	Reference temperature	230~260℃					
tL	Retention time for TL	Within 40sec.					
Τ <sub>Ρ</sub>	Peak temperature	260℃(Max)					
t <sub>P</sub>	Time for peak temperature	Within 10sec.					
ΔT <sub>R</sub> /Δt	Temperature rising rate	Under 3℃/sec.					
ΔT <sub>D</sub> /Δt	Temperature decreasing rate	Over -3℃/sec.					



\*Above conditions are for reference. Therefore, evaluate by customer's own circuit boards and reflow furnaces before using, because stress from circuit boards and temperature variations of reflow furnaces vary by customer's own conditions.

## 4 – 7. Attention Points in Soldering Operation

This product was developed as a surface mount LED especially suitable for reflow soldering. So reflow soldering is recommended. In case of implementing manual soldering,

please take care of following points.

①SOLDER USED

Sn-Cu, Sn-Ag-Cu, Sn-Ag-Bi-Cu

2 HAND SOLDERING CONDITION

LED products do not contain reinforcement material such as a glass fillers.

So thermal stress by soldering greatly influence its reliability.

Please keep following points for manual soldering.

	ITEM	RECOMMENDED CONDITION	
a)	Heating method	Condition ) Temp. of iron top less than 400℃ within 3 sec. Heating on PCB pattern, not direct to the LED. (Fig-1)	SOLDERING IRON
b)	Handling after	Please handle after the part temp.	Ļ
0)	soldering	goes down to room temp.	

#### 4 – 8. Cleaning after Soldering

Please follow the conditions below if the cleaning is necessary after soldering.

reade renormane contactors below in the dealining to needboary after bolaciningi						
Solvent	We recommend to use alcohols solvent such as, isopropyl alcohols					
Temperature	Under 30℃ within 3 minutes					
Ultrasonic Cleaning	15W/Below 1 liter (capacity of tank)					
Drying	Under 100°C within 3 minutes					

SOLDERING

	Notes
1)	The information contained herein is subject to change without notice.
2)	Before you use our Products, please contact our sales representative and verify the latest specifica- tions.
3)	Although ROHM is continuously working to improve product reliability and quality, semicon- ductors can break down and malfunction due to various factors. Therefore, in order to prevent personal injury or fire arising from failure, please take safety measures such as complying with the derating characteristics, implementing redundant and fire prevention designs, and utilizing backups and fail-safe procedures. ROHM shall have no responsibility for any damages arising out of the use of our Poducts beyond the rating specified by ROHM.
4)	Examples of application circuits, circuit constants and any other information contained herein are provided only to illustrate the standard usage and operations of the Products. The peripheral conditions must be taken into account when designing circuits for mass production.
5)	The technical information specified herein is intended only to show the typical functions of and examples of application circuits for the Products. ROHM does not grant you, explicitly or implicitly, any license to use or exercise intellectual property or other rights held by ROHM or any other parties. ROHM shall have no responsibility whatsoever for any dispute arising out of the use of such technical information.
6)	The Products are intended for use in general electronic equipment (i.e. AV/OA devices, communi- cation, consumer systems, gaming/entertainment sets) as well as the applications indicated in this document.
7)	The Products specified in this document are not designed to be radiation tolerant.
8)	For use of our Products in applications requiring a high degree of reliability (as exemplified below), please contact and consult with a ROHM representative : transportation equipment (i.e. cars, ships, trains), primary communication equipment, traffic lights, fire/crime prevention, safety equipment, medical systems, servers, solar cells, and power transmission systems.
9)	Do not use our Products in applications requiring extremely high reliability, such as aerospace equipment, nuclear power control systems, and submarine repeaters.
10)	ROHM shall have no responsibility for any damages or injury arising from non-compliance with the recommended usage conditions and specifications contained herein.
11)	ROHM has used reasonable care to ensure the accuracy of the information contained in this document. However, ROHM does not warrants that such information is error-free, and ROHM shall have no responsibility for any damages arising from any inaccuracy or misprint of such information.
12)	Please use the Products in accordance with any applicable environmental laws and regulations, such as the RoHS Directive. For more details, including RoHS compatibility, please contact a ROHM sales office. ROHM shall have no responsibility for any damages or losses resulting non-compliance with any applicable laws or regulations.
13)	When providing our Products and technologies contained in this document to other countries, you must abide by the procedures and provisions stipulated in all applicable export laws and regulations, including without limitation the US Export Administration Regulations and the Foreign Exchange and Foreign Trade Act.
14)	This document, in part or in whole, may not be reprinted or reproduced without prior consent of ROHM.



Thank you for your accessing to ROHM product informations. More detail product informations and catalogs are available, please contact us.

# ROHM Customer Support System

http://www.rohm.com/contact/

#### **General Precaution**

- 1. Before you use our Products, you are requested to care fully read this document and fully understand its contents. ROHM shall not be in an y way responsible or liable for failure, malfunction or accident arising from the use of a ny ROHM's Products against warning, caution or note contained in this document.
- 2. All information contained in this docume nt is current as of the issuing date and subject to change without any prior notice. Before purchasing or using ROHM's Products, please confirm the latest information with a ROHM sale s representative.
- 3. The information contained in this document is provided on an "as is" basis and ROHM does not warrant that all information contained in this document is accurate an d/or error-free. ROHM shall not be in an y way responsible or liable for any damages, expenses or losses incurred by you or third parties resulting from inaccuracy or errors of or concerning such information.