



Recommended P.C.B Layout
General Tolerance±0.05

Specifications:

规格:
Voltage rating:600V AC/DC
额定电压: 600V AC/DC
Current rating:9A AC/DC
额定电流: 9A AC/DC
Withstanding voltage:1500V AC/minute
耐受电压: 1500V AC/分钟
Temperature range:-25℃+85℃
温度范围: -25℃+85℃
Insulation resistance:≥1000MΩ
绝缘电阻: ≥1000MΩ
Contact resistance:≤10mΩ
接触电阻: ≤10mΩ
After environmental testing:≤20mΩ
环境测试后: ≤20兆欧

X9357 W V X-2'XX S-XX SW

- 01 Series No
- 02 Category:W-wafer
- 03 Welding Board Angle:V-Straight 180°
- 04 Welding Way: Blank-DIP
- 05 Row No.-Pin No: 2'XX-2'02P-2'12P
- 06 Plug the Pin&Special NO. S-With the column
- 07 Material:NO-PA66 94V-0-N2-PA66 94V-2
- 08 Planting Category:SW-Fog Tin plating

Poles	Dimensions(mm)			Poles	Dimensions(mm)		
	A	B	C		A	B	C
2*01	/	5.40	9.40	2*07	25.20	30.60	34.60
2*02	4.20	9.60	13.60	2*08	29.40	34.80	39.80
2*03	8.40	13.80	17.80	2*09	33.60	39.00	43.00
2*04	12.60	18.00	22.00	2*10	37.80	43.20	47.20
2*05	16.80	22.20	26.20	2*11	42.00	47.40	51.40
2*06	21.00	26.40	30.40	2*12	46.20	51.60	55.60

X9357WV-2'XXS-N2SW	Nylon 66 UL 94V-2	Brass	Tin-Plated	X9357H
X9357WV-2'XXS-N0SW	Nylon 66 UL 94V-0			
PART NO	Material	Material(Pin)	Finish(Pin)	Suitable XKB Terminal

广东星坤科技股份有限公司

生 日期

文件工程

REVISIONS

DATE REVISED APPROVED

UNSPECIFIED TOLERANCES

www.xkb.com www.helloxkb.com www.helloxkb.cn

DSND	DATE	SCALE: N/A	MODEL TYPE: X9357WV-2'XXS-XXSW
DWNN	DATE	VIEW: ①	PART NO.: 4.20mm Crimp Style Connector
CHKD	DATE	UNIT: mm/in	DWG NO.:
APPD	DATE	SIZE: A4	
XKB INDUSTRIAL PRECISION CO.,LIMITED			WEIGHT 1.0g SHEET 1/1 REVISION A0