

Specifications:



规格:

- Voltage rating:600V AC/DC
- 额定电压: 600V AC/DC
- Current rating:9A AC/DC
- 额定电流: 9A AC/DC
- Withstanding voltage: 1500V AC/minute
- 耐受电压: 1500V AC/分钟
- Temperature range:-25℃+85℃
- 温度范围: -25℃+85℃
- Insulation resistance:≥1000MΩ
- 绝缘电阻: ≥1000MΩ
- Contact resistance:≤10mΩ
- 接触电阻: ≤10mΩ
- After environmental testing:≤20mΩ
- 环境测试后: ≤20兆欧

XKB Connectivity

X9357 W V X 2\*XX ES -XX XX XX

- 01 Series No
- 02 Category:W-wafer
- 03 Welding Board Angle:V-Straight 180°
- 04 Welding Way: Blank-DIP
- 05 Row No.-Pin No: 2\*XX-Double
- 06 Plug the Pin&Special NO.:  
FS-The hollow needle with positioning column
- 07 Material:NO-PA66 94V-0;N2-PA66 94V-2
- 08 Planting Category:SN-Bright tin plating  
△ G30-Contact area Gold plating;30u" min;  
Tail area Bright tin plating
- 09 Color:Blank-Natural Color



XKB Connectivity

| Poles | Dimensions(mm) |       | Poles | Dimensions(mm) |       |
|-------|----------------|-------|-------|----------------|-------|
|       | A              | B     |       | A              | B     |
| 2*01  | —              | 5.60  | 2*07  | 25.20          | 36.80 |
| 2*02  | 4.20           | 9.80  | 2*08  | 29.40          | 35.00 |
| 2*03  | 8.40           | 14.00 | 2*09  | 33.60          | 39.20 |
| 2*04  | 12.60          | 18.20 | 2*10  | 37.80          | 43.40 |
| 2*05  | 16.80          | 22.40 | 2*11  | 42.00          | 47.60 |
| 2*06  | 21.00          | 26.60 | 2*12  | 46.20          | 51.80 |

XKB Connectivity

| PART NO              | Material          | Material(Pin) | Finish(Pin) | Suitable XKB Terminal |
|----------------------|-------------------|---------------|-------------|-----------------------|
| X9357WV-2*XXFS-NOG30 | Nylon 66 UL 94V-2 |               |             |                       |
| X9357WV-2*XXFS-N2SN  | Nylon 66 UL 94V-2 | Brass         | Tin-Plated  | X937H                 |
| X9357WV-2*XXFS-N0SN  | Nylon 66 UL 94V-0 |               |             |                       |

Recommended P.C.B Layout

General Tolerance±0.05

XKB Connectivity

广东星坤科技股份有限公司

生 日期

文件工程章

| ANGLAR      | ±5°  |
|-------------|------|
| L ≤ 4       | ±0.2 |
| 4 < L ≤ 16  | ±0.3 |
| 16 < L ≤ 63 | ±0.4 |
| L > 63      | ±0.5 |

UNSPECIFIED TOLERANCES

| DSND                                 | DATE | SCALE: NA   | MODEL TYPE:<br>X9357WV-2*XXFS-XXXX        |
|--------------------------------------|------|-------------|---|
| DWNN                                 | DATE | VIEW:       | PART NO.:<br>4.20mm Crimp Style Connector |
| CHKD                                 | DATE | UNIT: mm/in | DWG NO.:                                  |
| APPD                                 | DATE | SIZE: A4    |   |
| XKB INDUSTRIAL PRECISION CO.,LIMITED |      |             | WEIGHT<br>1.0g                            |
|                                      |      |             | SHEET<br>1/1                              |
|                                      |      |             | REVISION<br>A0                            |

REVISIONS DATE REVISED APPROVED

www.xkb.com www.helloxkb.cn